

PERFORMANCE**Processor**

AMD Ryzen™ AI 7 PRO 360 (8C / 16T, 2.0 / 5.0GHz, 8MB L2 / 16MB L3)

AI PC Category

Copilot+ PC

NPU

Integrated AMD Ryzen™ AI, up to 50 TOPS

Graphics

Integrated AMD Radeon™ 880M Graphics

Chipset

AMD SoC Platform

Memory

32GB Soldered LPDDR5x-7500

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

32GB soldered memory, not upgradable

Storage

1TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Support^[1]

One drive, up to 1TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Camera

5.0MP + IR Discrete with Privacy Shutter

Microphone

2x, 360°

Battery

Integrated 58Wh

Power Adapter

65W USB-C® Slim (2-pin)

DESIGN**Display^[2]**

14" WUXGA (1920x1200) IPS 400nits Anti-glare, 100% sRGB, Low Power

Touchscreen

None

Keyboard

Backlit, French

Case Color

Black

Case Material

Carbon Fiber Hybrid (Top), Aluminium (Bottom)

Pen

Pen Not Supported

Dimensions (WxDxH)^[3]

313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

Weight^[4]

Starting at 1.30 kg (2.86 lbs)

SOFTWARE**Operating System**

Windows® 11 Pro, French

Bundled Software

None

CONNECTIVITY**Ethernet^[5]**

No Onboard Ethernet

WLAN + Bluetooth®^[6]

Qualcomm® Wi-Fi® 7 NCM825, 802.11be 2x2 + BT5.3

WWAN

Non-WWAN

SIM Card

None

NFC

None

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)

None

Docking

Various docking solutions supported via Thunderbolt™ / USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® T14s Gen 6 \(AMD\)](#)**SECURITY & PRIVACY****Smart Card Reader**

None

Security Chip

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

- IR camera for Windows® Hello (facial recognition)
- Camera privacy shutter
- Ultrasonic Human Presence Detection

MANAGEABILITY**System Management**

Non-DASH

SERVICE**Base Warranty**

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES**Bundled Accessories^[7]**

None

CERTIFICATIONS**Green Certifications^[8]**

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes

Announce Date : 2024-10-23

EAN / UPC / JAN : 198155053023

End of Support : 2031-05-22

Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[5] Ethernet support via optional Lenovo USB-C to Ethernet Adapter.

[6] Wi-Fi 7 is only enabled on Windows 11 and operates as.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to
<https://psref.lenovo.com/Detail/2579?M=21M1001YCA>

Premier Support - A direct 24x7x365 line to our most elite technicians.




Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management



Copilot+PC

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39383)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36154)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A14086)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference