

SEAL CLEAN™ WATERPROOF KEYBOARD

Model: SSKSV207, SSWKSV207,
SSKSV207L, SSWKSV207L

Seal Clean Waterproof Keyboards from Seal Shield™. 100% waterproof & dishwasher-safe keyboard is IPX8-certified and designed to withstand industrial-grade disinfectants & cleaners. True type keyboard with tactile feel and full travel keys for smooth and natural typing. Features a Quick Connect or Long Cable with RF shielding and a Seal Cap™ for easy plug-and-play. Full-Size numeric keypad and Laser-etched keycaps enhance durability and product longevity throughout regular and vigorous cleaning.

FEATURES:



100% Waterproof,
Dishwasher-Safe,
& Fully Submersible



IPX8-Certified



Full-Size Numeric
Keypad and
Laser Etched Keycaps



Gold Coated USB
with Seal Cap™ USB
Protector



Cable Options Quick
Connect or Long Cable
with RF Shielding



Designed to Withstand
Industrial-Grade
Disinfectants & Cleaners



Standard Style Keyboard
for Smooth Typing



ABS Plastic with
Stainless Steel Screws &
Non-Corrosive Components



SSKSV207



SSWKSV207



SSKSV207L



SSWKSV207L

ADVANCED CLEANING CAPABILITIES

- Dishwasher-Safe
- Compatible with Spray & Wipe Disinfectant Products:
 - Clorox Healthcare®
 - Lysol®
 - PDI Products
 - Bleach, Ethanol, IPA, Quats, Citric Acid, & Hydrogen Peroxide, and Other Industrial-Grade Cleaners and Disinfectants





SEAL CLEAN™ WATERPROOF KEYBOARD

Model: SSKSV207, SSWKSV207, SSKSV207L, SSWKSV207L

TECHNICAL DATA:

Compatibility:	Windows® 10 Version 1803 x64
Construction:	ABS Plastic (Standard Style)
Net Dimensions L x W x H:	18.07 x 6.85 x 1.38 in (45.9 x 17.4 x 3.5 cm)
Key Layout:	104 US Language
Net Weight:	207: 1.93 lb (0.875 kg) 207L: 1.87 lb (0.850 kg)
Gross Weight:	207: 2.31 lb (1.050 kg) 207L: 2.26 lb (1.025 kg)
Cable Length:	SSKSV207L, SSWKSV207L: 6 ft.(1.83m) USB Extension Cable SSKSV207, SSWKSV207: 6in (15cm) Quick Connect Cable with 6 ft.(1.83m) USB Extension Cable
Connection Type:	Gold Plated USB (can support PS/2 technology)
Key Switch Force:	53 ± 7 gf
Key Switch Life Cycle:	Greater Than 10 Million Keystrokes
Key Switch Type:	Membrane Key Switch with Tactile Feedback
Keycaps Imaging Type:	Laser Etched
Total Key Travel:	4.0 ± 0.2mm
Operating Current:	60mA
Operating Voltage:	5VDC
Storage Temperature:	-5° - 140° F (-20° to 60° C)
EMI - RFI:	Conforms to FCC Rules for Class B Computing Device
Waterproof/Dustproof Ratings:	IPX8, NEMA 4X
Approvals/Certifications:	FCC, CE, RoHS, WEEE, WHQL, ICES-003, EAC, BIS KC, RCM, and cULus, REACH, Cal Prop 65



Copyright© 2024, Seal Shield, LLC. All rights reserved. All other trademarks and trade names are those of their respective owners.

Limited 2-Year Warranty