

HP ZBook Power 16 inch G11 Mobile Workstation PC (B4UF7UA)



Step up performance. Not size

Upgrade to professional ZBook performance and security at an unbelievably affordable price. Power up your productivity on this durable yet premium device—delivering enhanced collaboration features and pro-grade components to run pro software apps for CAD, 3D concepting, modeling, rendering and more.



Pro-certified power within reach

Blaze through 3D workloads with an integrated or discrete GPU,[1] Intel® CPU,[7] and large memory configurations.

Durable all-aluminum chassis

Designed to pass rigorous military standard testing[3] this PC is built to last with a distinctly premium touch.

Connect. Communicate. Collaborate

Collaborate effectively with ZBook Power. The 5MP camera,[1] Wi-Fi 6E,[8] and a long lasting battery[9] let you seamlessly connect

Featuring

Windows 11

Work anywhere without compromising on performance or security with Windows 11 powered by HP's collaboration and connectivity technology.

Intel® Core™ Ultra Processor

Unleash productivity with a new architecture that delivers power-efficient performance for complex business workloads and is purpose-built for the next era of AI software by sending the right task to the right engine at the right time. [10]

NVIDIA® Graphics

Power through projects with up to NVIDIA RTX™ 3000 Ada Generation Laptop GPU, certified for pro-apps.

HP Z Turbo Drive High-speed Storage

Work without limits in any location with local PCIe storage that's up to 6x faster than SATA SSD, and up to 21x faster than traditional HDD storage. [11]

Spill-resistant Keyboard

Accidents happen - which is why we designed our keyboard with a drain hole, so minor spills flow out the bottom for easy cleanup.

Specifications

Operating system	Windows 11 Pro
Processor family	Intel® Core™ Ultra 7 processor
Processor	Intel® Core™ Ultra 7 165H (up to 5.0 GHz with Intel® Turbo Boost Technology, 24 MB L3 cache, 16 cores, 22 threads) [6,7]
Chipset	Intel® integrated SoC
Memory	64 GB DDR5-5600 MT/s (2 x 32 GB)
Memory Slots	2 SODIMM; supports dual channel
Internal Storage	1 TB PCIe® Gen4 NVMe™ TLC M.2 SSD
Graphics	Discrete
Graphics (discrete)	NVIDIA RTX™ 3000 Ada Generation Laptop GPU (8 GB GDDR6 dedicated)
Graphics	Integrated
Graphics (integrated)	Intel® Arc™ Graphics
Display	40.6 cm (16") diagonal, WQXGA (2560 x 1600), IPS, anti-glare, Low Blue Light, 400 nits, 100% sRGB
Display	16" diagonal, WQXGA (2560 x 1600), IPS, anti-glare, Low Blue Light, 400 nits, 100% sRGB ^[21,22,23,24]
Display size (diagonal)	40.6 cm (16")
Display size (diagonal)	16"
Audio	Audio by Poly Studio, dual stereo speakers, HP World Facing Microphone dual array digital microphones, functions keys for volume up and down, combo microphone/headphone jack, HD audio
Minimum dimensions (W x D x H)	35.94 x 25.1 x 2.29 cm (Dimensions vary by configuration)
Minimum dimensions (W x D x H)	14.15 x 9.88 x 0.9 in (Dimensions vary by configuration)
Weight	Starting at 2.12 kg (Weight varies by configuration and components.)
Weight	Starting at 4.68 lb (Weight varies by configuration and components.)
Keyboard	Spill-resistant, backlit keyboard with numeric keypad
Pointing device	ClickPad Glass with multi-touch gesture support, taps enabled as default
Camera	5 MP IR camera
Ports	1 USB Type-A 5Gbps signaling rate (charging); 1 HDMI 2.1; 1 headphone/microphone combo; 1 power connector; 2 Thunderbolt™ 4 with USB Type-C® 40Gbps signaling rate (USB Power Delivery, DisplayPort™ 2.1)
Ports	1 USB Type-A 5Gbps signaling rate; 1 RJ-45; 1 SD 4.0 card reader; 1 nano security lock slot
Package dimensions (W x D x H)	552 x 69 x 345 mm
Wireless	Intel® Wi-Fi 6E AX211 (2x2) and Bluetooth® 5.3 wireless card, vPro®
Power	150 W external AC power adapter ^[20]
Battery type	HP Long Life 6-cell, 83 Wh Li-ion polymer
Ecolabels	TCO Certified
Energy star certified	ENERGY STAR® certified
Sustainable impact specifications	Low halogen; Bulk packaging available; External power supply 90% efficiency; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Outside box and corrugated cushions are 100% sustainably sourced and recyclable; 60% post-consumer recycled plastic
UPC number	198990036465

Top Recommended Displays, Accessories and Services

Series 7 Pro

HP Series 7 Pro 34 inch WQHD Conferencing Monitor - 734pm	8K157AA
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9AA
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk	8J9G2AA

Speakerphones

Poly Sync 20+ USB-C Speakerphone	772D0AA
Poly Sync 20 USB-C Speakerphone	7F0J7AA
Poly Sync 10 USB-A USB-C Speakerphone	772C3AA

Wireless Headset

Poly Voyager Focus 2 USB-C-C Headset +USB-C/A Adapter	9T9J3AA
---	---------

Wired Headset

Poly Blackwire 8225 Stereo USB-C Headset +USB-C/A Adapter	8X223AA
Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	8X231AA

Backpacks

HP Renew Business 17.3-inch Laptop Backpack	3E2U5AA
HP Renew Executive 16-inch Laptop Backpack	6B8Y1AA

Topload Bags

HP Renew Executive 16-inch Laptop Bag	6B8Y2AA
---------------------------------------	---------

Wireless Keyboards

HP 455 Programmable Wireless Keyboard	4R177AA
HP 475 Dual-Mode Wireless Keyboard	7N7B9AA
HP 975 Dual-Mode Wireless Keyboard	3Z726AA

Wireless Mice

HP 695 Rechargeable Wireless Mouse	8F1Y4AA
HP 935 Creator Wireless Mouse	1D0K8AA
HP 925 Ergonomic Vertical Mouse	6H1A5AA

Messaging Footnotes

[1] Optional feature that must be configured at purchase.

[3] AI Noise Suppression is delivered automatically through Windows update or can be downloaded from <https://support.hp.com/us-en/drivers>. Requires Windows 10 or higher, compatible with internal PC speakers, microphone and analog headsets. The AI Noise Suppression setting can be configured through the Application HP Audio Control.

[7] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[8] AI Noise Suppression is delivered automatically through Windows update or can be downloaded from <https://support.hp.com/us-en/drivers>. Requires Windows 10 or higher, compatible with internal PC speakers, microphone and analog headsets. The AI Noise Suppression setting can be configured through the Application HP Audio Control.

[9] Wi-Fi 6E is an optional feature that must be configured at purchase. Wi-Fi 6E requires a Wi-Fi 6E router, sold separately, to function in the 6GHz band. Availability of public wireless access points limited. Wi-Fi 6E is backwards compatible with prior 802.11 specs. Available in countries where Wi-Fi 6E is supported.

[10] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance. Optional feature that must be configured at purchase

[11] For hard drives, GB = 1 billion bytes. TB = 1 trillion bytes. Actual formatted capacity is less. Up to 30GB (for Windows 10) of system disk is reserved for system recovery software.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[20] 150 W power adapter is only available with discrete graphic options.

[21] QHD content required to view QHD images.

[22] HP Sure View Reflect integrated privacy screen is an optional feature that must be configured at purchase and is designed to function in landscape orientation.

[23] Resolutions are dependent upon monitor capability, and resolution and color depth settings.

[24] Actual brightness will be lower with HP Sure View or touch-screen.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Core, Iris, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD, and Radeon are trademarks of Advanced Micro Devices, Inc. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

