

# Eaton 93PX

## 208V rackmount 3-phase UPS




### Simple, reliable, cost-effective power for edge and data center applications

- Innovative quick-connect design for easy plug-and-play deployment and service
- Unity power factor (1.0) with 5, 7.5, 13, 15 or 20 kW capacity
- High power density with up to 7.5 kW in 9U and up to 20 kW in 12U
- Up to 92% energy efficiency (97% in ECO mode)
- Network management cards with market-leading cybersecurity
- Configurable in parallel for N+1 redundancy (13, 15 or 20 kW)
- Auto-restart after extended utility outage
- Online, double-conversion UPS
- Backfeed and surge protection
- TAA compliant




*Powering Business Worldwide*

# Feature focus



Front of 5 and 7.5 kW UPS (9U)

Back of 5 kW UPS  
(7.5 kW UPS is similar, but with  
30A input/output instead of 20A.)



Front of 13, 15 and 20 kW UPS (12U)

Back of 13 and 15 kW UPS  
(20 kW UPS is similar, but with hardwired input.  
Hardwired input and output are also available  
for 13, 15 and 20 kW UPS systems.)

13, 15 and 20 kW UPS  
models are also available  
in parallel bundles (not  
shown) that support  
N+1 redundancy.

- 1 3U quick-connect power module (PM)**  
5, 7.5, 13, 15 or 20 kW capacity. The power module connects to the MBP with included cabling (not shown).
- 2 3U quick-connect maintenance bypass panel (MBP)**  
Parallel MBPs are also available for configuring dual 13, 15 or 20 kW UPS systems for N+1 redundancy.
- 3 3U quick-connect extended battery module (EBM)**  
5 and 7.5 kW models include one EBM. 13, 15 and 20 kW models include two EBMs.
- 4 LCD control panel**  
3.5-inch (89 mm) color touchscreen with multi-language display.
- 5 AC input options (via MBP)**  
5 kW: L21-20P plug with 10-foot cord. 7.5 kW: L21-30P plug with 10-foot cord. 13-15 kW: IEC 309 60A plug with 10-foot cord or hardwired. 20 kW: hardwired only.

- 6 AC output options (via MBP)**  
(Corded output connects directly to rack PDU input cords.)  
5 kW: (2) L21-20R receptacles with 2-foot cord. 7.5 kW: (2) L21-30R receptacles with 2-foot cord. 13-20 kW: (2) IEC 309 60A receptacles with 2-foot cord or hardwired.
- 7 Cybersecure network management card (NMC)**  
Network management card supports Web/SNMP (NETWORK-M3) or Modbus/Web/SNMP/BACnet (INDGW-M3) protocols.
- 8 Communication ports (RS-232, USB, EPO)**
- 9 Quick-connect ports for PM/MBP connection**  
The power module and MBP connect to each other with included cabling (not shown).
- 10 EBM connectors**  
The power module connects to the EBM(s) with included cabling.

# Ordering information

## 93PX 208V UPS bundles

Standard UPS bundles include 3U power module (PM) with network management card (NMC), 3U maintenance bypass panel (MBP) and one or two 3U extended battery modules (EBMs). 5–7.5 kW models include one EBM. 13–20 kW models include two EBMs. Parallel bundles (“PAR” suffix) support N+1 redundancy and include twice as many PMs, NMCs and EBMs as the standard bundles, combined with a 3U parallel MBP.

| Catalog number  | Capacity    | MBP input connection                       | MBP output connection(s)                             | Rack size | Network card   |
|-----------------|-------------|--------------------------------------------|------------------------------------------------------|-----------|----------------|
| 93PX20K         | 20 kW       | Hardwired                                  | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 12U       | NETWORK-M3     |
| 93PX20KIND      | 20 kW       | Hardwired                                  | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 12U       | INDGW-M3       |
| 93PX20KINDPAR   | 20 kW (N+1) | Hardwired                                  | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 21U       | (2) INDGW-M3   |
| 93PX20KHW       | 20 kW       | Hardwired                                  | Hardwired (5-wire)                                   | 12U       | NETWORK-M3     |
| 93PX20KHWP      | 20 kW (N+1) | Hardwired                                  | Hardwired (5-wire)                                   | 21U       | (2) NETWORK-M3 |
| 93PX20KHWIND    | 20 kW       | Hardwired                                  | Hardwired (5-wire)                                   | 12U       | INDGW-M3       |
| 93PX20KHWINDPAR | 20 kW (N+1) | Hardwired                                  | Hardwired (5-wire)                                   | 21U       | (2) INDGW-M3   |
| 93PX15K         | 15 kW       | IEC 309 60A (5-wire) plug with 10 ft. cord | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 12U       | NETWORK-M3     |
| 93PX15KIND      | 15 kW       | IEC 309 60A (5-wire) plug with 10 ft. cord | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 12U       | INDGW-M3       |
| 93PX15KINDPAR   | 15 kW (N+1) | IEC 309 60A (5-wire) plug with 10 ft. cord | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 21U       | (2) INDGW-M3   |
| 93PX15KHW       | 15 kW       | Hardwired                                  | Hardwired (5-wire)                                   | 12U       | NETWORK-M3     |
| 93PX15KHWP      | 15 kW (N+1) | Hardwired                                  | Hardwired (5-wire)                                   | 21U       | (2) NETWORK-M3 |
| 93PX15KHWIND    | 15 kW       | Hardwired                                  | Hardwired (5-wire)                                   | 12U       | INDGW-M3       |
| 93PX15KHWINDPAR | 15 kW (N+1) | Hardwired                                  | Hardwired (5-wire)                                   | 21U       | (2) INDGW-M3   |
| 93PX13K         | 13 kW       | IEC 309 60A (5-wire) plug with 10 ft. cord | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 12U       | NETWORK-M3     |
| 93PX13KIND      | 13 kW       | IEC 309 60A (5-wire) plug with 10 ft. cord | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 12U       | INDGW-M3       |
| 93PX13KINDPAR   | 13 kW (N+1) | IEC 309 60A (5-wire) plug with 10 ft. cord | (2) IEC 309 60A (4-wire) receptacles with 2 ft. cord | 21U       | (2) INDGW-M3   |
| 93PX13KHW       | 13 kW       | Hardwired                                  | Hardwired (5-wire)                                   | 12U       | NETWORK-M3     |
| 93PX13KHWP      | 13 kW (N+1) | Hardwired                                  | Hardwired (5-wire)                                   | 21U       | (2) NETWORK-M3 |
| 93PX13KHWIND    | 13 kW       | Hardwired                                  | Hardwired (5-wire)                                   | 12U       | INDGW-M3       |
| 93PX13KHWINDPAR | 13 kW (N+1) | Hardwired                                  | Hardwired (5-wire)                                   | 21U       | (2) INDGW-M3   |
| 93PX8K          | 7.5 kW      | L21-30P plug with 10 ft. cord              | (2) L21-30R receptacles with 2 ft. cord              | 9U        | NETWORK-M3     |
| 93PX8KIND       | 7.5 kW      | L21-30P plug with 10 ft. cord              | (2) L21-30R receptacles with 2 ft. cord              | 9U        | INDGW-M3       |
| 93PX5K          | 5 kW        | L21-20P plug with 10 ft. cord              | (2) L21-20R receptacles with 2 ft. cord              | 9U        | NETWORK-M3     |
| 93PX5KIND       | 5 kW        | L21-20P plug with 10 ft. cord              | (2) L21-20R receptacles with 2 ft. cord              | 9U        | INDGW-M3       |

## Accessories

| Catalog number | Description                                                                                                                                                                                                                                                                                   |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 93PXEBM240     | Extended battery module (EBM) for 93PX UPS systems, 3U. Minimum quantity: 1 EBM for 5–7.5 kW UPS; 2 EBMs for 13–20 kW non-parallel UPS; 4 EBMs for 13–20 kW parallel UPS. Maximum quantity: 5 EBMs for 5–7.5 kW UPS; 5 EBMs for 13–20 kW non-parallel UPS; 10 EBMs for 13–20 kW parallel UPS. |
| NETWORK-M3     | Network management card with SNMP/Web communications and certified cybersecurity. Included with select UPS bundles.                                                                                                                                                                           |
| INDGW-M3       | Industrial network management card with Modbus/SNMP/Web/BACnet communications and certified cybersecurity. Included with select UPS bundles.                                                                                                                                                  |
| EM PDT1H1C2    | Environmental monitoring probe with temperature, humidity and dry contact monitoring. Requires NETWORK-M3 or INDGW-M3. Connect up to 3 per card.                                                                                                                                              |

# Comprehensive data center solutions

From edge to data center, Eaton provides a single source for all the products, services and support you need for your IT infrastructure. See page 7 for a selection of Eaton rack PDUs and rack enclosures compatible with 93PX 208V UPS systems.

Additional solutions include KVM switches, console servers, network cables, power cords, cable management, cooling, aisle containment, busway systems, software and services.

**Learn more at [Eaton.com/DataCenter](https://www.eaton.com/DataCenter)**

# Simplified fleet management

Every 93PX UPS comes with a cybersecure network card, allowing you to monitor and manage your UPS fleet remotely for greater convenience and peace of mind.

For smaller environments, you can connect to UPS systems using a web browser and receive email alerts. For larger deployments across multiple locations, 93PX UPS systems integrate smoothly via SNMP with digital solutions from our **Brightlayer Data Centers suite**.



**Brightlayer**  
Data Centers suite

**Distributed IT Performance Management (DITPM) software** helps you remotely monitor and control up to thousands of UPS systems and PDUs at remote sites.

- Know what's happening with real-time reports, trend charts, dashboards and alerts prioritized by severity.
- Troubleshoot and resolve issues more quickly.
- Remotely control load segments regardless of vendor.
- Update firmware remotely to improve cybersecurity.
- Leverage integrations with virtualization platform leaders.
- Gracefully shut down IT equipment in your required order.

Learn more at [Eaton.com/DITPM](https://Eaton.com/DITPM)



Remote power management dashboard from DITPM software.

**Data Center Performance Management (DCPM) software** helps you manage power, space, connectivity and cooling to maximize uptime while minimizing capital and operating costs.

- Gain efficiencies and reduce costs with real-time data and automated alerts.
- View 2D and 3D visualizations and automated reports.
- Gain near-real-time visibility into key performance indicators.
- Integrate with other software, such as building management systems, to improve efficiency, productivity, data accuracy, decision-making and cost savings.

Learn more at [Eaton.com/DCPM](https://Eaton.com/DCPM)




Data center thermal map from DCPM software.

Our **Remote Monitoring Service**, also known as PredictPulse™, provides 24/7 remote monitoring and predictive analytics to forecast failures before issues arise and dispatches field service technicians when needed.

- Know about future component failures before they happen.
- Gain fast response and repairs from Eaton technicians.
- Access real-time health trends, alarms and outages prevented.

Learn more at [Eaton.com/RemoteMonitoringService](https://Eaton.com/RemoteMonitoringService)



Battery notification from Remote Monitoring Service.

# Certified cybersecurity

The included network management card complies with UL and IEC cybersecurity standards and provides industry-leading security and automation features.

## Zero-trust architecture

- Minimizes cybersecurity vulnerabilities through hardware root of trust, enabling secure boot and complete chain of trust with private hardware key encryption.

## Zero-touch provisioning

- Automatically configures equipment to save time and reduce errors in large-scale deployments.

## User-configurable firewall

- Reduces your organization's attackable surface area.
- Helps meet network/security compliance requirements.
- Supports IP white list.

## RESTful API

- Allows you to easily integrate networked UPS systems with native systems and automate M2M interactions.

## Secure access via web browser or SNMP

- Access UPS systems using the secure web browser interface or integrate with a network management system via SNMP.



For more information, download our cybersecurity solutions brief (PDF).

# Ready for virtualization, hyperconverged infrastructure and generative AI

Brightlayer software enables seamless integration and intelligent coordination with virtualized, hyperconverged and generative AI infrastructures. Support for complex orchestrations during blackouts and other power events allows you to extend runtime, preserve data and gracefully shut down or migrate servers per your preferences.

Eaton is the leader in power management for virtualization platforms and has more than 500 hours invested in testing with alliance partners like Cisco, Dell, HPE, NetApp, Nutanix, Scale Computing and VMware.

Learn more at [Eaton.com/alliances](https://Eaton.com/alliances)



# Quick and easy deployment and service

Eaton's 93PX UPS has an innovative quick-connect design for easy plug-and-play deployment and service.



Simply connect the rack PDU's AC input plug to the AC output receptacle of the UPS.

(13–20 kW UPS systems offer 4-wire IEC 309 60A output receptacles or 5-wire hardwired output, depending on the model selected.)

## Plug-and-play UPS system

- Interconnections between the UPS power module, the maintenance bypass panel and the extended battery module(s) provide easy plug-and-play setup and serviceability.

## Quick AC input connection

- 5–15 kW UPS systems can be configured with corded AC input for easy power connection.
- 13–20 kW UPS systems are also available with hardwired input.

## Quick AC output connection to rack PDUs

- All UPS systems can be configured with corded AC output receptacles, allowing you to simply plug compatible rack PDUs into the UPS.
- 13–20 kW UPS systems are also available with hardwired output.

## From unboxing to connection in a few easy steps

1. Mount the UPS modules in a standard 19-inch rack using the included hardware.
2. Connect the UPS modules together with the included cables.
3. For corded input UPS systems, plug the UPS into the utility outlet with the input power cord on the back of the maintenance bypass panel.
4. For corded output UPS systems, plug your rack PDUs into the corded AC output receptacles on the back of the maintenance bypass panel. (See page 7 for compatible Eaton rack PDU options.)

# Key applications

## High-density IT infrastructure

- Eaton's 93PX provides up to 20 kW of critical backup power for high-density applications.
- Mounts in a standard 19-inch IT rack or rack enclosure.
- Small rack footprint and high power density save valuable data center white space.
- Allows IT managers to monitor and control power in distributed and edge deployments.
- Included network management card provides best-in-class cybersecurity.
- Provides up to 97% efficiency in ECO mode to reduce energy consumption and operating costs.



## Commercial buildings and industrial facilities

- Can be deployed outside data center environments and supports challenging loads.
- Select bundles include an industrial gateway card {INDGW-M3} to support key commercial/ industrial protocols like Modbus, BACnet and SNMP.



## Healthcare

- Compact footprint saves space in cramped hospitals, clinics and other medical facilities.
- Adapts to rack or standalone installation, making it adaptable to different healthcare setups.
- Online double-conversion operation with pure sine wave power and zero transfer time supports medical devices requiring the highest power quality, stability and reliability.



# Complete your solution with Eaton

## Eaton rack PDUs

**Basic PDUs** provide reliable power distribution with branch circuit protection. **Metered input PDUs** include remote management with bank-level monitoring. **Metered outlet PDUs** include remote management with outlet-level monitoring. **Managed PDUs** are our most advanced rack PDUs and include remote management with outlet-level monitoring and control. PDUs shown below are vertical PDUs (0U), except EMIU29-06 (2U horizontal).

| UPS bundle                   | Compatible managed PDUs                                                                                                                                                                                      | Compatible metered outlet PDUs                                                                                                                                                                                                          | Compatible metered input PDUs                                                                                                                                                                    | Compatible basic PDUs                                                                                                      |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| 93PX20K <sup>1</sup>         | EVMA4609X <sup>4</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMAGU23X <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39) | EVMOGU23A-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 12xC13, 12xC39)<br>EVMOGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39) | EMIU29-06 <sup>7</sup> (17.3 kW; 6xL6-30R; 2U)<br>EVM4609X <sup>4</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMIGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)                 | EVBAGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)                                                |
| 93PX20KIND <sup>1</sup>      |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX20KINDPAR <sup>1</sup>   |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX20KHW <sup>2</sup>       | EVMAGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                                                             | EVMOGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMOGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                        | EVMIGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMIGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)<br>EVMIGU23X <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39) | EVBAGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                                             |
| 93PX20KHWPAR <sup>2</sup>    |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX20KHWIND <sup>2</sup>    |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX20KHWINDPAR <sup>2</sup> |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX15K <sup>3</sup>         | EVMA4609X <sup>4</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMAGU23X <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39) | EVMOGU23A-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 12xC13, 12xC39)<br>EVMOGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39) | EMIU29-06 <sup>7</sup> (17.3 kW; 6xL6-30R; 2U)<br>EVM4609X <sup>4</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMIGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)                 | EVBAGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)                                                |
| 93PX15KIND <sup>3</sup>      |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX15KINDPAR <sup>3</sup>   |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX15KHW <sup>2</sup>       | EVMAGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                                                             | EVMOGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMOGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                        | EVMIGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMIGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)<br>EVMIGU23X <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39) | EVBAGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                                             |
| 93PX15KHWPAR <sup>2</sup>    |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX15KHWIND <sup>2</sup>    |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX15KHWINDPAR <sup>2</sup> |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX13K <sup>3</sup>         | EVMA4609X <sup>4</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMAGU23X <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39) | EVMOGU23A-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 12xC13, 12xC39)<br>EVMOGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39) | EMIU29-06 <sup>7</sup> (17.3 kW; 6xL6-30R; 2U)<br>EVM4609X <sup>4</sup> (17.3 kW; 24xC13, 18xC39)<br>EVMIGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)                 | EVBAGU23X-E <sup>5</sup> + CBL356-10 <sup>6</sup> (17.3 kW; 24xC13, 18xC39)                                                |
| 93PX13KIND <sup>3</sup>      |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX13KINDPAR <sup>3</sup>   |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX13KHW <sup>2</sup>       | EVMAGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                                                             | EVMOGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMOGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                        | EVMIGU23A-E <sup>5</sup> + CBL357-10 (17.3 kW; 12xC13, 12xC39)<br>EVMIGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)<br>EVMIGU23X <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39) | EVBAGU23X-E <sup>5</sup> + CBL357-10 (17.3 kW; 24xC13, 18xC39)                                                             |
| 93PX13KHWPAR <sup>2</sup>    |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX13KHWIND <sup>2</sup>    |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX13KHWINDPAR <sup>2</sup> |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX8K <sup>3</sup>          | EVMA2130X (8.6 kW; 24xC13, 18xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL351-10 (8.6 kW; 24xC13, 18xC39)<br>EVMAGU23X <sup>5</sup> + CBL351-10 (8.6 kW; 24xC13, 18xC39)                                           | EMOCPD36JEY2K3 <sup>7</sup> (8.6 kW; 21xC13, 12x5-20R)<br>EVMOGU23X-E <sup>5</sup> + CBL351-10 (8.6 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL351-10 (8.6 kW; 24xC13, 18xC39)                                                  | EVM12130X (8.6 kW; 24xC13, 18xC39)<br>EVMIGU23X-E <sup>5</sup> + CBL351-10 (8.6 kW; 24xC13, 18xC39)<br>EVMIGU23X <sup>5</sup> + CBL351-10 (8.6 kW; 24xC13, 18xC39)                               | PDU3V6L2130 <sup>7</sup> (8.6 kW; 36xC13, 6xC19, 6x5-20R)<br>EVBAGU23X-E <sup>5</sup> + CBL351-10 (8.6 kW; 24xC13, 18xC39) |
| 93PX8KIND <sup>3</sup>       |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
|                              |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
| 93PX5K <sup>3</sup>          | EVMA2120A (5.8 kW; 12xC13, 12xC39)<br>EVMAGU23X-E <sup>5</sup> + CBL367-10 (5.8 kW; 24xC13, 18xC39)<br>EVMAGU23X <sup>5</sup> + CBL367-10 (5.8 kW; 24xC13, 18xC39)                                           | EMOCPB36JZY2K3 <sup>7</sup> (5.8 kW; 15xC13, 12x5-20R)<br>EVMOGU23X-E <sup>5</sup> + CBL367-10 (5.8 kW; 24xC13, 18xC39)<br>EVMOGU23X <sup>5</sup> + CBL367-10 (5.8 kW; 24xC13, 18xC39)                                                  | EMI18-10 (5.8 kW; 30xC13, 6xC19, 3x5-20R)<br>EVMIGU23X-E <sup>5</sup> + CBL367-10 (5.8 kW; 24xC13, 18xC39)<br>EVMIGU23X <sup>5</sup> + CBL367-10 (5.8 kW; 24xC13, 18xC39)                        | PDU3V6L2120LV <sup>7</sup> (5.7 kW; 42x5-20R)<br>EVBAGU23X-E <sup>5</sup> + CBL367-10 (5.8 kW; 24xC13, 18xC39)             |
| 93PX5KIND <sup>3</sup>       |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |
|                              |                                                                                                                                                                                                              |                                                                                                                                                                                                                                         |                                                                                                                                                                                                  |                                                                                                                            |

**C39 outlets:** Flexible C39 outlets combine the functionality of C13 and C19 outlets. **Input power cord length:** 10 ft. unless noted. **Other notes:** (1) UPS with hardwired input and corded output. (2) UPS with hardwired input and output. (3) UPS with corded input and output. (4) Add “-06” to model number for 6 ft. input power cord. (5) Universal-input PDU (UPDU) compatible with variety of interchangeable input power cords. Capacity is 5–23 kW, depending on input power cord. UPDUs ending with “-E” have end-entry input cord connection. Others have front-entry (perpendicular) connection. (6) Change “-10” to “-06” in cord model number for 6 ft. input power cord. (7) Includes 6 ft. input power cord.



Don't see the PDU you need? Find more at [RackPDUselector.Eaton.com](https://RackPDUselector.Eaton.com)

## Eaton rack enclosures

Eaton 93PX 208V UPS systems are compatible with standard EIA 19-inch rack enclosures with a maximum device depth of at least 37 inches (940 mm).

| Catalog number | Type               | Height | Width             | Maximum device depth | Weight capacity (Static/dynamic) | Color |
|----------------|--------------------|--------|-------------------|----------------------|----------------------------------|-------|
| SR25UB         | Standard           | 25U    | 23.6 in. (600 mm) | 37 in. (940 mm)      | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR42UB         | Standard           | 42U    | 23.6 in. (600 mm) | 37 in. (940 mm)      | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR42UBDP       | Standard deep      | 42U    | 23.6 in. (600 mm) | 42 in. (1067 mm)     | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR42UBDPWD8    | Standard deep/wide | 42U    | 31.5 in. (800 mm) | 44 in. (1118 mm)     | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR42UBEIS      | Industrial         | 42U    | 23.6 in. (600 mm) | 37 in. (940 mm)      | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR42UBZ4       | Seismic            | 42U    | 23.6 in. (600 mm) | 37 in. (940 mm)      | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR45UB         | Standard           | 45U    | 23.6 in. (600 mm) | 37 in. (940 mm)      | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR45UBDP       | Standard deep      | 45U    | 23.6 in. (600 mm) | 42 in. (1067 mm)     | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR48UB         | Standard           | 48U    | 23.6 in. (600 mm) | 37 in. (940 mm)      | 3500/2250 lb. (1588/1021 kg)     | Black |
| SR48UBDP       | Standard deep      | 48U    | 23.6 in. (600 mm) | 42 in. (1067 mm)     | 3500/2250 lb. (1588/1021 kg)     | Black |



Don't see the rack you need? Find more at [TrippLite.Eaton.com/racks](https://TrippLite.Eaton.com/racks)

## Eaton 93PX 208V UPS technical specifications (preliminary)

| Power rating   | 5 kW                                     | 7.5 kW | 13 kW                                                                                                      | 15 kW | 20 kW |
|----------------|------------------------------------------|--------|------------------------------------------------------------------------------------------------------------|-------|-------|
| Phase (in/out) | 3-phase, 4W + ground<br>(Wye in/Wye out) |        | Hardwired output: 3-phase, 4W + ground<br>(Wye in/Wye out); Corded output: 3-phase,<br>3W + ground (Delta) |       |       |

### Input characteristics

|                                  |                                                                |                         |                                            |     |           |
|----------------------------------|----------------------------------------------------------------|-------------------------|--------------------------------------------|-----|-----------|
| Nominal voltage                  | 208 VAC (Ph-Ph)/120 VAC (Ph-N)                                 |                         |                                            |     |           |
| Input voltage range              | 121–270 VAC (Ph-Ph) @ 50% load; 161–53 VAC (Ph-Ph) @ 100% load |                         |                                            |     |           |
| Frequency range                  | 50/60 Hz ± 4 Hz in line mode, auto-sensing                     |                         |                                            |     |           |
| Nominal input current            | 16A                                                            | 24A                     | 48A                                        | 48A | 71A       |
| Backfeed protection              | Yes                                                            |                         |                                            |     |           |
| Power factor                     | > 0.99 @ 100% R/RCD load, 208 VAC (Ph-Ph)                      |                         |                                            |     |           |
| Input harmonic distortion (THDi) | < 4% @ full linear load                                        |                         |                                            |     |           |
| AC input connection (via MBP)    | L21-20P,<br>10 ft. cord                                        | L21-30P,<br>10 ft. cord | IEC 309 60A,<br>10 ft. cord (or hardwired) |     | Hardwired |

### Output characteristics

|                               |                                                                                        |                            |                                              |       |       |
|-------------------------------|----------------------------------------------------------------------------------------|----------------------------|----------------------------------------------|-------|-------|
| Power factor                  | 1.0                                                                                    |                            |                                              |       |       |
| Output voltage                | 208 VAC (Ph-Ph)/120 VAC (Ph-N)                                                         |                            |                                              |       |       |
| Voltage regulation            | ± 1%                                                                                   |                            |                                              |       |       |
| Output frequency              | 50/60 Hz, 60 Hz default                                                                |                            |                                              |       |       |
| Frequency regulation          | ± 0.1 Hz                                                                               |                            |                                              |       |       |
| Nominal output current        | 13.9A                                                                                  | 20.9A                      | 36.2A                                        | 41.7A | 55.6A |
| Current crest ratio (maximum) | 3:1                                                                                    |                            |                                              |       |       |
| Harmonic distortion (THDv)    | ≤ 2% (linear load), ≤ 5% (non-linear load)                                             |                            |                                              |       |       |
| Transfer time                 | AC to battery mode: zero; Inverter to bypass: zero                                     |                            |                                              |       |       |
| Waveform (battery mode)       | Pure sine wave                                                                         |                            |                                              |       |       |
| Overload (AC mode)            | 102–110% for 60 min.; 110–125% for 10 min.;<br>125–150% for 1 min.; ≥150% for 0.4 sec. |                            |                                              |       |       |
| Overload (battery mode)       | 100–110% for 60 min.; 110–125% for 10 min.;<br>125–150% for 1 min.; ≥150% for 0.4 sec. |                            |                                              |       |       |
| Overload (bypass mode)        | 100–130% continuously; ≥130% for 1 min.                                                |                            |                                              |       |       |
| Output connections (via MBP)  | (2) L21-20R,<br>2 ft. cord                                                             | (2) L21-30R,<br>2 ft. cord | (2) IEC 309 60A, 2 ft. cord<br>or hardwired  |       |       |
| Parallel configuration        | Not available                                                                          |                            | 2 power modules parallel for redundancy only |       |       |

### Battery and charger

|                                             |                                               |                     |                                                               |                                               |                                               |
|---------------------------------------------|-----------------------------------------------|---------------------|---------------------------------------------------------------|-----------------------------------------------|-----------------------------------------------|
| DC voltage                                  | ± 120 VDC                                     |                     |                                                               |                                               |                                               |
| Battery quantity per module (EBM)           | 20 pcs (10 Ah) per EBM                        |                     |                                                               |                                               |                                               |
| Charger current                             | 2–10A, user-adjustable<br>(2A default)        |                     | 2–10A, user-adjustable<br>(4A default)                        |                                               |                                               |
| Minimum battery modules (EBMs)              | 1 EBM                                         |                     | 2 EBMs                                                        |                                               |                                               |
| Maximum battery modules (EBMs)              | 5 EBMs                                        |                     | 5 EBMs (10 EBMs for parallel bundles,<br>with 5 EBMs per UPS) |                                               |                                               |
| Float voltage                               | ± 13.65V/pc                                   |                     |                                                               |                                               |                                               |
| Max charging voltage                        | ± 14.1V/pc                                    |                     |                                                               |                                               |                                               |
| Charger temperature compensation            | ± 3 mV/°C/cell                                |                     |                                                               |                                               |                                               |
| Low voltage cutoff/<br>shutdown             | 10.7V/pc                                      |                     |                                                               |                                               |                                               |
| Estimated backup runtime<br>(100%/50% load) | 1 EBM:<br>13/31 min.                          | 1 EBM:<br>7/18 min. | 2 EBMs:<br>10/26 min.<br>4 EBMs:<br>23/53 min.                | 2 EBMs:<br>8/20 min.<br>4 EBMs:<br>19/45 min. | 2 EBMs:<br>5/13 min.<br>4 EBMs:<br>13/32 min. |
| Battery charger                             | Advanced 3-stage smart charger                |                     |                                                               |                                               |                                               |
| Recharge time to 90%                        | ≤ 5.4 hr.<br>(1 EBM)                          |                     | ≤ 5.2 hr.<br>(2 EBMs)                                         | ≤ 5.0 hr.<br>(2 EBMs)                         | ≤ 4.8 hr.<br>(2 EBMs)                         |
| Battery type                                | VRLA, 10 Ah                                   |                     |                                                               |                                               |                                               |
| EBM connection cables                       | Quick-connect cables with Anderson connectors |                     |                                                               |                                               |                                               |

| Efficiency                   | 5 kW          | 7.5 kW | 13 kW | 15 kW | 20 kW |
|------------------------------|---------------|--------|-------|-------|-------|
| Online mode (50%/100% load)  | ≥ 92% / ≥ 91% |        |       |       |       |
| ECO mode (50%/100% load)     | ≥ 96% / ≥ 97% |        |       |       |       |
| Battery mode (50%/100% load) | ≥ 92% / ≥ 91% |        |       |       |       |

### Dimensions

|                                      |                                                                        |                   |                                                                          |                     |                     |
|--------------------------------------|------------------------------------------------------------------------|-------------------|--------------------------------------------------------------------------|---------------------|---------------------|
| Power module unit dimensions (DxWxH) | 31.7 x 17.2 x 5.2 in. (806.3 x 438 x 131 mm)<br>3U rack size           |                   |                                                                          |                     |                     |
| Power module unit weight             | 68.3 lb.<br>(31 kg)                                                    | 77 lb.<br>(35 kg) | 79.4 lb.<br>(36 kg)                                                      | 79.4 lb.<br>(36 kg) | 81.6 lb.<br>(37 kg) |
| EBM unit dimensions (DxWxH)          | 1 EBM: 30.8 x 17.2 x 5.2 in.<br>(781.5 x 438 x 131 mm)<br>3U rack size |                   | 2 EBMs: 30.8 x 17.2 x 10.3 in.<br>(781.5 x 438 x 262 mm)<br>6U rack size |                     |                     |
| EBM unit weight                      | 1 EBM: 161 lb. (73 kg)                                                 |                   | 2 EBMs: 322 lb. (146 kg)                                                 |                     |                     |

### Environment

|                       |                                                                                                  |         |         |         |         |
|-----------------------|--------------------------------------------------------------------------------------------------|---------|---------|---------|---------|
| Operating temperature | 32 to 104°F (0 to 40°C)                                                                          |         |         |         |         |
| Storage temperature   | PM and MBP: 5 to 140°F (-15 to 60°C); EBM: 5 to 104°F (-15 to 40°C)                              |         |         |         |         |
| Relative humidity     | < 95% (non-condensing)                                                                           |         |         |         |         |
| Operating altitude    | No derating up to 3280 ft. (1000 m);<br>1% derating per 328 ft. (1000 m) above 3280 ft. (1000 m) |         |         |         |         |
| Noise level @ 1 m     | < 60 dB                                                                                          | < 62 dB | < 60 dB | < 60 dB | < 70 dB |

### Management

|                                                                       |                                                                                                                                                                              |
|-----------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Control panel                                                         | 3.5-inch (89 mm) color LCD touchscreen with multi-language display (English, Spanish, French)                                                                                |
| Network management card (included with select UPS bundles)            | NETWORK-M3 (SNMP/Web and UL/IEC certified cybersecurity.)                                                                                                                    |
| Industrial network management card (included with select UPS bundles) | INDGW-M3 (Modbus/SNMP/Web/BA/Cnet and UL/IEC certified cybersecurity.)                                                                                                       |
| Environmental monitoring probe (optional)                             | EMPDT1H1C2 (Provides temperature, humidity and dry contact monitoring. Supports daisy-chaining up to three probes. Requires NETWORK-M3 or INDGW-M3 network management card.) |
| Other ports                                                           | RS-232, USB and EPO                                                                                                                                                          |

### Approvals

|                                |                                                                                      |
|--------------------------------|--------------------------------------------------------------------------------------|
| Safety (USA and Canada)        | UL1778:2014 (5th Ed) R4-28-2023, CAN/CSA-C22.2 No. 107.3-14 (3rd Ed)+G11 (R:2017-10) |
| FCC/ICES                       | Class A; 47 CFR FCC Part 15 Subpart B; ICES-003 Issue 7                              |
| Safety (international)         | IEC62040-1:2017+A1:2021+A2:2022                                                      |
| EMI/EMC                        | EN61000-3-12:2011; IEC62040-2:2016                                                   |
| Surge protection               | IEC/EN-61000-4-5                                                                     |
| Vibration, shock, drop testing | According to ISTA standards                                                          |
| Other                          | TAA compliant; RoHS compliant                                                        |

### Warranty

|                                 |                           |
|---------------------------------|---------------------------|
| Limited product warranty period | 2 years (U.S. and Canada) |
|---------------------------------|---------------------------|

Each UPS system includes a power module (PM), maintenance bypass panel (MBP) and one or two extended battery modules (EBMs). Due to continuing improvements, specifications are subject to change without notice.

For more information, please call  
Eaton at 773-869-1236 or email  
[CPDISalesEngineering@Eaton.com](mailto:CPDISalesEngineering@Eaton.com)