



Height-Adjustable TV Mount Stand

Holds One 32" to 65" TV up to 45 kg (100 lbs.), Tempered Glass Base, Ideal for Placement on TV Consoles, Black

Part No.: [462297](#)

EAN-13: 0766623462297 | UPC: 766623462297

This Table Top TV Stand brings your TV to new heights without ever scratching a wall

The Manhattan Height-Adjustable TV Mount Stand offers a superior TV-viewing experience without having to drill holes in the wall. If you didn't want to risk an insecure installation or can't alter your wall's surface, this TV stand gives you the option to make better TV possible.

Sleek style and strength

A heavy-duty steel construction universally fits 32" to 65" TVs with VESA mount patterns up to 600x400. This Table Top TV Stand is strength-tested to support loads up to 45 kg (100 lbs.) and offers height adjustability to two levels: 485 and 535 mm (19 and 21 in.). The black tempered-glass base creates a solid, stylish-looking stand that's ideal for placing soundbars, set-top boxes or other accessories, all while fitting snugly against a wall.

Clever cable management

To organize your TV's HDMI, Ethernet and power cables, this mount lets you run them through the clip on the back. This smart cable management helps create a cleaner look and reduces potential trip hazards.

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.

Features:



- Free-standing mount for one 32" to 65" TV up to 45 kg (100 lbs.), ideal for placement on TV consoles
- Height-adjustable at two levels: 485 and 535 mm (19 and 21 in.)
- Base area with 600 mm width and 280 mm depth (23.6 x 11 in.), great for placing soundbars, streaming boxes, or other accessories
- Sleek design for a snug fit on a wall - the benefits of a wall mount without drilling holes
- Heavy-duty steel construction with powder coating
- Black tempered-glass base for a solid stand and stylish look
- Cable management with attachable clips on pole for a clean and organized look
- Rubber feet to prevent slipping and to protect your surface from scratches
- Easy and quick installation, all hardware included
- Meets VESA standards: 100x100, 200x100, 400x100, 200x200, 300x200, 400x200, 300x300, 400x300, 400x400, 600x400
- Lifetime warranty

Specifications:**General**

- Certifications: RoHS
- Designed for most 32" - 65" flat and curved screens
- Weight capacity: 45 kg (100 lbs.)
- Total dimensions (L x W x H): 735 x 660 x 280 mm (28.94 x 25.98 x 2.09 in.)
- Base dimensions: (L x W x H): 280 x 600 x 8 mm (11 x 22.6 x 0.3 in.)
- Net weight: 6.35 kg (14 lbs.)
- Gross weight: 7.45 g (16.42 lbs.)
- Material: steel and tempered glass
- VESA standards: 100x100, 200x100, 400x100, 200x200, 300x200, 400x200, 300x300, 400x300, 400x400, 600x400

Package Contents

- Height-Adjustable TV Mount Stand
- Installation hardware with instructions



2 Height Options



