

## PERFORMANCE

### Processor

Intel® Core™ Ultra 5 225T, 10C (6P + 4E) / 10T, Max Turbo up to 4.9GHz, 20MB

### AI PC Category<sup>[1]</sup>

AI PC

### NPU

Integrated Intel® AI Boost, up to 13 TOPS

### Graphics

Integrated Intel® Graphics

### Chipset

Intel® Q870 Chipset

### Memory

1x 32GB SO-DIMM DDR5-5600

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory<sup>[2]</sup>

Up to 64GB (2x 32GB DDR5 SO-DIMM)

### Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal

### Max Storage Support<sup>[3]</sup>

Up to two drives, 2x M.2 2280 SSD

- M.2 2280 SSD up to 2TB

### RAID Preset

None

### Card Reader

No card reader

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC233VB or Conexant CX11771 codec

### Speakers

2Wx1

### Power Supply

90W 89% Adapter

## DESIGN

### Keyboard

USB Traditional Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Expansion Slots

Three M.2 slots (one for WLAN, two for SSD / discrete NPU)

### Case Color

Black

### Stand

Vertical Stand

### Adapter Cage

None

### Toolless Chassis Screw

None

### Dust Filter

None

### Mounting

None

### IO Box

None

### Pen

Pen Not Supported

### Form Factor

Tiny (1L)

### Dimensions (WxDxH)<sup>[4]</sup>

179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)

### Weight<sup>[5]</sup>

Around 1.18 kg (2.6 lbs)

## CONNECTIVITY

### WLAN + Bluetooth<sup>[6]</sup>

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

### WWAN

Non-WWAN

### Ethernet

Integrated 100/1000M

### Front Ports

- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), data transfer only
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports Always On and 5V@2.1A charging
- 1x headphone / microphone combo jack (3.5mm)

### Rear Ports

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one supports Smart Power On
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4a (HBR2)
- 1x Ethernet (GbE RJ-45)

### Optional Rear Ports (configured)

DP 1.4

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

### Fingerprint Reader

No fingerprint reader

### Physical Locks

Kensington® Security Slot™, 3 x 7 mm

### Kensington® Cable Lock

None

### Chassis Intrusion Switch

Chassis Intrusion Switch

## MANAGEABILITY

### System Management<sup>[7]</sup>

Non-vPro®

## SERVICE

### Base Warranty

3-year, Onsite

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 9.0
- RoHS compliant
- TCO Certified 10.0

### Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Solar Radiation, Contamination by Fluids, Salt Fog)

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

Lenovo® AI Now

## ACCESSORIES

### Bundled Accessories

None

## MODEL

**TopSeller** : Yes **Announce Date** : 2025-05-13

**EAN / UPC / JAN** : 199271049617 **End of Support** : 2031-12-13

Note:

<sup>[1]</sup> AI PCs have a NPU capable of 10+ TOPs to run the Copilot.....

· Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39202)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39468)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26647)

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference