

ThinkPad X9-14 Gen 1

PERFORMANCE

Processor	Intel® Core™ Ultra 7 258V, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.8GHz, 12MB
AI PC Category	Copilot+ PC
NPU	Integrated Intel® AI Boost, up to 47 TOPS
Graphics	Integrated Intel® Arc™ Graphics 140V
Chipset	Intel® SoC Platform
Memory	32GB Soldered LPDDR5x-8533, MoP Memory
Memory Slots	Memory soldered to systemboard, no slots, dual-channel
Max Memory	32GB soldered memory, not upgradable
Storage	1TB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0
Storage Support^[1]	One drive, up to 2TB M.2 2242 SSD
Storage Slot	One M.2 2242 PCIe® 4.0 x4 slot
Card Reader	None
Audio Chip	High Definition (HD) Audio, Cirrus Logic® CS42L43
Speakers	Stereo speakers, 2W x2, Dolby Atmos®
Camera	FHD 1080p + IR Discrete with E-shutter
Microphone	2x, Array
Battery	Integrated 55Wh
Power Adapter	65W USB-C® Slim GaN (2-pin)
DESIGN	
Display	14" WUXGA (1920x1200) OLED 400nits Anti-glare, 100% DCI-P3, 60Hz, DisplayHDR™ True Black 500, Dolby Vision®
Touchscreen	None
Keyboard	Backlit, English

Touchpad	Buttonless glass surface multi-touch Haptic Touchpad, supports Precision TouchPad (PTP), 80 x 130 mm (3.15 x 5.12 inches)
Case Color	Grey
Case Material	Aluminium (Top), Aluminium (Bottom)
Pen	Pen Not Supported
Dimensions (WxDxH)^[2]	311.8 x 212.3 x 6.7 - 17.18 mm (12.28 x 8.36 x 0.26 - 0.68 inches)
Weight^[3]	Starting at 1.21 kg (2.66 lbs)
SOFTWARE	
Operating System	Windows® 11 Pro, English (US) / English (UK)
Bundled Software	Intel® Connectivity Performance Suite + Lenovo® AI Now
CONNECTIVITY	
Ethernet^[4]	No Onboard Ethernet
WLAN + Bluetooth^[5]	Intel® Wi-Fi® 7 BE201, 802.11be 2x2 + BT5.4
WWAN	Non-WWAN
SIM Card	None
NFC	None
Standard Ports	<ul style="list-style-type: none">2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.11x HDMI® 2.1, up to 4K/60Hz1x Headphone / microphone combo jack (3.5mm)
Optional Ports (configured)	None
Docking	Various docking solutions supported via Thunderbolt™ / USB-C®. For more compatible docking solutions, please visit Docking for ThinkPad® X9-14 Gen 1
SECURITY & PRIVACY	
Smart Card Reader	None

Security Chip

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

• Ultrasonic Human Presence Detection (WUXGA models)

• E-shutter

• IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories^[6]

None

CERTIFICATIONS

Green Certifications^[7]

• ENERGY STAR® 8.0

• EPEAT™ Gold Registered

• ErP Lot 6/26

• RoHS compliant

• TCO Certified 10.0

Other Certifications

• Eyesafe® Certified 2.0

• Intel® Evo™ Platform

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller

: Yes

Announce Date

: 2025-01-17

EAN / UPC / JAN

: 198155937323

End of Support

: 2031-08-21

Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] The system dimensions may vary depending on configurations.

[3] The system weight is approximate and based on results in.....

· Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2705?M=21QA0004US>

Premier Support - A direct 24x7x365 line to our most elite technicians.

Advanced technical support, 24x7x365, in more than 100 markets

Technical Account Managers for proactive relationship and escalation management

Comprehensive hardware & OEM software support

Priority on service delivery and repair parts

Single point of contact for simplified end-to-end case management

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

ThinkPad Universal USB-C Dock

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39383)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36154)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A14086)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

PSREF
Product Specifications
Reference