

PORTÉGÉ® X30W-M

FREEDOM AND FLEXIBILITY THAT WORKS FOR ANYONE

When success hinges on flexibility, the impressively thin and light Portégé® X30W-K 2-in-1 convertible from Dynabook is both the perfect laptop and perfect tablet for whatever the workday brings.



PERFORMANCE FOR MAXIMUM PRODUCTIVITY

Featuring powerful 13th Gen Intel® Core™ processor options, the Portégé® X30W-K can be configured with up to 32GB of LPDDR5 and comes reinforced with ultra-fast SSDs, Wi-Fi 6E and Thunderbolt™ 4 for uncompromising performance.



ULTRALIGHT INTEL® EVO™ WINDOWS 11 2-IN-1

For artists, entrepreneurs, and everyone in between, the Portégé® X30W-K 2-in-1 laptop weighs in at under 1kg and was designed to foster next-level creativity and take care of business from literally anywhere.



TAP YOUR INNER ARTIST

The Portégé® X30W-K blends premium laptop design with tablet flexibility, ideal for bringing ideas to life. Its vibrant 13.3" Corning® Gorilla® Glass display and responsive Wacom® pen offer natural, precise input for an unparalleled creative experience.



TESTED TO MILITARY DURABILITY STANDARDS

With a magnesium alloy chassis and Gorilla® Glass display shield this 2-in-1 meets MIL-STD-810H durability standards and was engineered to endure the rigors of extreme working conditions.



NEXT LEVEL CONNECTIVITY

Thunderbolt 4 ports connect modern accessories at blistering speeds. Dynabook docking solutions can connect up to four 4K displays and a variety of USB and USB-C devices with a single cable connection.



A UNIQUE PERSPECTIVE

A front-facing HD webcam with privacy shutter ensures clear video conferencing, while an 8MP world-facing camera with anti-glare coating produces high-quality photos and videos in tablet mode.



+Care Service® Warranty with On-Site

Portégé® laptops come standard with +Care Service® Warranty with On-Site, providing three years of on-site service standard for featured configurations and four years of on-site service for Build-to-Order configurations. With additional access to an extensive service and support network, Dynabook +Care Service Warranty with On-Site helps businesses minimize downtime and reduce IT costs.



PLATFORM SPECIFICATIONS AND CONFIGURABLE OPTIONS

Operating System*

- Windows 11 Pro

Processor*

- 13th Generation Intel® Core Processor
 - Core Ultra 5 125U
 - Core Ultra 5 135U
 - Core Ultra 7 155U
 - Core Ultra 7 165U
 - Core Ultra 5 125H
 - Core Ultra 5 135H
 - Core Ultra 7 155H
 - Core Ultra 7 165H

Graphics

- Intel® Iris® X^e Graphics

Memory*

- Up to 32 GB LPDDR5X

Display*

- 13.3" FHD (1920x1080) IGZO² Display
 - 10-point Multi-touch
 - Digital Ink Support
 - Convertible with 360-degree Hinges
 - Corning® Gorilla® Glass NBT™

Storage*

- Up to 1TB Gen 4 PCIe NVMe SSD

Communications

- Intel Ethernet Connection i219
- Intel® Wi-Fi 6E AX211 (Gig+) 802.11ax
- Bluetooth™ 5.2

Camera w/ Privacy Shutter*

- Webcam with Dual-Microphones
- IR Camera for Windows Hello™ Face Sign-in

World-Facing Camera

- 8 Megapixel

Audio

- Dual-Array Microphones
- harman/kardon Stereo Speakers
- Dolby Atmos®

Ports

- HDMI®
- Two (2) USB-C® 4.0 / Thunderbolt™ 4 Ports
- One (1) USB 3.2 Gen 1 Type-A Ports
 - USB Sleep & Charge Support
- Headset Jack
 - Microphone / Headphone Combo Port
- microSD™ Card Slot

Security*

- Microsoft Secured-core PC
- Trusted Platform Module (dTPM) 2.0
- Fingerprint Reader
- Security Lock Slot

Input Devices

- Premium Raised-tile, Backlit Keyboard
- ClickPad Pointing Device
- Dynabook TruPen

Battery

- 53 Wh Battery

Physical Description

- Mystic Blue Metallic
- Magnesium Alloy Chassis
- Designed to Pass MIL-STD-810H Testing Methodologies
- Dimensions:
 - 306 x 210 x 17.9 Millimeters
 - 11.96 x 7.77 x 0.70 Inches
- Starting Weight†:
 - 989 Grams
 - 2.18 Pounds

Regulatory / Environmental Specifications

- EPEAT® Rated
- ENERGY STAR® Qualified
- RoHS Compatible

CONFIGURE THE RIGHT LAPTOP FOR YOUR ORGANIZATION TODAY

US.DYNABOOK.COM



Optional Accessories

- PS0120UA1PRP – Dynabook Thunderbolt™ 4 Dock
- PA5356U-1PRP – Dynabook USB-C® Dock
- PS0001UA1PRP – USB-C® to HDMI® / VGA / LAN / USB 3.0 Adapter with Power Delivery (PD) Charging
- PS0089UA1PRP – USB-C® to VGA / LAN Adapter with Power Delivery (PD) Charging

- PA5352U-1ACA – 65W USB-C® AC Adapter (5V / 9V / 15V / 20V)
- PS0097NA1PEN – Dynabook Universal Pen
- PA5261U-1ETS – Digital Pen Replacement Tips

1. Weight. Weight may vary depending on product configuration, vendor components, manufacturing variability and options selected. * Based on Configuration

2. Warranty. Dynabook's standard limited warranty terms and limitations apply. Visit www.support.dynabook.com/warranty for details. ** Visit <http://us.dynabook.com/info> for a complete list of all product legal footnotes