



GRSH01

Adjustable Depth Heavy Duty Fixed Rack Shelf - Vented

The IOGEAR Vented Adjustable Depth Fixed Shelf is designed for use in equipment racks to hold heavy items. The adjustable depth allows it to fit various rack sizes, and the ventilation helps prevent overheating of equipment.



Features

- Heavy duty construction supports up to 330Lbs
- Vented 27.5 inch shelf designed for optimal airflow
- Adjustable mounting depth supports racks between 19.5 to 38.3 inches
- Includes M6 cage nuts and M6x12mm screws for mounting

Requirements

- Mounting to Square Cage Holes: The included M5 cage nuts will be needed along with the M5 Screws and washers.
- Mounting to M5 Threaded Holes: No cages nuts are needed. Only M5 screws and washers are needed.

Package Contents

- 1 x 1U Rack Shelf
- 8 x M5x12mm Screws
- 8 x M5 Cage Nuts
- 8x Plastic Washers
- 1 x Quick Start Guide



Specifications

FUNCTION		GRSH01	DIMENSIONS		GRSH01
Environment			Unit Dimensions		
Supported Rack Depth		19.5 - 38.3	Height		1.8" (4.6cm)
Max Supported Weight		330 lbs.	Length		27.6" (70.1cm)
Housing			Depth		17.6" (44.7cm)
Case		Metal	Unit Package Dimensions		
			Height		4.6" (11.7cm)
			Width		22.3" (56.6cm)
			Depth		30.75" (78.1cm)
			Master Carton		
			Height		4.6" (11.7cm)
			Width		22.3" (56.6cm)
			Depth		30.75" (78.1cm)
			Master Carton Qty.		1
			Weight		
			Master Carton Wt.		15.4lb (7kg)
			Unit Pack Wt.		15.4lb (7kg)
			Unit Wt.		12.5b (5.7kg)