

Tab K11 Plus

PERFORMANCE

Processor

Qualcomm® Snapdragon® SDM685 (8C, 4x A73 @2.8 GHz + 4x A53@1.9 GHz)

Graphics

Integrated Qualcomm® Adreno™ GPU

Chipset

Qualcomm® SoC Platform

Memory

6GB Soldered LPDDR4x

Storage

128GB UFS 2.2

Card Reader

microSD Card Slot

Storage Support

- 128GB UFS 2.2 on systemboard
- microSD card, supports up to 1TB

Speakers

4 speakers, optimized with Dolby Atmos®

Microphone

2x, Array

Camera

Front 8.0MP / Rear 13.0MP with Flashlight

VoiceCall^[1]

No

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor
- Proximity (P) sensor

Vibration Motor

Eccentric Rotating Mass (ERM)

Battery

Integrated 8600mAh (Typ.)

Power Adapter

10V / 2A

DESIGN

Display

11.45" 2K (2000x1200) TDDI 400nits, 72% NTSC, 90Hz, Touch

Touchscreen

10-point Multi-touch

Case Material

Metal

Keyboard

None

Pen^[2]

Pen Upgradable (Purchase Separately)

Dimensions (WxDxH)^[3]

268.7 x 168.96 x 7.15 mm (11.58 x 6.65 x 0.28 inches)

Weight^[4]

Around 520 g (1.15 lbs)

Case Color

Luna Grey

SOFTWARE

Operating System^[5]

Android™ 14 or Later

CONNECTIVITY

WLAN + Bluetooth®

Wi-Fi® 6, 802.11ax 2x2 + BT5.3

WWAN

Non-WWAN

NFC

NFC

Location Services

GPS + GLONASS + Galileo + Beidou

Standard Ports

- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot
- 1x Pogo pin connector (4-point)

SERVICE

Base Warranty^[6]

1-year, Mail-in

ACCESSORIES

Bundled Accessories^[7]

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0 (only available for TB352FU)
- ErP Lot 6/26
- RoHS compliant

Dust and Water Resistant

IP52

Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

PSREF

Product Specifications Reference

MODEL

Product : TB352FU

TopSeller : Yes

Announce Date : 2025-01-07

EAN / UPC / JAN : 198156671387



Product image is a sample, it may not match the real color of this model

Note:

[1] Use of Voice call requires cellular data plan. Voice call functionality details may vary based on local operator network, data and messaging services. Please contact your carriers for details.

[2] For details upon pen compatibility, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>. Pen availability may vary by country / region.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[5] For the latest upgrade information, please visit [Android Upgrade Matrix](https://support.lenovo.com/solutions/accs-guide).

[6] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

[7] For compatible accessories, please check the file "Lenovo Android Tablet - Option Compatibility Matrix" from <https://support.lenovo.com/solutions/accs-guide>.

• Lenovo reserves the right to change specifications without notice.
• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to

<https://psref.lenovo.com/Detail/2466?M=ZADS0102US>

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.

HASSLE FREE

‘Getting started’ and ‘how-to’ assistance for hardware and software. Easy solutions that are simple to reach – that’s how Premium Care delivers you the ideal support experience.

REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can’t be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication “as is” without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

Lenovo Tab Pen Plus

With 4,096 levels of pressure and tilt detection, sketch, draw or just take notes with the highest degree of precision, responsiveness and control yet with the new Lenovo Tab Pen Plus, featuring ultra-low-latency, hig...

Smart Charge Station 4pin USB-C(US)

Smart Charging Station provides easy charging for selected models of Lenovo tablets, and also a stand for “Smart” functions.

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

PSREF
Product Specifications
Reference