

KC 500 MX LP TKL

Compact, mechanical low-profile keyboard in a slim design



Models may vary from the image shown

CHERRY MX LOW PROFILE 2.0 SWITCH

The CHERRY KC 500 MX LP TKL is part of the first keyboard series with the new CHERRY MX LP 2.0 switches. These are characterized by super-soft actuation, absolute switching reliability and an incredibly long service life. This is the start of a new generation of slim mechanical keyboards thanks to its improved haptics and sound.

HIGH-END PBT KEY CAPS

Also brand new are our own key caps made of PBT material, on which the symbols are sprayed directly using plastic injection. The result is absolute wear resistance and durability. In addition, the material used ensures a subtle, dampened sound when typing and is pleasantly quiet.

BACKLIGHTING

A discreet white backlight keeps you working even in the dark. Lockable status keys such as CAPS LOCK, NUM LOCK, WINDOWS or FN also have integrated red LEDs. This allows you to see at a glance which toggle keys are activated.

TIMELESS DESIGN

The design is timeless and elegant. With the anodized metal plating and other metallic accents in the background, the CHERRY KC 500 MX LP TKL fits

easily in modern workplaces. Nevertheless, it is robust enough to be used in the industrial sector. Fold-out feet allow the angle to be adjusted to suit your preferences. The high-quality USB-A to USB-C cable can be disconnected. With a total height of only 19.1 mm on the front side and less than 22 mm at the rear, it is one of the slimmest mechanical keyboards.

VERSATILE

The CHERRY KC 500 MX LP TKL is an outstanding choice for power users, programmers and frequent writers. Of course, gaming is also possible without any problems. As it is a wired keyboard despite its high-end features, the CHERRY KC 500 MX LP TKL remains affordable and offers excellent value for money.

COMPACT TENKEYLESS VERSION

In the TKL version, the number pad has been omitted, resulting in a smaller footprint and more desk space. Otherwise, each key is in its usual size in its usual place.

FUNCTION AND PERFORMANCE

- Slim design with compact dimensions and extra low height
- Original CHERRY MX low-profile 2.0 switches (made in Germany)
- White lighting with colored status buttons
- PBT key caps with 2-component injection molding
- Foldable feet for tilt adjustment
- Anodized metal surface

TECHNICAL DATA

Colour:	black
Weight main product:	535 g
Weight of product without packaging:	535 g

Weight of product incl. packaging: 821 g

Weight of master carton incl. content:	8,754 g
--	---------

Content of master carton (pieces):	10
------------------------------------	----

Dimensions product without packaging:	351 mm x 124 mm x 21,17 mm
---------------------------------------	----------------------------

Dimensions product incl. packaging:	382 mm x 173 mm x 32 mm
-------------------------------------	-------------------------

Dimensions master carton:	410 mm x 355 mm x 210 mm
---------------------------	--------------------------

Cable length:	180 cm
---------------	--------

Storage temperature:	-20 °C - 45 °C
----------------------	----------------

Working temperature:	0 °C - 40 °C
----------------------	--------------

Product approvals:	• CE • China RoHS • FCC • KCC • UKCA
--------------------	--

System	USB-C
--------	-------

Requirements-Hardware:

Operating system:	• Windows 7 or higher • Windows 10 or higher
-------------------	---

Scope of delivery:	• Keyboard • Manual • Keycaps • USB-cable
--------------------	--

Reliability:	MTBF 90: > 10 Mio.
--------------	--------------------

Software support:	CHERRY KEYS
-------------------	-------------

Service life per key (in million strokes):	100 mio. actuations
--	---------------------

Max. current consumption (mA) of keyboard: 500 mA

Keyboard format:	TKL (80%)
------------------	-----------

Integrated metal plate:	yes
-------------------------	-----

Volume (dB) of keyboard:	40 db
--------------------------	-------

N-Key Rollover:	yes
-----------------	-----

Anti-ghosting:	yes
----------------	-----

Key encryption:	AES-128
-----------------	---------

Response time:	1 ms
----------------	------

Actuating force (cN):	45 cN
-----------------------	-------

Pre-Travel:	1 mm
-------------	------

Total Key Travel:	3 mm
-------------------	------

Key labeling:	Double shot injection molding
---------------	-------------------------------

Palm rest:	Palm rest not available
------------	-------------------------

USB-Hub:	no
----------	----

Number of keys:	87
-----------------	----

Illumination:	white
---------------	-------

Adjustable feet:	yes
------------------	-----

Status LEDs:	in keys
--------------	---------

Key technology:	Mechanical
-----------------	------------

Switches:	CHERRY MX LP 2.0 IVORY
-----------	------------------------

Keycap material:	PBT
------------------	-----

EAN:	4025112117329
------	---------------

UPC:	840183608958
------	--------------

Model number:	MX25550
---------------	---------

Protection class:	Standard
-------------------	----------

Warranty:	2 years warranty
-----------	------------------

Layout:	US (USA)
---------	----------

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.