

PERFORMANCE**Processor**

AMD Ryzen™ AI 9 HX PRO 370 (12C / 24T, 2.0 / 5.1GHz, 12MB L2 / 24MB L3)

AI PC Category

Copilot + PC, AI-Ready Workstations

NPU

Integrated AMD Ryzen™ AI, up to 50 TOPS

Graphics

Integrated AMD Radeon™ 890M Graphics

Chipset

AMD SoC Platform

Memory

2x 48GB SO-DIMM DDR5-5600 Non-ECC

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory

Up to 96GB (2x 48GB DDR5 SO-DIMM)

Storage

2TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Max Storage Support^[1]

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Card Reader

No card reader

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Camera

5.0MP + IR with Privacy Shutter and Human Presence Detection

Microphone

2x, Array

Battery

57Wh

Power Adapter

65W USB-C® Slim GaN (2-pin)

DESIGN**Display^[2]**

14" WUXGA (1920x1200) IPS 500nits Anti-glare, 100% sRGB, Low Power, Eyesafe®, UL Low Blue Light

Color Calibration

ICC Template Color Calibration

Keyboard

Backlit, French

Case Color

Black

Case Material

PC + 20% CF + 50% GF + 30% PCC (Top), PC + 20% CF + 30% PCC (Bottom)

Pen

Pen Not Supported

Dimensions (WxDxH)^[3]

315.90 x 223.70 x 10.90/16.13 (front/rear), 21.8 (maximum) mm;
12.44 x 8.81 x 0.43/0.64 (front/rear), 0.86 (maximum) inches

Weight^[4]

Starting at 1.39 kg (3.06 lbs)

SOFTWARE**Operating System**

Windows® 11 Pro, French / Canadian French / English

Bundled Software

Lenovo® AI Now

CONNECTIVITY**WLAN + Bluetooth®**

MediaTek Wi-Fi® 7 MT7925, 802.11be 2x2 + BT5.4

WWAN

Non-WWAN

Ethernet

100/1000M (RJ-45)

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with PD 3.0 and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Security keyhole

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® P14s Gen 6 \(AMD\)](#)

SECURITY & PRIVACY**Security Chip**

Discrete TPM 2.0 Enabled

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

- Bottom cover tamper detection
- Camera privacy shutter (camera models)
- Ultrasonic Human Presence Detection for IR camera
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY**System Management**

AMD PRO Manageability

SERVICE**Base Warranty**

1-year, Courier or Carry-in

Included Upgrade

1Y Premier Support Upgrade from 1Y Courier/Carry-in

CERTIFICATIONS**Green Certifications^[5]**

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified 10.0

Other Certifications

- UL Low Blue Light
- Eyesafe® Certified 2.0

Mil-Spec Test

MIL-STD-810H military test passed

ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

MODEL

TopSeller : Yes

EAN / UPC / JAN : 198157589421

Announce Date : 2025-05-23

End of Support : 2031-11-22

Note:

[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[5] EPEAT is registered where applicable, please visit [epeat.net](#) for registration status by country.

Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...



ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

- The ThinkPad Hybrid USB-C with USB-A dock is a productivity solution for any USB-C or USB-A laptop, including non-Lenovo laptops from Dell, HP, and Apple, providing power, display, and port expansion in any m...

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference