

**PERFORMANCE****Processor**

Intel® Core™ i5-12450HX, 8C (4P + 4E) / 12T, P-core up to 4.4GHz, E-core up to 3.1GHz, 12MB

**AI PC Category<sup>[1]</sup>**

AI-Powered Gaming PC

**Graphics**

NVIDIA® GeForce RTX™ 3050 6GB GDDR6, Boost Clock 1432MHz, TGP 65W, 142 AI TOPS

**Chipset**

Intel® HM670 Chipset

**Memory<sup>[2]</sup>**

1x 8GB SO-DIMM DDR5-4800

**Memory Slots**

One DDR5 SO-DIMM slot

**Max Memory**

Up to 32GB DDR5-4800

**Storage**

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

**Storage Slot**

Two M.2 2242 PCIe® 4.0 x4 slots

**Max Storage Support<sup>[3]</sup>**

Up to two drives, 2x M.2 SSD  
• M.2 2242 SSD up to 1TB each

**Optical**

None

**Card Reader**

3-in-1 Card Reader

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC3287 codec

**Speakers**

Stereo speakers, 2W x2, optimized with Nahimic Audio

**Microphone**

2x, Array

**Camera**

HD 720p with Privacy Shutter

**Battery**

57Wh

**Power Adapter**

135W Slim Tip (3-pin)

**DESIGN****Display<sup>[4]</sup>**

15.6" FHD (1920x1080) IPS 300nits Anti-glare, 100% sRGB, 144Hz

**Touchscreen**

None

**Screen-to-Body Ratio**

88% AAR (active area ratio)

**Color Calibration**

None

**Pen**

Pen Not Supported

**Keyboard**

Non-backlit, English

**Touchpad**

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 69 x 104 mm (2.72 x 4.09 inches)

**Dimensions (WxDxH)<sup>[5]</sup>**

359.3 x 236 x 19.9-22.95 mm (14.15 x 9.29 x 0.78-0.90 inches)

**Weight<sup>[6]</sup>**

Starting at 1.77 kg (3.9 lbs)

**Case Color**

Luna Grey

**Case Material**

PC-ABS (Top), PC-ABS (Bottom)

**Surface Treatment**

IMR (In-Mold Decoration by Roller)

**SOFTWARE****Operating System**

Windows® 11 Home, English

**Bundled Software**

Office Trial

**CONNECTIVITY****WLAN + Bluetooth®**

Wi-Fi® 6, 802.11ax 2x2 + BT5.2

**WWAN**

Non-WWAN

**Ethernet**

100/1000M (RJ-45)

**Standard Ports**

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), data transfer only
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Card reader
- 1x Power connector

**SECURITY & PRIVACY****Security Chip**

Firmware TPM 2.0 Enabled

**Fingerprint Reader**

None

**Other Security**

Camera privacy shutter

**SERVICE****Base Warranty**

1-year, Courier or Carry-in

**Included Upgrade**

None

**ACCESSORIES****Bundled Accessories**

None

**CERTIFICATIONS****Green Certifications**

- ErP Lot 6/26
- RoHS compliant

**MODEL**

TopSeller : No

Announce Date : 2025-01-24

EAN / UPC / JAN : 198157086678

End of Support : 2030-10-28



Product image is a sample, it may not match the real color of this model

**Note:**

[1] AI-Powered Gaming PCs feature Lenovo AI Engine+ and NVIDIA GeForce RTX GPUs to handle AI-driven tasks and deliver exceptional gaming performance.

[2] Installed memory is actually DDR5-5600 but may run as DDR5-4800 depending on the memory support capability of processor.

[3] The storage capacity supported is based on the test.....

• Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

## Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38620)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73714)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K75663)

Please click [here](#) to view the full list of accessories.



**PSREF**  
Product Specifications  
Reference