

Lenovo 300e Yoga Chromebook Gen 4

PSREF Product Specifications Reference

PERFORMANCE

Processor

MediaTek Kompanio 528 (8C, 2x A76 @2.2GHz + 6x A55 @2.0GHz)

Graphics

Integrated Arm Mali-G52 2EE MC2 GPU

Chipset

MediaTek SoC Platform

Memory^[1]

4GB Soldered LPDDR4x-3733

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

4GB soldered memory, not upgradable

Storage

32GB eMMC 5.1

Storage Support^[2]

32GB eMMC 5.1 on systemboard

Storage Slot

eMMC on systemboard, no slots

Card Reader

No card reader

Audio Chip

High Definition (HD) Audio

Speakers

Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

Camera

Front HD 720p with Privacy Shutter / Rear 5.0MP

Microphone

Mono (Front) + Mono (Rear)

Battery

47Wh

Power Adapter

65W USB-C® (2-pin)

DESIGN

Display^[3]

11.6" HD (1366x768) IPS 250nits Glossy / Anti-fingerprint, 50% NTSC, 60Hz, Corning® Gorilla® Glass, Touch

Touchscreen

10-point Multi-touch

Keyboard

Non-backlit, English

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 60.5 x 104 mm (2.38 x 4.09 inches)

Case Color

Surface Treatment

Texture

Case Material

PC-ABS (Top), PC-ABS (Bottom)

Pen

Lenovo® Integrated Pen for 300e/500e Yoga® Chromebook Gen 4 (Garaged)

Dimensions (WxDxH)^[4]

287 x 200 x 18.6 mm (11.3 x 7.9 x 0.73 inches)

Weight^[5]

Around 1.33 kg (2.93 lbs)

Others

Buttons: power key, volume key

SOFTWARE

Operating System

ChromeOS

Bundled Software

None

CONNECTIVITY

Ethernet

No Onboard Ethernet

WLAN + Bluetooth^[6]

MediaTek Wi-Fi® 6 MT7921, 802.11ax 2x2 + BT5.1

WWAN

Non-WWAN

SIM Card

None

Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C® 3.2 Gen 1 (support data transfer, Power Delivery and DisplayPort™)
- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)

None

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for Lenovo® 300e Yoga® Chromebook Gen 4](#)

SECURITY & PRIVACY

Security Chip

Google Security Chip H1

Fingerprint Reader

None

Physical Locks

Kensington® Nano Security Slot™

Other Security

Camera privacy shutter

SERVICE

Base Warranty

1-year, Mail-in

Included Upgrade

None

ACCESSORIES

Bundled Accessories^[7]

None

CERTIFICATIONS

Green Certifications^[8]

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 9.0

Other Certifications

ASTM F963 test passed

Mil-Spec Test

MIL-STD-810H military test passed (20 test items)

MODEL

TopSeller : Yes **Announce Date** : 2024-12-17

EAN / UPC / JAN : 198156469328 **End of Support** : N/A



Product image is a sample, it may not match the real color of this model
· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to <https://psref.lenovo.com/Detail/2189?M=82W2002GUS>

Graphite Grey

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

ThinkPad Universal USB-C Dock

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Lenovo USB-C Mini Dock_US

Expand Your Potential with An Universal Mini Dock; Lenovo understands that modern business depends on a wide variety of PC's and even brands to meet their business needs. To make this easier Lenovo USB-C Mini dock is ...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

PSREF
Product Specifications
Reference