

## PERFORMANCE

### Processor

AMD Ryzen™ 3 7335U (4C / 8T, 3.0 / 4.3GHz, 2MB L2 / 8MB L3)

### Graphics

Integrated AMD Radeon™ 660M Graphics

### Chipset

AMD SoC Platform

### Memory

1x 8GB SO-DIMM DDR5-4800

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory<sup>[1]</sup>

Up to 16GB DDR5-4800

### Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe®

### Optane™ Memory

None

### Max Storage Support<sup>[2]</sup>

One drive, up to 1TB M.2 SSD

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC233-CG codec

### Speakers

3Wx2, HARMAN

### Camera

5.0MP

### Microphone

Dual Microphone

### Power Supply

90W 89% Adapter

## DESIGN

### Display<sup>[3]</sup>

23.8" FHD (1920x1080) IPS Anti-glare 250nits, 100Hz, 99% sRGB, hardware low blue light, 3-side borderless, non-touch

### Touchscreen

None

### Keyboard

Wireless EOS Keyboard, Luna Grey, English / French (CA)

### Mouse

Wireless EOS Mouse, Luna Grey

### Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

### Case Color

Luna Grey

### Stand

AIO Stand

### Wireless Charger

None

### Pen

Pen Not Supported

### Form Factor

AIO (24 inches)

### Dimensions (WxDxH)<sup>[4]</sup>

540 x 192 x 431 mm (21.25 x 7.56 x 16.97 inches)

### Weight<sup>[5]</sup>

Around 6.0 kg (13.23 lbs)

## CONNECTIVITY

### WLAN + Bluetooth®

Wi-Fi® 6, 802.11ax 2x2 + BT5.2

### WWAN

Non-WWAN

### Ethernet

Integrated 100/1000M

### Rear Ports

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 1x HDMI®-in 1.4
- 1x HDMI®-out 2.1 TMDS
- 1x Ethernet (RJ-45)
- 1x power connector

### Left Ports

- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), data transfer only
- 1x headphone / microphone combo jack (3.5mm)

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0 integrated in SoC

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3/7
- GREENGUARD®
- RoHS / WEEE / REACH

### Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light
- TÜV Rheinland® Ultra Low Noise

## SOFTWARE

### Operating System

Windows® 11 Home, French / English

### Bundled Software

None

## MODEL

<b>TopSeller</b>	: No	<b>Announce Date</b>	: 2025-04-18
<b>EAN / UPC / JAN</b>	: 197530183638	<b>End of Support</b>	: 2030-02-18



AMD2

Product image is a sample, it may not match the real color of this model

Note:

[1] The max memory is based on the test results with current Lenovo memory offerings.

[2] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[3] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

• Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



## Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38603)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73715)
GOOD	2Y Onsite upgrade from 1Y Mail-in delivery (5WS0K85946)

Please click [here](#) to view the full list of accessories.

