

# Legion T7 34IAS10

## PERFORMANCE

### Processor

Intel® Core™ Ultra 7 265KF, 20C (8P + 12E) / 20T, Max Turbo up to 5.5GHz, 36MB

### AI PC Category

AI-Powered Gaming PC

### NPU

Integrated Intel® AI Boost, up to 13 TOPS

### Graphics<sup>[1]</sup>

NVIDIA® GeForce RTX™ 5080 16GB GDDR7

### Chipset

Intel® Z890 Chipset

### Memory<sup>[2]</sup>

2x 16GB UDIMM DDR5-5600

### Memory Slots

Four DDR5 UDIMM/CUDIMM slots, dual-channel capable

### Max Memory<sup>[3]</sup>

Up to 128GB DDR5-5600

### Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

### Storage Support<sup>[4]</sup>

Up to six drives, 2x 3.5" HDD + 4x M.2 SSD

- 3.5" HDD up to 2TB

- M.2 SSD up to 2TB

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC1220 codec

### Speakers

No speakers

### Power Supply

850W 90%

## DESIGN

### Keyboard

USB Calliope Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Expansion Slots

- One PCIe® 5.0 x16
- One PCIe® 4.0 x16 (x4 signal)
- One PCIe® 3.0 x1
- Five M.2 slots (one for WLAN, four for SSDs)

### Case Color

Storm Grey

## System Lighting

Legion Lighting + Internal Ambient Lighting

### Chassis

Transparent Cover

### Cooler

3x 120MM with RGB Light + PCH Heatsink + VRM Heatsink

### System Fan

1x Rear + 2x Top with ARGB

### Form Factor

Tower (34L)

### Dimensions (WxDxH)

211 x 451.6 x 477.4 mm (8.3 x 17.77 x 18.79 inches)

### Weight<sup>[5]</sup>

Around 18 kg (39.68 lbs)

## CONNECTIVITY

### Ethernet

2.5GbE RTL8125BG

### WLAN + Bluetooth®

Wi-Fi® 6E, 802.11ax 2x2 + BT5.3

### Top Ports

- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 1x headphone / microphone combo jack (3.5mm)

### Rear Ports<sup>[6][7][8]</sup>

- 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.1 and DisplayPort™ 2.1
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 4x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x DisplayPort™ 1.4
- 1x Ethernet (2.5GbE RJ-45)
- 1x Power connector
- 6x Audio connectors

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0 integrated in chipset

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

3Y Legion Ultimate Support with Onsite

## CERTIFICATIONS

## PSREF

Product Specifications  
Reference

### Green Certifications

- ErP Lot 3
- RoHS compliant
- None

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

None

## MODEL

TopSeller : No

EAN / UPC / JAN : 198157015067

Announce Date : 2025-03-24

End of Support : 2030-11-25



Product image is a sample, it may not match the real color of this model

### Note:

[1] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

[2] Installed memory is actually DDR5-6400 but may run as DDR5-5600 or less depending on the memory support capability of Intel.

[3] The max memory is based on the test results with current Lenovo memory offerings.

[4] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] For video ports on discrete graphics, please see graphics section.

[7] For some models, this connector does not support display function.

[8] DisplayPort out connector are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2541?M=90Y6003KUS>

## Premium Care - Advanced Support from Real People. Real Fast.

### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Recommended Accessories

### Lenovo USB-C to Ethernet Adapter

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

### Lenovo Professional Wireless Combo Keyboard & Mouse (US English)

This sleek and stylish full-size keyboard and mouse combo offers exceptional quality in a modern wireless solution. The slim 3-zone keyboard with number pad has responsive quiet keys and a premium typing experience. O...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

### PSREF

Product Specifications  
Reference