

PERFORMANCE

Display Size	31.5"
View Area	697.3x392.2 mm
Panel	In-Plane Switching
Backlight	WLED
Aspect Ratio	16:9
Resolution	3840x2160
Pixel Pitch	0.1816x0.1816 mm
Dot / Pixel Per Inch	140 dpi
View Angle (H / V)	178 / 178
Response Time	4ms GtG (Extreme mode) / 6ms GtG (Typical mode)
Color Support	1.07 Billion
Refresh Rate	48Hz - 60Hz
Brightness	350 cd/m ²
Contrast Ratio	1500:1
Color Gamut	99% sRGB, 99% BT.709
Screen Surface Treatment	Yes
Curvature	None
Camera	Modular Camera Support
Microphone	None
Speakers	Modular Speaker Support
Power Consumption (Typical / Maximum)	25.5W / 195W
Power Adapter	Integrated

DESIGN

Stand	Tilt, Swivel, Pivot, Height Adjust Stand
Case Color	Eclipse Black
Side Bezel Width	2 mm
Mounting	Supports VESA mount 100 x 100 mm
ThinkCentre M Series Support	Tiny Support
Dimensions (WxDxH)^[1]	<ul style="list-style-type: none"> • Lowest Position 714.2 x 218.0 x 439.3 mm (28.12 x 8.58 x 17.30 inches) • Highest Position 714.2 x 218.0 x 594.3 mm (28.12 x 8.58 x 23.40 inches) • Head Only 714.2 x 46.5 x 413.0 mm (28.12 x 1.83 x 16.26 inches)
Packaging Dimensions (WxDxH)	950.0 x 139.0 x 520.0 mm (37.40 x 5.47 x 20.47 inches)
Weight^[2]	<ul style="list-style-type: none"> • Monitor With Stand 9.2 kg (20.3 lbs) • Monitor Head Only 6.3 kg (13.9 lbs)
Packaging Weight	13.5 kg (29.8 lbs)

CONNECTIVITY

USB Port	x USB-C® (USB 10Gbps, DP 1.4 Alt Mode HBR3, PD3.0 100W, USB upstream), 3x USB-A (USB 5Gbps, 1x BC1.2, USB downstream), 1x USB-C (USB 5Gbps, 15WPD, USB downstream)
Video Connector	1x HDMI® 2.1 TMDS, 1x DP 1.4 (HBR3), 1x USB-C® (10Gbps, DP 1.4 Alt Mode HBR3)
Network Connectivity	1x RJ45, Ethernet (10M/100M/1000M)

SERVICE

Base Warranty	3-year
----------------------	--------

CERTIFICATIONS

Environmental Certification	ENERGY Star Certified, TCO 10, TCO Edge 2.1, EPEAT™ Gold, EU Energy Efficiency Level (Level-F), Volatile Organic Compound Certification, RoHS
Ergonomic Certification	TÜV Rheinland® Eye Comfort 4 Stars, Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution)
Sync Technology	

None

Special Features

- HDR10 Compliance
- Lenovo® ThinkColour (Lenovo Accessories and Display Manager) Support Lenovo ThinkColour supports Windows® 10 & 11, Mac OS (functions vary across systems). Lenovo Accessories and Display Manager is formerly Lenovo Display Control Center.
- LDFM (Lenovo® Display Fleet Manager)
- Mirrored Power Button
- Natural Low Blue Light
- Smart Power

SOFTWARE**Operating System**

Support Windows® 10, Windows 11

ACCESSORIES**In the Box**

- Monitor with stand
- 1x DP 1.4 cable (1.8m)
- 1x USB-C® to USB-C Gen 2 cable (1.5m)
- 1x Power cable (1.8m)
- Quick setup guide

MODEL

Region	: APS
EAN / UPC / JAN	: 0198156726827 / 198156726827 / None
Announce Date	: 2025-06-23



Product image is a sample, it may not match the real color of this model
Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

• Lenovo reserves the right to change specifications without notice.

Premium Care - Advanced Support from Real People. Real Fast.




REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Essential FHD Webcam Gen2
4XC1S15018



ThinkCentre Tiny Mounting Kit 4XF1R07369



ThinkVision MS30 Monitor Soundbar
4XD1J05151

Please click [here](#) to view the full list of accessories.

Lenovo

PSREF
Product Specifications
Reference