

PERFORMANCE

- Processor**
Intel® Core™ Ultra 7 155U, 12C (2P + 8E + 2LPE) / 14T, Max Turbo up to 4.8GHz, 12MB
- AI PC Category**^[1]
AI PC
- NPU**
Integrated Intel® AI Boost, up to 11 TOPS
- Graphics**
Integrated Intel® Graphics
- Chipset**
Intel® SoC Platform
- Memory**
1x 16GB SO-DIMM DDR5-5600
- Memory Slots**
Two DDR5 SO-DIMM slots, dual-channel capable
- Max Memory**^[2]
Up to 64GB DDR5-5600
- Storage**
512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0
- Storage Support**^[3]
One drive, up to 2TB M.2 2280 SSD
- Storage Slot**
One M.2 2280 PCIe® 4.0 x4 slot
- Card Reader**
None
- Optical**
None
- Audio Chip**
High Definition (HD) Audio, Senary SN6147 codec
- Speakers**
Stereo speakers, 2W x2, Dolby Audio™
- Camera**
HD 720p with Privacy Shutter
- Microphone**
2x, Array
- Battery**
46.5Wh
- Power Adapter**
65W USB-C® Slim (2-pin)

DESIGN

- Display**^{[4][5]}
14" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, DBEF5
- Touchscreen**
None

- Keyboard**
Backlit, French
- Case Color**
Black
- Case Material**
PC-ABS (Top), PC-ABS (Bottom)
- Pen**
No support
- Dimensions (WxDxH)**^[6]
313.7 x 226 x 18.92 mm (12.35 x 8.90 x 0.74 inches)
- Weight**^[7]
Starting at 1.4 kg (3.09 lbs)

SOFTWARE

- Operating System**
Windows® 11 Pro, French
- Bundled Software**
None

CONNECTIVITY

- WLAN + Bluetooth**^[8]
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3
- WWAN**
Non-WWAN
- SIM Card**
None
- Ethernet**
100/1000M (RJ-45)
- NFC**
None
- Standard Ports**
- 1x USB-A (Hi-Speed USB / USB 2.0)
 - 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
 - 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), with USB PD 3.0 and DisplayPort™ 1.4
 - 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
 - 1x HDMI® 2.1, up to 4K/60Hz
 - 1x Headphone / microphone combo jack (3.5mm)
 - 1x Ethernet (RJ-45)

- Optional Ports (configured)**
None

- Docking**
Various docking solutions supported via Thunderbolt™ or USB-C®.
For more compatible docking solutions, please visit [Docking for ThinkPad® L14 Gen 5 \(Intel®\)](#)

SECURITY & PRIVACY

- Smart Card Reader**
None
- Security Chip**
Discrete TPM 2.0 Enabled
- Fingerprint Reader**
None
- Physical Locks**
Kensington® Nano Security Slot™, 2.5 x 6 mm
- Other Security**
Camera privacy shutter

MANAGEABILITY

- System Management**
Non-vPro®

SERVICE

- Base Warranty**
1-year, Courier or Carry-in
- Included Upgrade**
None

ACCESSORIES

- Bundled Accessories**
None

CERTIFICATIONS

- Green Certifications**^[9]
- ENERGY STAR® 8.0
 - EPEAT™ Gold Registered
 - ErP Lot 6/26
 - RoHS compliant
 - TCO Certified 10.0

- Mil-Spec Test**
MIL-STD-810H military test passed

MODEL

- | | | | |
|------------------------|----------------|-----------------------|--------------|
| TopSeller | : Yes | Announce Date | : 2025-01-14 |
| EAN / UPC / JAN | : 198156805577 | End of Support | : 2030-11-16 |

Note:

[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The storage capacity supported is based on the test results with current Lenovo storage offerings.

[4] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[5] 3M DBEF5 (Dual Brightness Enhancement Film) improves the.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to <https://psref.lenovo.com/Detail/2473?M=21L10065CA>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39383)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36154)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A14086)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference