

## PERFORMANCE

### Processor

AMD Ryzen™ 5 7520U (4C / 8T, 2.8 / 4.3GHz, 2MB L2 / 4MB L3)

### Graphics

Integrated AMD Radeon™ 610M Graphics

### Chipset

AMD SoC Platform

### Memory

8GB Soldered LPDDR5-5500

### Memory Slots

Memory soldered to systemboard, no slots, dual-channel

### Max Memory

8GB soldered memory, not upgradable

### Storage

256GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

### Storage Slot

One M.2 2242 PCIe® 3.0 x2 slot

### Max Storage Support

One drive, up to 1TB M.2 2242 SSD

### Optical

None

### Card Reader

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 1.5W x2, Dolby Audio™

### Microphone

2x, Array

### Camera

HD 720p with Privacy Shutter

### Battery

38Wh

### Power Adapter<sup>[1]</sup>

65W USB-C® (3-pin)

## DESIGN

### Display

15.6" FHD (1920x1080) TN 250nits Anti-glare

### Touchscreen

None

### Screen-to-Body Ratio

87%

### Pen

Pen Not Supported

### Keyboard

Non-backlit, English

### Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 62 x 104 mm (2.44 x 4.09 inches)

### Dimensions (WxDxH)<sup>[2]</sup>

359.2 x 235.8 x 19.9 mm (14.14 x 9.28 x 0.78 inches)

### Weight<sup>[3]</sup>

Less than 1.63 kg (3.59 lbs)

### Case Color

Business Black

### Case Material

PC-ABS (Top), PC-ABS (Bottom)

### Surface Treatment

Texture

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

Office Trial

## CONNECTIVITY

### WLAN + Bluetooth®

Wi-Fi® 6, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### Ethernet

100/1000M (RJ-45)

### Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C® 3.2 Gen 1 (support data transfer, Power Delivery (20V only) and DisplayPort™ 1.2)
- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Power connector

### Docking

Various docking solutions supported via USB-C®.

For more compatible docking solutions, please visit [Docking for Lenovo® V15 G4 AMN](#)

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0 Enabled

### Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

### Fingerprint Reader

None

### Other Security

Camera privacy shutter

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications<sup>[4]</sup>

- TCO Certified 9.0
- ENERGY STAR® 8.0
- EPEAT™ Silver Registered
- ErP Lot 3
- FSC certified package
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed

### Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

## MODEL

**TopSeller** : Yes **Announce Date** : 2025-06-18

**EAN / UPC / JAN** : 199271909997 **End of Support** : 2029-08-19



AMD

Product image is a sample, it may not match the real color of this model

· Lenovo reserves the right to change specifications without notice.  
 · California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

## Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38566)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0U55751)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)

Please click [here](#) to view the full list of accessories.

