

Rugged Case for Lenovo M11/K11 2024 (330FU/TB330XU/TB-331FC)

CODi's Rugged Case is a complete 3-in-1 solution that provides 360° of device protection. It includes a polycarbonate tray and front with a thick silicone bumper for increased corner protection. The case is easy to install, comfortable to use, and gives the user confidence their tablet is protected, no matter the environment.



CERTIFICATIONS



Shock Absorbing & Drop Testing Certification

MIL-STD-810G, Method 516.6

CODi's Rugged Cases are proven to protect the devices they hold against damage due to drops.



Contamination by Fluid Certification

MIL-STD-810G, Method 504.1

CODi's Rugged Cases are proven to withstand cleaning and disinfecting chemicals.

PART NUMBER	C30705096
MATERIALS	Polycarbonate / Silicone
COMPATIBILITY	Lenovo M11/K11 2024 (330FU/TB330XU/TB-331FC)
DIMENSIONS	10.5 x 7.5 x 2 in
WEIGHT	1.05 lbs
WARRANTY	Limited One Year Warranty

FEATURES

- 3-PART DESIGN GIVES YOUR TABLET 360° PROTECTION
- INTEGRATED KICK-STAND FOR PORTRAIT OR LANDSCAPE VIEWING MODES
- 360° ROTATING, ADJUSTABLE NEOPRENE HAND STRAP
- THICK SILICONE BUMPERS AT EACH CORNER FOR ENHANCED SCREEN PROTECTION
- COMPATIBLE WITH TEMPERED GLASS SCREEN PROTECTORS
- INCLUDES ADJUSTABLE, DETACHABLE SHOULDER STRAP THAT CAN BE SECURED AT ALL FOUR CASE CORNERS
- EASY ACCESS TO PORTS, BUTTONS, CAMERAS AND SPEAKERS

FOR MORE INFORMATION



Contact our US-based customer support team:

+1 800.263.4462

custsupport@codiworldwide.com

or visit [CODiWorldwide.com](https://www.CODiWorldwide.com)

CODi Acquisition, LLC

3070 McCann Farm Drive, Unit 104 // Garnet Valley, PA 19060