

## PERFORMANCE

### Processor

Intel® N250 (4C / 4T, Max Turbo up to 3.8GHz, 6MB)

### Graphics

Integrated Intel® Graphics

### Chipset

Intel® SoC Platform

### Memory

8GB Soldered LPDDR5-4800

### Memory Slots

Memory soldered to systemboard, no slots

### Max Memory

8GB soldered memory, not upgradable

### Storage

128GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

### Max Storage Support<sup>[1]</sup>

One drive, up to 256GB M.2 2242 SSD

### Storage Slot

One M.2 2242 PCIe® 3.0 x4 slot (M.2 SSD models)

### Card Reader

No card reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, optimized with Dolby Audio™

### Camera

Front HD 720p with Privacy Shutter + Rear 5.0MP

### Microphone

Mono (Front) + Mono (Rear)

### Battery

47Wh

### Power Adapter

65W USB-C® (2-pin)

## DESIGN

### Display<sup>[2]</sup>

11.6" HD (1366x768) IPS 250nits Glossy / Anti-fingerprint, 50% NTSC, 60Hz, Corning® Gorilla® Glass, Touch

### Touchscreen

OGS, 10-point Multi-touch

### Keyboard

Non-backlit, French / English

### Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 60.5 x 104 mm (2.38 x 4.09 inches)

### Case Color

Slate Grey

### Surface Treatment

Texture Painting (Top), Texture (Bottom)

### Case Material

PC-ABS (Top), PC-ABS (Bottom)

### Pen

Lenovo® Integrated Pen, on-board garaged, rechargeable, supports AES protocol

### Dimensions (WxDxH)<sup>[3]</sup>

287 x 200 x 19.75 mm (11.3 x 7.9 x 0.78 inches)

### Weight<sup>[4]</sup>

Around 1.28 kg (2.82 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro, French / English

### Bundled Software

None

## CONNECTIVITY

### WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

### WWAN

Non-WWAN

### SIM Card

None

### Ethernet

No Onboard Ethernet

### Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1), with USB PD
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD and DisplayPort™
- 1x HDMI® 1.4
- 1x Headphone / microphone combo jack (3.5mm)

### Docking

Various docking solutions supported via USB-C®.

For more compatible docking solutions, please visit .

[Docking for Lenovo® 300w 2-in-1 Gen 5](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0 Enabled

### Fingerprint Reader

None

### Physical Locks

Kensington® Nano Security Slot™

### Other Security

Camera privacy shutter

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant

### Other Certifications

ASTM F963 test passed

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

TopSeller : No

Announce Date : 2025-04-07

EAN / UPC / JAN : 198156807434

End of Support : N/A



Product image is a sample, it may not match the real color of this model

Note:

[1] The storage capacity supported is based on the test.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

## Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38566)
BETTER	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0U55751)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0Q81869)

Please click [here](#) to view the full list of accessories.

