

## PERFORMANCE

### Processor

Intel® Core™ Ultra 9 285, 24C (8P + 16E) / 24T, Max Turbo up to 5.6GHz, 36MB Intel® Smart Cache

### AI PC Category<sup>[1]</sup>

AI-Ready Workstations

### Processor Sockets

1x FCLGA1851

### Integrated Graphics

Integrated Intel® Graphics

### Discrete Graphics

1x NVIDIA® RTX A1000 8GB

### Chipset

Intel® Q870 Chipset

### Memory

2x 32GB SODIMM DDR5-5600 Non-ECC

### Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

### Max Memory<sup>[2]</sup>

Up to 128GB (2x 64GB DDR5 CSODIMM)

### PCIe® NVMe® Controller

Integrated NVMe® controller

### PCIe® NVMe® Drive

1x 1TB SSD M.2 2280 PCIe® 5.0x4 Performance NVMe® Opal

### Audio Chip

High Definition (HD) Audio, Realtek® ALC233VB codec

### Power Supply

330W 90% Adapter

## DESIGN

### Keyboard

USB Traditional Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Case Color

Black

### Dust Filter

None

### Toolless Chassis Screw

None

### Mounting

None

### Stand

Vertical Stand

### Dimensions (WxDxH)<sup>[3]</sup>

179 x 182.9 x 37mm with rubber feet (7.0 x 7.2 x 1.5 inches with rubber feet)

### Weight<sup>[4]</sup>

1.4 kg (3 lbs, maximum configuration)

## CONNECTIVITY

### Onboard Ethernet

Intel® I219-LM, 1x GbE RJ-45

### Optional Ethernet

None

### WLAN + Bluetooth®

Intel® Wi-Fi® 7 BE200, 802.11be 2x2 + BT5.4, vPro®

### Front Ports

- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)

### Rear Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 3x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports Smart Power On
- 1x HDMI® 2.1 TMDS
- 1x DisplayPort™ 1.4
- 1x Ethernet (GbE RJ-45)

### Optional Rear Ports (configured)

4x miniDP 1.4a on NVIDIA® RTX A1000

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

### Physical Locks

Kensington® Security Slot™, 3 x 7 mm

### Cable Lock

No Cable

### Chassis Intrusion Switch

Chassis Intrusion Switch

## MANAGEABILITY

### System Management

Intel® vPro® Enterprise with Intel® AMT 16

## SERVICE

### Base Warranty

3-year, Onsite

### Included Upgrade

None

## CERTIFICATIONS

### ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

### Mil-Spec Test

MIL-STD-810H military test passed

## SOFTWARE

### Operating System

Windows® 11 Pro, English

### Bundled Software

None

## MODEL

TopSeller	: Yes	Announce Date	: 2025-07-15
EAN / UPC / JAN	: 199272034858	End of Support	: 2033-06-12



Product image is a sample, it may not match the real color of this model

### Note:

[1] With scalable configurations of higher-performance CPUs and professional NVIDIA RTX GPUs, in addition to advantage of the same modern AI PC technology, AI-Ready workstation power the demanding AI consumption & development workflows.

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The system dimensions may vary depending on configurations.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The Mount supports both 75x75mm and 100x100mm VESA. The VESA standard enabl...

## Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39273)
BETTER	3Y Premier Support Plus upgrade from 3Y Onsite (5WS1L39093)
GOOD	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26646)

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference