

PERFORMANCE

Display Size	34"
View Area	795.3x332.9 mm
Panel	OLED
Aspect Ratio	21:9
Resolution	3440x1440
Pixel Pitch	0.2310x0.2310 mm
Dot / Pixel Per Inch	110 dpi
View Angle (H / V)	178° / 178°
Response Time	0.03 ms
Color Support	1.07 Billion
Refresh Rate	240Hz
Brightness	275 cd/m ² (Typical, APL 100%), 450 cd/m ² (Max, APL 25%), 1300 cd/m ² (Peak, APL 1.5%)
Contrast Ratio	1500000:1
Color Gamut	99% sRGB, 98.5% DCI-P3
Screen Surface Treatment	Anti-glare
Curvature	800R
Speakers	5Wx2
Power Consumption (Typical / Maximum)	64W / 320W
Power Adapter	Integrated

DESIGN

Stand	Tilt, Swivel, Height Adjust Stand
Case Color	White and Black
Side Bezel Width	1.5 mm

Mounting	Supports VESA mount 100 x 100 mm
Dimensions (WxDxH) ^[1]	- Head Only 789.6 x 177.1 x 369.3 mm (31.09 x 6.97 x 14.54 inches) - Lowest Position 789.6 x 262.9 x 442.5 mm (31.09 x 10.35 x 17.42 inches) - Highest Position 789.6 x 262.9 x 577.5 mm (31.09 x 10.35 x 22.74 inches)
Packaging Dimensions (WxDxH)	940.0 x 282.0 x 475.0 mm (37.00 x 11.10 x 18.70 inches)
Weight ^[2]	- Monitor With Stand 8.7 kg (19.2 lbs) - Monitor Head Only 6.4 kg (14.1 lbs)
Packaging Weight	14.6 kg (32.3 lbs)

CONNECTIVITY

USB Port	1x USB-B (USB 5Gbps, USB upstream), 1x USB-C® (USB 5Gbps, USB upstream), 3x USB-A (USB 5Gbps, USB downstream), 2x USB-C® (USB 5Gbps, downstream)
Video Connector	1x HDMI® 2.1 FRL, 1x HDMI® 2.1 FRL with eARC, 1x DP 1.4 (HBR3), 1x USB-C® (DP 1.4 Alt Mode HBR3)
Network Connectivity	1x RJ45, Ethernet (10M/100M/1000M/2500M)

SERVICE

Base Warranty	3-year
---------------	--------

CERTIFICATIONS

Environmental Certification	RoHS, EU Energy Efficiency Level (Level-G), Volatile Organic Compound Certification
Ergonomic Certification	Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort (3 Stars), TÜV Rheinland® Flicker Free
Sync Technology	AMD FreeSync™ Premium Pro, Adaptive Sync

Special Features	- DisplayHDR™ TB400 - ClearMR 13000 - Factory Calibration: Avg. Delta E<2 at sRGB - Picture In Picture (PIP) / Picture By Picture (PBP) Support - NVIDIA® G-SYNC® Compatible - AMD FreeSync™ Premium Pro AMD FreeSync™ technology only can work with AMD Radeon™ series graphics card. - Lenovo® Artery (Lenovo® Accessories and Display Manager) Support Lenovo® Artery supports Windows® 10 & 11, Mac OS, and Windows® On Arm (functions vary across systems). Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center. Realtek® Dragon Software. - Adaptive Sync - Gaming Console Support - KVM Switch - Natural Low Blue Light - Smart Power The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device - Smart Sense Auto Ambient Brightness Sensor, Human Detection Sensor - True Split
------------------	---

SOFTWARE

Operating System	Support Windows® 10, Windows® 11
------------------	----------------------------------

ACCESSORIES

Video Cables	DP cable, USB-C® to USB-C® cable, HDMI® cable
--------------	---

MODEL

Product	: Lenovo® Legion™ Pro 34WD-10		
Announce Date	: 2024-12-06	Region	: NA
EAN / UPC / JAN	: 0198153820764 / 198153820764 / None		

Note:
^[1] The system dimensions may vary depending on configurations.
^[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>
To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference