

PERFORMANCE**Processor**

MediaTek Dimensity 6300 (8C, 2x A76 @2.4 GHz + 6x A55@2.0 GHz)

Graphics

Integrated Arm Mali-G57 MC2 GPU

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR4x

Storage

128GB UFS 2.2

Card Reader

microSD Card Slot

Max Storage Support

- 128GB UFS 2.2 on systemboard
- microSD card, supports up to 2TB (exFAT)

Speakers

4 speakers, optimized with Dolby Atmos®

Microphone

Mono

Camera

Front 5.0MP / Rear 8.0MP

VoiceCall^[1]

No

Vibration Motor

No support

Sensors

- Accelerometer sensor
- Ambient light sensor (ALS)
- Hall sensor

Battery

7040mAh (Typical)

Power Adapter

10V / 2A

DESIGN**Display^[2]**

11" 2.5K (2560x1600) IPS 500nits Anti-fingerprint, 72% NTSC, 90Hz, Touch

Touchscreen

In-cell, 10-point Multi-touch

Screen-to-Body Ratio

85%

Pen

Pen Bundled

Keyboard

None

Dimensions (WxDxH)^{[3][4]}

254.59 x 166.15 x 6.99 mm (10.02 x 6.54 x 0.28 inches)

Weight^[5]

480 g ± 10 g (1.06 lbs ± 0.02 lbs)

Case Color

Luna Grey

Case Material

Metal

SOFTWARE**Operating System^[6]**

Android™ 15 or Later

CONNECTIVITY**WLAN + Bluetooth**

Wi-Fi® 5, 802.11ac 1x1 + BT5.2

WWAN

Non-WWAN

Location Services

GPS + GLONASS + Galileo

Standard Ports

- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

SECURITY & PRIVACY**Fingerprint Reader**

None

SERVICE**Base Warranty^[7]**

1-year, Mail-in

ACCESSORIES**Bundled Accessories**

Lenovo® Tab Pen + Folio Case

CERTIFICATIONS**Green Certifications**

- ENERGY STAR® 9.0 (only available for TB336FU)
- ErP Lot 6/26
- RoHS compliant

Dust and Water Resistant

IP52

Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

Product : TB336FU

EAN / UPC / JAN: 198157039605

TopSeller : No

Announce Date: 2025-04-23



Product image is a sample, it may not match the real color of this model
Note:

[1] Use of Voice call requires cellular data plan. Voice call functionality details may vary based on local operator network, data and messaging services. Please contact your carriers for details.

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] The system dimensions may vary depending on configurations.

[4] The height is 8.29 mm (0.33 inches) with the camera bump.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

[7] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access

<https://support.lenovo.com/warrantylookup/warrantylookup>.

• Lenovo reserves the right to change specifications without notice.

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Folio Keyboard for IdeaTab
ZG38C07087



Lenovo TWS Earbuds (X9 Edition)-NA
Version 4XD1S14145



Please click [here](#) to view the full list of accessories.

Lenovo

PSREF
Product Specifications
Reference