



Poly Savi 8445 Office DECT 1920-1930 MHz Convertible Headset Customer Special 9 (B9GB6AA)

Overview

Built for the modern office

Ready for the modern office with an intuitive user interface on the universal base that can connect to almost any Savi headset. Ensure flexibility for users with the ability to connect from your computer, desk phone or mobile phone [1].

Be heard clearly

With the Poly Savi 8400 Office series headset system, you can stay focused on your tasks while enjoying crystal-clear conversations thanks to a noise-canceling microphone with close conversation limiting.

Multi-device connectivity

Designed for the modern office with 3-way connectivity, the Poly Savi 8400 office series is the perfect solution for business calls allowing you to stay connected in the office. You can even conference four headsets together with the base for increased productivity.

Untether from your desk

Enjoy the convenience of hands-free calling and a longer roaming range with the Poly Savi 8400 office series. With up to 13 hours of talk time and the ability to roam up to 590 ft / 180 m means you can keep the calls going, even away from the desk [2].

[1] Does not connect to the Savi 7200 headset.

[2] Line of sight from computer.

Specifications

Audio	Hybrid Active noise cancellation (ANC); Microphone noise cancellation with close conversation limiting
Weight	21 g
Weight	0.04 lb
Battery life	Unlimited talk and standby time
UPC number	198990726748
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Wireless headset; USB Type-A cable; USB Type-C® cable; Office base; AC power adapter; Charging cradle; Spare battery; Telephone interface cable (TIC); USB deluxe charger for spare battery; Convertible fit kit

Additional specifications

Base controls	Scroll wheel; Back key; USB softphone line button; Bluetooth® line button; Telephone interface line button; Configurable button
Battery type	Rechargeable Li-ion polymer
Bluetooth version	Bluetooth® Core 5.2
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-
Charge time	<3 hours
Color	Black
Compatibility	Compatible with PCs via DECT™, USB Type-A, USB Type-C® or RJ-11 cable
Compatible Operating Systems	Windows 11; Windows 10; macOS
Connection type	Wireless: DECT™, Bluetooth® (via office base); Wired: USB Type-A, USB Type-C®, RJ-11
Ear cushions	Artificial leather (surface material)
Impedance	32 ohms
Management Software	Poly Lens ^[1]
Microphone bandwidth	100 Hz to 10 kHz
Microphone type	Noise cancelling
Sensitivity (microphone)	112 dB SPL
Sensitivity (speaker)	118 dB SPL
Speaker bandwidth	100 Hz to 6.8 kHz (wideband mode); 20 Hz to 20 kHz (multimedia mode)
Speaker size	32 mm
Supported bluetooth profiles	A2DP; HFP; HSP
UNSPSC code	43191638
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] Requires downloadable software on [Poly.com/lens](https://poly.com/lens). Host PC requires Windows 10 or higher.

Audio

★ : Recommended

Audio Accessories

Poly APA-24 (ALCATEL) Electronic Hookswitch TAA	85Q52AA
Poly APC-43 Electronic Hookswitch TAA	85Q55AA
Poly APD-80 Electronic Hookswitch TAA	85Q58AA
Poly APN-91 Electronic Hookswitch TAA	85Q59AA
Poly APP-51 Electronic Hookswitch TAA	85Q60AA
Poly APS-11 Electronic Hookswitch TAA	85Q78AA
Poly APU-76 Electronic Hookswitch TAA	85R00AA
Poly APV-63 Electronic Hookswitch TAA	85R01AA
Poly Busy Light (Angle Plug)	920Q4AA
Poly EHS 3.5mm to 3.5mm Cable	85R17AA
Poly HL10 Handset Lifter	784Q1AA
Poly HL10 Handset Lifter TAA	8R713AA
Poly HL10 Handset Lifter with Straight Plug TAA	784Q2AA
Poly HL10 Lifter Arm +Ring Detector Accessory	8A7E3AA
Poly RD-1 Electronic Hookswitch	85R71AA
Poly Savi 740/745 Headband	85R31AA
Poly Savi 740/745 Neckband	85R32AA
Poly Savi 8200 5 Unit Charge Base	85R34AA
Poly Savi 8240/8245 Battery	85R41AA
Poly Savi 8240/8245 Deluxe Charging Cradle	85R44AA
Poly Savi 8240/8245 Fit	85R45AA
Poly Savi 8240/8245 Foam Sleeves for Earloop (20 Pieces)	85Q65AA
Poly Savi 8240/8245 Standard Charging Cradle	85R47AA
Poly Savi 8240/8245 USB-A Charging Cable for Headset and Battery	85R43AA
Poly Savi 8245 Deluxe Cradle with Battery	85R49AA
Poly Savi 8245 Headset Cradle and Wearing Accessories	85T32AA
Poly Savi 8400/7400 Office DECT 1880-1900 MHz Base	8L569AA
Poly Savi 8400/7400 Office DECT 1920-1930 MHz Base	8L571AA
Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1880-1900 MHz Base	8L558AA

Poly Savi 8400/7400 Office Microsoft Teams Certified DECT 1920-1930 MHz Base	8L562AA
Poly Savi 8410/8420 Office Charging Cradle	8L573AA
Poly Savi 8440/8445 Office Charging Cradle	8L577AA
Poly Savi D400 DECT 1920-1930 MHz Dongle	8L550AA
Poly Savi D400 Microsoft Teams Certified DECT 1920-1930 MHz Dongle	8L552AA
Poly Savi D400 UC DECT 1880-1890 MHz Dongle	8J8V9AA
Poly Savi D400 UC DECT 1880-1900 MHz Dongle	8J8V7AA
Poly Savi D400 UC DECT 1893-1906 MHz Dongle	8J8V6AA
Poly Savi D400 UC DECT 1920-1930 MHz Dongle	85T33AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1880-1900 MHz Dongle	8J8W1AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1893-1906 MHz Dongle	8J8W0AA
Poly Savi D400 UC Microsoft Teams Certified DECT 1920-1930 MHz Dongle	85T34AA
Poly Savi Office Power Supply with Right Angled Plug -9V 1000mA	8L5A2AA
Poly Savi Office S2 Telephone Cable	85R55AA
Poly Savi Office Straight Plug Online Indicator	85R52AA
Poly Savi Office Telephone Interface Cable	85R57AA
Poly Savi Office Universal AC Power Supply with Straight Plug -9V 1000mA	85R59AA
Poly USB-A to USB-C Adapter	85Q48AA
Poly USB-C to USB-A Adapter	85Q49AA

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Aug 04, 2025 7:54 AM UTC+0000