

PERFORMANCE**Processor**

Intel® Xeon® w3-2425, 6C (6P + OE) / 12T, 3 / 4.4GHz, 15MB

AI PC Category^[1]

AI-Ready Workstations

Processor Sockets

1x FCLGA4677

Discrete Graphics

1x NVIDIA® RTX 2000 Ada Generation 16GB

Chipset

Intel® W790 Chipset

Memory^[2]

4x 16GB RDIMM DDR5-4800 ECC

Memory Slots

8 DDR5 DIMM slots, 4 channels capable

Max Memory^[3]

Up to 512GB (8x 64GB RDIMM)

PCIe® NVMe® Controller

Integrated NVMe® Controller, non-RAID

PCIe® NVMe® Drive

1x 2TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal

SATA Controller

Onboard Intel® RSTe SATA

SATA/SAS Drive

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC897-Q codec

Power Supply

1000W Platinum Fixed

DESIGN**Keyboard**

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Expansion Slots

Supports 6 PCIe® slots with 2x PCIe® 5.0 slots and 4x PCIe® 4.0 slots.

- Slot 1: PCIe® 5.0 x16, full height, full length, 75W, double-width, by CPU
- Slot 2: PCIe® 4.0 x4, full height, full length, 25W, by PCH
- Slot 3: PCIe® 5.0 x16, full height, full length, 75W, double-width, by CPU
- Slot 4: PCIe® 4.0 x4, full height, full length, 25W, by PCH
- Slot 5: PCIe® 4.0 x8, full height, full length, 25W, by CPU
- Slot 6: PCIe® 4.0 x4, full height, full length, 25W, by PCH

Dimensions (WxDxH)^[4]

165 x 453.9 x 446 mm (6.5 x 17.9 x 17.6 inches, with feet)

Weight^[5]

19 kg (41.9 lbs, maximum configuration)

CONNECTIVITY**Onboard Ethernet**

Intel® I219-LM, 1x GbE RJ-45

Optional Ethernet

None

WLAN + Bluetooth®^[6]

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.1, vPro®

Card Reader

15-in-1 Card Reader

Front Ports

1x headphone / microphone combo jack (3.5mm)

Optional Front Ports (configured)

- 2x USB-C® 3.2 Gen 2
- 2x USB 3.2 Gen 2

Rear Ports^[7]

- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 3x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x Ethernet (GbE RJ-45)
- 1x line-in (3.5mm)
- 1x line-out (3.5mm)

Optional Rear Ports (configured)

None

SECURITY & PRIVACY**Security Chip**

Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks

- Access panel lock kit with common key
- Kensington® Security Slot™, 3 x 7 mm

Cover Lock

Lock Kit with Common Key

Chassis Intrusion Switch

Chassis Intrusion Switch

MANAGEABILITY**System Management^[8]**

Intel® vPro® Enterprise with Intel® AMT 16

Diagnostic

Front Diagnostic Panel with QR code

SERVICE**Base Warranty**

3-year, Onsite

Included Upgrade

3Y Premier Support Upgrade from 3Y Onsite

CERTIFICATIONS**ISV Certifications**Please visit [ISV certifications for Lenovo® Workstations](#)**SOFTWARE****Operating System**

Windows® 11 Pro for Workstations, English

Bundled Software

None

MODEL**TopSeller** : Yes**Announce Date** : 2025-04-29**EAN / UPC / JAN** : 198158866613**End of Support** : 2031-05-03

Product image is a sample, it may not match the real color of this model

Note:

[1] With scalable configurations of higher-performance CPUs and professional NVIDIA RTX GPUs, in addition to advantage of the same modern AI PC technology, AI-Ready workstation power the demanding AI consumption & development workflows.

[2] System comes with DDR5-4800 memory and some configurations will run at 4400 MT/s due to the memory support capability of processor.

[3] The max memory is based on the test results with current Lenovo memory offerings.

[4] The system dimensions may vary depending on configurations.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] Bluetooth 5.3 is hardware ready but may run at a lower version due to OS limitations.

Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

[7] For video ports on discrete graphics, please see.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management



Technical Account Managers for proactive relationship and escalation management



Priority on service delivery and repair parts



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39074)
GOOD	4Y Premier Support upgrade from 3Y Premier Support (5WS0W86673)

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference