

PERFORMANCE**Display Size**

34"

View Area

797.2x333.7 mm

Panel

Vertical Alignment

Backlight

WLED

Aspect Ratio

21:9

Resolution

3440x1440

Pixel Pitch

0.2318x0.2318 mm

Dot / Pixel Per Inch

110 dpi

View Angle (H / V)

178° / 178°

Response Time

4ms (Extreme mode) / 6ms (Normal mode)

Color Support

16.7 Million

Refresh Rate

48Hz - 120Hz

Brightness300 cd/m²**Contrast Ratio**

3000:1

Color Gamut

99% sRGB, 99% BT.709

Screen Surface Treatment

Anti-glare

Curvature

1500R

Camera

Modular Camera Support

Microphone

None

Speakers

Modular Speaker Support

Power Consumption (Typical / Maximum)

30W / 200W

Power Adapter

Integrated

Touchscreen

None

Smart System

None

DESIGN**Stand**

Tilt, Swivel, Height Adjust Stand

Case Color

Eclipse Black

Side Bezel Width

2 mm

Mounting

Supports VESA mount 100 x 100 mm

ThinkCentre® M Series Support

Tiny Support

Pen

None

Dimensions (WxDxH)^[1]

- Head Only | 806.1 x 114.7 x 356.5 mm (31.74 x 4.52 x 14.04 inches)
- Lowest Position | 806.1 x 220.0 x 390.4 mm (31.74 x 8.66 x 15.37 inches)
- Highest Position | 806.1 x 220.0 x 545.4 mm (31.74 x 8.66 x 21.47 inches)

Packaging Dimensions (WxDxH)

980.0 x 186.0 x 495.0 mm (38.58 x 7.32 x 19.49 inches)

Weight^[2]

- Monitor With Stand | 9.2 kg (20.3 lbs)
- Monitor Head Only | 6.4 kg (14.1 lbs)

Packaging Weight

13.7 kg (30.3 lbs)

CONNECTIVITY**USB Port**

1x USB-C® (USB 5Gbps, USB upstream), 3x USB-A (USB 5Gbps, USB downstream), 1x USB-C® (USB 5Gbps, PD 15W, USB downstream)

Video Connector

1x HDMI® 2.1 TMDS, 1x DP 1.4 (HBR2), 1x USB-C® (5Gbps, DP 1.4 Alt Mode HBR2)

Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M)

SERVICE**Base Warranty**

3-year

CERTIFICATIONS**Environmental Certification**

ENERGY STAR® Certified, TCO 10, TCO Edge 2.1, EU Energy Efficiency Level (Level-E), EPEAT™ Gold

Ergonomic Certification

Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free, TÜV Rheinland® Eye Comfort (5 Stars)

Sync Technology

None

Special Features

- HDR10 Compliance
- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support
- Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS (functions vary across systems).
- Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- LDFM (Lenovo® Display Fleet Manager)
- Mirrored Power Button
- Natural Low Blue Light
- Smart Power

SOFTWARE**Operating System**

Support Windows® 10, Windows® 11

ACCESSORIES**Video Cables**

USB-C® to USB-C® cable, DP cable

MODEL

Announce Date : 2025-04-16

Region : NA

EAN / UPC / JAN : 0198155878657 / 198155878657 / None

Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkVision MC60 Monitor Webcam

4XC1J05150

Take your virtual meetings to the next level. The ThinkVision MC60 Monitor Webcam is an intuitive webcam that offers the most stunning video quality—full 1080p resolution designed to fit on your monitor seamlessly. Ca...



Lenovo Essential FHD Webcam

4XC1B34802

The Lenovo FHD Webcam is powered by a Full HD 1080P 2 Megapixel CMOS camera that allows your friends, family, and colleagues to see you as clear as day, even when they are worlds away. With full stereo dual-mics that ...

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference