

PERFORMANCE**Display Size**

27"

View Area

597.9x336.3 mm

Panel

In-Plane Switching

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.3114x0.3114 mm

Dot / Pixel Per Inch

82 dpi

View Angle (H / V)

178° / 178°

Response Time

4ms GtG (Extreme mode) / 6ms GtG (Typical mode)

Color Support

16.7 Million

Refresh Rate

100Hz

Brightness300 cd/m²**Contrast Ratio**

1500:1

Color Gamut

99% sRGB

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Camera

None

Microphone

None

Speakers

2Wx2

Power Consumption (Typical / Maximum)

16.3W / 34W

Power Adapter

Integrated

DESIGN**Stand**

Tilt, Swivel, Pivot, Height Adjust Stand

Case Color

Raven Black

Side Bezel Width

2.3 mm

Mounting

Supports VESA mount 100 x 100 mm

ThinkCentre M Series Support

Tiny Support

Dimensions (WxDxH)^[1]

• Lowest Position | 613.1 x 220 x 383.5 mm (24.14 x 8.66 x 15.1 inches)

• Highest Position | 613.1 x 220 x 538.5 mm (24.14 x 8.66 x 21.2 inches)

• Head Only | 613.1 x 40.4 x 366.4 mm (24.14 x 1.59 x 14.43 inches)

Packaging Dimensions (WxDxH)

695.0 x 155.0 x 447.0 mm (27.36 x 6.10 x 17.60 inches)

Weight^[2]

• Monitor With Stand | 6.2 kg (13.7 lbs)

• Monitor Head Only | 4.0 kg (8.8 lbs)

Packaging Weight

• EPS: 7.9 kg (17.4 lbs)

• Pulp: 8.5 kg (18.7 lbs)

CONNECTIVITY**USB Port**

None

Video Connector1x HDMI[®] 1.4, 1x DP 1.2, 1x VGA**Network Connectivity**

None

SERVICE**Base Warranty**

3-year

CERTIFICATIONS**Environmental Certification**ENERGY STAR[®] Certified, TCO 10, TCO Edge 2.1, EPEAT[™] Gold, EU Energy Efficiency Level (Level-D), Volatile Organic Compound Certification, RoHS**Ergonomic Certification**TÜV Low Blue Light (Hardware solution), TÜV Rheinland[®] Flicker Free**Sync Technology**


None

Special Features

Natural Low Blue Light

SOFTWARE**Operating System**Support Windows[®] 10, Windows 11**ACCESSORIES****In the Box**

- Monitor with stand
- 1x HDMI[®] 1.4 cable (1.8m)
- 1x Power cable (1.8m)
- 4x Screws
- Quick setup guide

MODEL**Region** : NA**EAN / UPC / JAN**: 0198157546813 / 198157546813 / None**Announce Date** : 2025-07-02

Product image is a sample, it may not match the real color of this model
Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

• Lenovo reserves the right to change specifications without notice.

• California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

Premium Care - Advanced Support from Real People. Real Fast.




REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.



Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference