

PERFORMANCE

Processor

Intel® Core™ i3-N305 (8C / 8T, Max Turbo up to 3.8GHz, 6MB)

Graphics

Integrated Intel® Graphics

Chipset

Intel® SoC Platform

Memory

1x 16GB SO-DIMM DDR5-5600

Memory Slots

One DDR5 SO-DIMM slot

Max Memory^{[1][2]}

Up to 16GB DDR5-5600

Storage

512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Max Storage Support^[3]

One drive, up to 512GB M.2 SSD

Card Reader

No card reader

Optical

None

Audio Chip

High Definition (HD) Audio

Speakers

2Wx1

Power Supply^[4]

65W 89% Adapter

DESIGN

Keyboard

USB, Calliope, Black, English (US)

Mouse

USB Calliope Mouse, Black

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Case Color

Black

Stand

Vertical Stand

Adapter Cage

None

Toolless Chassis Screw

None

Dust Filter

None

Mounting

None

IO Box

None

Pen

Pen Not Supported

Form Factor

Tiny (1L)

Dimensions (WxDxH)^[5]

- Tiny only (without rubber feet) | 179 x 182.9 x 34.5 mm (7.05 x 7.2 x 1.36 inches)
- Tiny only (with rubber feet) | 179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)

Weight^[6]

Around 0.89 kg (1.96 lbs)

CONNECTIVITY

WLAN + Bluetooth®

Intel® Wi-Fi® 6 AX203, 802.11ax 2x2 + BT5.2

WWAN

Non-WWAN

Ethernet

Integrated 100/1000M

Front Ports

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (Hi-Speed USB / USB 2.0), one supports Smart Power On
- 1x HDMI® 1.4
- 1x DisplayPort™ 1.4
- 1x Ethernet (RJ-45)

Optional Rear Ports (configured)

None

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 integrated in SoC

Fingerprint Reader

No fingerprint reader

Physical Locks

Kensington® Security Slot™, 3 x 7 mm

Kensington® Cable Lock

None

Chassis Intrusion Switch

Chassis intrusion switch

MANAGEABILITY

System Management

None

SERVICE

Base Warranty

1-year, Onsite

Included Upgrade

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- ErP Lot 3/7
- GREENGUARD®
- RoHS compliant
- VOC Report

SOFTWARE

Operating System

Windows® 11 IoT Enterprise LTSC 2024, English

Bundled Software

None

ACCESSORIES

Bundled Accessories

None

MODEL

TopSeller : Yes

Announce Date : 2025-10-06

EAN / UPC / JAN : 199272779643

End of Support : 2032-04-30



Product image is a sample, it may not match the real color of this model

· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The Mount supports both 75x75mm and 100x100mm VESA. The VESA standard enabl...



ThinkCentre Tiny Sandwich Kit II

4XHON04098

The ThinkCentre Tiny Sandwich Kit II is a mechanical bracket which can mount your ThinkCentre Tiny PC between monitor and ThinkCentre Extend Arm. The Tiny Sandwich kit enables more desktop and floor space while provid...

Please click [here](#) to view the full list of accessories.

Lenovo

PSREF
Product Specifications
Reference