

### PERFORMANCE

- Display Size**  
27"
- View Area**  
596.7x335.7 mm
- Panel**  
In-Plane Switching
- Backlight**  
WLED
- Aspect Ratio**  
16:9
- Resolution**  
2560x1440
- Pixel Pitch**  
0.2331x0.2331 mm
- Dot / Pixel Per Inch**  
109 dpi
- View Angle (H / V)**  
178° / 178°
- Response Time**  
4ms GtG (Extreme mode) / 6ms GtG (Typical mode)
- Color Support**  
16.7 Million
- Refresh Rate**  
48Hz - 120Hz
- Brightness**  
350 cd/m<sup>2</sup>
- Contrast Ratio**  
1500:1
- Color Gamut**  
99% sRGB, 99% BT.709
- Screen Surface Treatment**  
Anti-glare
- Curvature**  
Flat Panel
- Camera**  
Modular Camera Support
- Microphone**  
None
- Speakers**  
Modular Speaker Support
- Power Consumption (Typical / Maximum)**  
17W / 90W
- Power Adapter**  
Integrated
- Touchscreen**  
None

- Smart System**  
None
- DESIGN**
- Stand**  
Tilt, Swivel, Pivot, Height Adjust Stand
- Case Color**  
Eclipse Black
- Side Bezel Width**  
2 mm
- Mounting**  
Supports VESA mount 100 x 100 mm
- ThinkCentre® M Series Support**  
Tiny Support

- Pen**  
None
- Dimensions (WxDxH)<sup>[1]</sup>**
  - Lowest Position | 613.6 x 195.0 x 384.3 mm (24.16 x 7.68 x 15.13 inches)
  - Highest Position | 613.6 x 195.0 x 539.3 mm (24.16 x 7.68 x 21.23 inches)
  - Head Only | 613.6 x 46.0 x 357.1 mm (24.16 x 1.81 x 14.06 inches)
- Packaging Dimensions (WxDxH)**  
613.6 x 195.0 x 539.3 mm (24.16 x 7.68 x 21.23 inches)
- Weight<sup>[2]</sup>**
  - Monitor With Stand | 6.5 kg (14.3 lbs)
  - Monitor Head Only | 4.3 kg (9.6 lbs)

- Packaging Weight**  
Models without ThinkVision® VoIP Stack MC60 Monitor Webcam: 9.1 kg (20.1 lbs)

### CONNECTIVITY

- USB Port**  
3x USB-A (USB 5Gbps), 1x USB-C® (USB 5Gbps, PD 15W), 1x USB-B (USB 5Gbps, USB upstream)
- Video Connector**  
1x HDMI® 2.1 TMDS, 1x DP 1.4 (HBR2)
- Network Connectivity**  
None

### SERVICE

- Base Warranty**  
3-year

### CERTIFICATIONS

- Environmental Certification**  
ENERGY STAR® Certified, TCO 10, TCO Edge 2.1, EPEAT™ Gold, RoHS, EU Energy Efficiency Level (Level-D)

- Ergonomic Certification**  
Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort (5 Stars)
- Sync Technology**  
None
- Special Features**
  - HDR10 Compliance
  - Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support  
Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS (functions vary across systems).  
Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
  - LDFM (Lenovo® Display Fleet Manager)
  - Natural Low Blue Light

### SOFTWARE

- Operating System**  
Support Windows® 10, Windows® 11

### ACCESSORIES

- Video Cables**  
HDMI® cable, USB-A to USB-B cable

### MODEL

- Announce Date** : 2025-04-02      **Region** : APS
- EAN / UPC / JAN** : 0198155827921 / 198155827921 / None



Product image is a sample, it may not match the real color of this model

Note:  
 [1] The system dimensions may vary depending on configurations.  
 [2] The system weight is approximate and based on results in.....  
 · Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo Essential FHD Webcam

4XC1B34802

The Lenovo FHD Webcam is powered by a Full HD 1080P 2 Megapixel CMOS camera that allows your friends, family, and colleagues to see you as clear as day, even when they are worlds away. With full stereo dual-mics that ...



### Lenovo Performance FHD Webcam

4XC1D66055

A USB Video Class (UVC) compliant video camera designed for teleconferencing applications on desktop or laptop. It's a reliable digital video device to transfer video data with HD quality through a high-speed USB inte...

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference