

PERFORMANCE

Processor

MediaTek Helio G85 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)

Graphics

Integrated Arm Mali-G52 MC2 GPU

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR4x

Storage

64GB eMMC 5.1

Card Reader

microSD Card Slot

Max Storage Support

- 64GB eMMC 5.1 on systemboard
- microSD card, supports up to 1TB

Speakers

2 side speakers, optimized with Dolby Atmos®

Microphone

Mono

Camera

Front 2.0MP / Rear 8.0MP

VoiceCall

No

Vibration Motor

No support

Sensors

- Accelerometer sensor
- Hall sensor
- Virtual light sensor

Battery^[1]

5100mAh (Typical)

Power Adapter

None

DESIGN

Display^[2]

8.7" HD (1340x800) IPS 480nits Anti-fingerprint, 60% NTSC, 60Hz, Touch

Touchscreen

In-cell, 10-point Multi-touch

Screen-to-Body Ratio

86%

Pen

Pen Not Supported

Keyboard

None

Dimensions (WxDxH)^{[3][4]}

211 x 124.8 x 8.5 mm (8.31 x 4.91 x 0.33 inches)

Weight^[5]

Around 320 g (0.71 lbs)

Case Color

Luna Grey

Case Material

Plastic

SOFTWARE

Operating System^[6]

Android™ 14 or Later

CONNECTIVITY

WLAN + Bluetooth®

Wi-Fi® 5, 802.11ac 1x1 + BT5.3

WWAN

Non-WWAN

Location Services

GPS + GLONASS + Galileo + Beidou

Standard Ports

- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging, digital audio
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

SERVICE

Base Warranty^[7]

1-year, Mail-in

ACCESSORIES

Bundled Accessories

Folio Case

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0 (only available for TB305FU)
- ErP Lot 6/26
- RoHS compliant

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

Product	: TB305FU	Announce Date	: 2025-02-18
TopSeller	: No		
EAN / UPC / JAN	: 198157171930		



Product image is a sample, it may not match the real color of this model

Note:

[1] Support 15W quick charge

[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[3] The system dimensions may vary depending on configurations.

[4] The height is 9.45 mm (0.37 inches) with the camera bump.

[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[6] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

[7] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Folio Case for Lenovo Tab One

ZG38C06914

Protect your Lenovo Tab One with all-around coverage and enjoy hands-free entertainment anytime.



Lenovo Folio Case for Lenovo Tab One

ZG38C06922

Protect your Lenovo Tab One with all-around coverage and enjoy hands-free entertainment anytime.

Please click [here](#) to view the full list of accessories.

Lenovo

PSREF
Product Specifications
Reference