

## PERFORMANCE

### Processor

MediaTek Dimensity 6300 (8C, 2x A76 @2.4GHz + 6x A55@2.0GHz)

### Graphics

Integrated Arm Mali-G57 MC2 GPU

### Chipset

MediaTek SoC Platform

### Memory

8GB Soldered LPDDR4x

### Storage

128GB UFS 2.2

### Card Reader

microSD Card Slot

### Max Storage Support

- 128GB UFS 2.2 on systemboard
- microSD card, supports up to 2TB (exFAT)

### Speakers

4 speakers, optimized with Dolby Atmos®

### Microphone

Mono

### Camera

Front 8.0MP / Rear 13.0MP with Flashlight

### VoiceCall

No

### Vibration Motor

No support

### Sensors

- Accelerometer sensor
- Ambient light sensor (ALS)
- Hall sensor

### Battery

7040mAh (Typical)

### Power Adapter

10V / 2A

## DESIGN

### Display<sup>[1]</sup>

11" 2.5K (2560x1600) IPS 500nits Anti-fingerprint, 72% NTSC, 90Hz, Touch

### Touchscreen

In-cell, 10-point Multi-touch

### Screen-to-Body Ratio

85%

### Pen

Pen Upgradable (Purchase Separately)

### Keyboard

None

### Dimensions (WxDxH)<sup>[2][3]</sup>

254.59 x 166.15 x 6.99 mm (10.02 x 6.54 x 0.28 inches)

### Weight<sup>[4]</sup>

480 g ± 10 g (1.06 lbs ± 0.02 lbs)

### Case Color

Luna Grey

### Case Material

Metal

## SOFTWARE

### Operating System<sup>[5]</sup>

Android™ 15 or Later

## CONNECTIVITY

### WLAN + Bluetooth

Wi-Fi® 5, 802.11ac 1x1 + BT5.2

### WWAN

Non-WWAN

### SIM Card

No Support

### Location Services

GPS + GLONASS + Galileo

### Standard Ports

- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

## SERVICE

### Base Warranty<sup>[6]</sup>

1-year, Mail-in

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 9.0 (only available for TB336FU)
- ErP Lot 6/26
- RoHS compliant

### Dust and Water Resistant

IP52

### Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

## MODEL

**Product** : TB336FU **TopSeller** : Yes  
**EAN / UPC / JAN**: 199272786962 **Announce Date**: 2025-09-19

Product image is a sample, it may not match the real color of this model

### Note:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[2] The system dimensions may vary depending on configurations.

[3] The height is 8.29 mm (0.33 inches) with the camera bump.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[5] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

[6] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access

<https://support.lenovo.com/warrantylookup/warrantylookup>.

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.

- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through phone, chat, or email - our expert technicians will take care of your device issues.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

## Base Warranty - Included with the system you purchase with default 1-year coverage window.

## Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service\*

\*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories

 United States of America



Lenovo Folio Keyboard for IdeaTab  
ZG38C07087



Lenovo Idea Tab Folio Case ZG38C06984



Lenovo Tab Pen Plus ZG38C05194

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference