

## PERFORMANCE

### Processor

Intel® Core Ultra 7 255H, 16C (6P + 8E + 2LPE) / 16T, Max Turbo up to 5.1GHz, 24MB Intel Smart Cache

### AI PC Category

AI-Ready Workstations

### NPU

Integrated Intel® AI Boost, up to 13 TOPS

### Graphics

NVIDIA® RTX PRO 500 Blackwell Generation 6GB GDDR7 Laptop GPU

### Chipset

Intel® SoC Platform

### Memory

1x 32GB SODIMM DDR5-5600 Non-ECC

### Memory Slots

Two DDR5 SODIMM / CSODIMM slots, dual-channel capable

### Max Memory

Up to 96GB (2x 48GB DDR5 CSODIMM)

### Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

### Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

### Max Storage Support<sup>[1]</sup>

Up to one 2TB M.2 2280 Gen 5 Performance SSD

### Card Reader

No card reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby Audio™

### Microphone

2x, Array

### Camera

5.0MP + IR with Privacy Shutter and Human Presence Detection

### Battery

57Wh

### Power Adapter

100W USB-C® Slim (3-pin)

## DESIGN

### Display

14.5" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, 60Hz, Eyesafe®, TÜV Low Blue Light, Touch

### Touchscreen

Add-on Film Touch, 10-point Multi-touch

### Screen-to-Body Ratio

88%

### Color Calibration

AICCP Color Calibration

### Pen

Pen Not Supported

### Keyboard

Backlit, English

### Dimensions (WxDxH)<sup>[2]</sup>

325.5 x 227.6 x 11.2 / 15.1 (front / rear), 21.7 (maximum) mm 12.81 x 8.96 x 0.44 / 0.59 (front / rear), 0.85 (maximum) inches

### Weight<sup>[3]</sup>

- Models with integrated graphics | Starting at 1.60 kg (3.53 lbs)
- Models with discrete graphics | Starting at 1.64 kg (3.61 lbs)

### Case Color

Black

### Case Material

Aluminium (Top), Aluminium (Bottom)

## SOFTWARE

### Operating System

Windows® 11 Pro, English (US) / English (UK)

### Bundled Software

Lenovo® AI Now

## CONNECTIVITY

### WLAN + Bluetooth

Intel® Wi-Fi® 7 BE201, 802.11be 2x2 + BT5.4

### WWAN

WWAN Not Supported

### SIM Card

None

### Ethernet

100/1000M (RJ-45)

### Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x Thunderbolt™ 4, with USB PD 3.0
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (GbE RJ-45)
- 1x Security keyhole

### Docking

Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit [Docking for ThinkPad P14s Gen 6 \(Intel\)](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0 Enabled

### Physical Locks

Kensington® Nano Security Slot, 2.5 x 6 mm

### Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

### Other Security

- Bottom cover tamper detection
- Camera privacy shutter
- Ultrasonic Human Presence Detection for IR camera
- IR camera for Windows® Hello (facial recognition)

## MANAGEABILITY

### System Management

Non-vPro®

## SERVICE

### Base Warranty

3-year, Courier or Carry-in with 1-year Battery

### Included Upgrade

3Y Premier Support Upgrade from 3Y Courier/Carry-in

## ACCESSORIES

## CERTIFICATIONS

### ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

### Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified, generation 10

### Mil-Spec Test

MIL-STD-810H military test passed

### Other Certifications

- Eyesafe® Certified 2.0
- TÜV Rheinland® Low Blue Light

## MODEL

TopSeller : Yes EAN / UPC / JAN: 199272955955

Announce Date: 2025-09-13 End of Support : 2032-04-03

- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice. To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams) 4XD1S19778



Lenovo 350 Bluetooth Silent Mouse (Fan Edition - Brazil) GY51U71760

Please click [here](#) to view the full list of accessories.

## Recommended Services

BEST	5Y Premier Support upgrade from 3Y Premier Support (5WS1H31773)
BETTER	4Y Premier Support upgrade from 3Y Premier Support (5WS1H31743)

**Lenovo**

**PSREF**  
Product Specifications  
Reference