

PERFORMANCE

Processor

AMD Ryzen™ 7 250 (8C / 16T, 3.3 / 5.1GHz, 8MB L2 / 16MB L3)

AI PC Category

AI PC^[1]

NPU

Integrated AMD Ryzen™ AI, up to 16 TOPS

Graphics

Integrated AMD Radeon™ 780M Graphics

Chipset

AMD SoC Platform

Memory

2x 16GB SODIMM DDR5-5600

Memory Slots

Two DDR5 SODIMM slots, dual-channel capable

Max Memory^[2]

Up to 64GB DDR5-5600

Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Slot

Two M.2 slots • One M.2 2242 PCIe® 4.0 x4 slot • One M.2 2280 PCIe 4.0 x4 slot

Max Storage Support^[3]

Up to two drives, 2x M.2 SSD • M.2 2242 SSD up to 2TB • M.2 2280 SSD up to 2TB

Card Reader

SD Card Reader

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Audio™

Microphone

2x, Array

Camera

FHD 1080p + IR Hybrid with Privacy Shutter

Battery

48Wh

Power Adapter

65W USB-C® (3-pin)

Special Features

Modern Standby

DESIGN

Display

14" WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC, 60Hz^[4]

Touchscreen

None

Screen-to-Body Ratio

90%

Color Calibration

No Color Calibration

Pen

Pen Not Supported

Keyboard

Backlit, English

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

Dimensions (WxDxH)^[5]

313.5 x 224 x 17.5 mm (12.34 x 8.82 x 0.69 inches)

Weight^[6]

Starting at 1.36 kg (2.99 lbs)

Case Color

Arctic Grey

Case Material

Aluminium (Top), PC-ABS (Bottom)

Surface Treatment

Anodizing Sandblasting (Top), Texture (Bottom)

SOFTWARE

Operating System

Windows® 11 Pro, English (US) / English (UK)

Bundled Software

Office Trial + Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth

Wi-Fi® 6, 802.11ax 2x2 + BT5.2

WWAN

WWAN Not Supported

Ethernet

100/1000M (RJ-45)

Standard Ports

- 1x USB-A (USB 5Gbps), Always On
- 1x USB-A (USB 5Gbps)
- 2x USB-C® (USB4® 40Gbps), with USB PD 45-65W and DisplayPort™ 1.4a
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x SD card reader

Docking

Various docking solutions supported via USB-C®. For more compatible docking solutions, please visit [Docking for ThinkBook 14 G9 AHP](#)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0 Enabled

Physical Locks

Kensington® Nano Security Slot, 2.5 x 6 mm

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

SERVICE

Base Warranty

1-year, Courier or Carry-in

Included Upgrade

1Y Onsite upgrade from 1Y Courier/Carry-in, CO2 Offset 0.5 ton (2nd Generation Carbon Offset Projects)

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

TopSeller : Yes EAN / UPC / JAN: 199274387792

Announce Date: 2025-12-26 End of Support : 2032-06-14

Note:

- [1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.
- [2] Maximum memory 64GB DDR5-5600 is only to test technical readiness of notebook. Available memory to sell would vary.
- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice. To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

 United States of America



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams) 4XD1S19778



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498

Please click [here](#) to view the full list of accessories.

Recommended Services

BEST	4Y Premier Support for AIPC upgrade from 1Y Onsite (5WS1U93928)
BETTER	3Y Premier Support for AIPC upgrade from 1Y Onsite (5WS1U93927)
GOOD	3Y Onsite upgrade from 1Y Onsite (5WS0K27114)

Lenovo

PSREF
Product Specifications
Reference