

PERFORMANCE**Display Size**

64.5"

View Area

1428.5x803.5 mm

Panel

In-Plane Switching

Backlight

DLED

Aspect Ratio

16:9

Resolution

3840x2160

Pixel Pitch

0.372x0.372 mm

Dot / Pixel Per Inch

68 dpi

View Angle (H / V)

178° / 178°

Response Time

8ms

Color Support

1.07 Billion

Refresh Rate

60Hz

Brightness400 cd/m²**Contrast Ratio**

5000:1

Color Gamut

72% NTSC, 75% DCI-P3, 95% sRGB

Screen Surface Treatment

Anti-glare

Curvature

Flat Panel

Camera

None

Microphone

None

Speakers

10Wx2

Power Consumption (Typical / Maximum)

110W / 380W

Power Adapter

Integrated

Touchscreen

None

Smart System

None

DESIGN**Stand**

Tilt support

Case Color

Black

Side Bezel Width

1.9 mm

Mounting

Supports VESA mount 300 x 300 mm

ThinkCentre® M Series Support

None

Pen

None

Dimensions (WxDxH)^[1]

1446.3 x 126 x 847 mm / 56.94 x 4.96 x 33.35 inches

Packaging Dimensions (WxDxH)

1620.0 x 188.0 x 945.0 mm (63.78 x 7.41 x 37.21 inches)

Weight^[2]

25.1 kg (55.4 lbs.)

Packaging Weight

31.4 kg (69.2 lbs)

CONNECTIVITY**USB Port**

4x USB-A (USB 5Gbps), 1x USB-C® (USB 5Gbps, PD 15W), 1x USB-B (USB 5Gbps, USB upstream), 1x USB-C® (USB 10Gbps, 96W PD3.1, USB upstream)

Video Connector

2x HDMI® 2.1 TMDS, 1x DP 1.4, 1x DP 1.4 out, 1x USB-C® (DP 1.4 Alt Mode HBR3)

Network Connectivity

1x RJ45, Ethernet (10M/100M/1000M)

SERVICE**Base Warranty**

3-year

CERTIFICATIONS**Environmental Certification**

ENERGY STAR® Certified, EPEAT™ Silver, RoHS, EU Energy Efficiency Level (Level-F)

Ergonomic Certification

TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Flicker Free

Sync Technology

None

Special Features

- HDR10 Compliance
- Picture In Picture (PIP) / Picture By Picture (PBP) Support
- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support
- Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS (functions vary across systems).
- Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center.
- AI Power Saving (5%)
- DaisyChain Support (Up to 4)
- Hardware Low Blue Light
- KVM Switch
- Smart Power

The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device

SOFTWARE**Operating System**

Support Windows® 10, Windows® 11

ACCESSORIES**Video Cables**

USB-C® to USB-C® cable

MODEL**Announce Date** : 2025-02-14**Region** : NA**EAN / UPC / JAN** : 0198156853820 / 0198156853820 / None

Product image is a sample, it may not match the real color of this model

- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference