



*All images in this datasheet are for illustrative purposes only.

UHD Signage UH5Q Series

UHD Signage Display with LG webOS Platform and Advanced Security



HDR Support



Slim & Even Bezel



webOS Smart Platform



LG Shield


UH5Q

Screen Size	65" / 55" / 49" / 43"
Screen Resolution	3,840 × 2,160 (UHD)
Brightness	Up to 500 nits (Typ.)
Surface Treatment (Haze)	65" / 55" / 43": 25% 49": 28%
Bezel Width	11.4 mm (Even Bezel)



Superb Picture Quality with Ultra HD Resolution

With the resolution of UHD, it makes the colors and details of the content vivid and realistic. In addition, the wide viewing angle provides clear content.



Even & Slim Bezel Design

The UH5Q series features perfectly balanced horizontal and vertical slim bezels, creating a visually harmonious display solution. Its specialized design simplifies installation in retail environments while delivering a truly immersive viewing experience.



Convenient webOS Platform

The UH5Q is equipped with a high-performance SoC (System on Chip) that allows for multiple tasks to be performed without a separate media player. The webOS platform provides app development tools with an intuitive UI that enhances user convenience, and includes webOS partner apps to create an SI-friendly (System Integrator) environment.



Design for Space Utilization

Designed with thin bezels and simple cable management, the UH5Q saves space. With specialized hidden power inlets, it can be installed close to the wall, leaving only about 13.5 mm of space with the slim bracket.

* The product image will differ slightly from the actual appearance of the product due to the variance caused by each inch option.



Durability that Provides Reliability

Optimized for business environments, the UH5Q is protected against salt, dust, iron powder and humidity thanks to conformal partial coating on power board, allowing for stable operation. Also, its customer-centric features, such as IP5x and Shock Monitoring*, provide both reliability and satisfaction.

* When a physical impact occurs on the product, an alert is provided to the administrator through the media controller.



Comprehensive Security

webOS Signage goes beyond security measures at the operating system (OS) level. LG Shield employs a five-tiered defense system, encompassing server, application, operating system, system, and hardware. Each layer operates independently, providing comprehensive protection against various threats. Also webOS platform support ETSI EN 303 645.




SuperSign™ Solutions

SuperSign* is an integrated and intuitive content management solution for creative and organized digital signage content in your space, connecting customers to a range of services with convenient user experiences. There are a variety of versions such as SuperSign Cloud, so discover and enjoy the version that best fits you.

* SuperSign must be purchased separately

CONNECTIVITY

65" / 55" / 49" / 43"



SPECIFICATIONS

		65UH5Q-E	55UH5Q-E	49UH5Q-E	43UH5Q-E	
Panel	Screen Size	65"	55"	49"	43"	
	Panel Technology	ADS	ADS	IPS	ADS	
	Back Light Type	Edge	Edge	Edge	Edge	
	Aspect Ratio	16:9	16:9	16:9	16:9	
	Native Resolution	3840x2160 (UHD)	3840x2160 (UHD)	3840x2160 (UHD)	3840x2160 (UHD)	
	Refresh Rate	60Hz	60Hz	60Hz	60Hz	
	Brightness (Typ.)	Up to 500 nits	Up to 500 nits	Up to 500 nits	Up to 500 nits	
	Contrast Ratio	1,200:1	1,200:1	1,100:1	1,200:1	
	Dynamic CR	1,000,000:1	1,000,000:1	1,000,000:1	1,000,000:1	
	Color Gamut	BT709 95%	BT709 95%	BT709 95%	BT709 95%	
	Viewing Angle (H x V)	178° x 178°	178° x 178°	178° x 178°	178° x 178°	
	Color Depth (Number of Colors)	1.07 Billion Colors (10 bit (D))	1.07 Billion Colors (10 bit (D))	1.07 Billion Colors (10 bit (D))	1.07 Billion Colors (10 bit (D))	
	Response Time	8ms (G to G)	8ms (G to G)	8ms (G to G)	8ms (G to G)	
	Surface Treatment (Haze)	25%	25%	25%	25%	
	Lifetime	Up to 50,000 Hrs	Up to 50,000 Hrs	Up to 50,000 Hrs	Up to 50,000 Hrs	
Operation Hours (Hours/Day)	24/7	24/7	24/7	24/7		
Portrait / Landscape	Yes / Yes	Yes / Yes	Yes / Yes	Yes / Yes		
Connectivity	Input	HDMI (3, HDCP 2.2/1.4), DP (HDCP 2.2/1.3), RS-232C (4 Pin Phone-Jack), RJ45 (LAN), IR, USB 2.0 Type A (2)				
	Output	Audio, RS-232C (4 Pin Phone-Jack), IR (No / Yes (Support IR Daisy Chain via RS232C In/Out))				
Mechanical	Bezel Color	Black	Black	Black	Black	
	Bezel Width	11.4 mm (Even)	11.4 mm (Even)	11.4 mm (Even)	11.4 mm (Even)	
	Weight (Head)	46.5 lbs. / 21.1 kg	31.5 lbs. / 14.3 kg	25.2 lbs. / 11.4 kg	20.7 lbs. / 9.4 kg	
	Packed Weight	59.5 lbs. / 27.0 kg	39.9 lbs. / 18.1 kg	31.3 lbs. / 14.2 kg	24.9 lbs. / 11.3 kg	
	Monitor Dimensions (W x H x D)	57.4 x 32.8 x 1.2 in. 1,459 x 835 x 29.7 mm	48.9 x 28.1 x 1.2 in. 1,240.1 x 711.9 x 29.7 mm	43.5 x 25 x 1.2 in. 1,104.3 x 635.5 x 29.7 mm	38.3 x 22.1 x 1.2 in. 971.7 x 561.0 x 29.7 mm	
	Carton Dimensions (W x H x D)	62.2 x 37.4 x 6.8 in. 1,580 x 950 x 172 mm	53.5 x 31.9 x 5.9 in. 1,360 x 810 x 152 mm	47.8 x 29.2 x 5.6 in. 1,215 x 742 x 142 mm	41.5 x 25.9 x 5.5 in. 1,055 x 660 x 140 mm	
	VESA™ Standard Mount Interface	300 x 300 mm	300 x 300 mm	300 x 300 mm	200 x 200 mm	
Key Features	Internal Memory 16 GB, Wi-Fi & Bluetooth (Built-in), Temperature Sensor, Auto Brightness Sensor ² , Acceleration (Gyro) Sensor, Local Key Operation, webOS 8.0, Local Contents Scheduling, Group Manager, USB Plug & Play, Fail Over, Booting Logo Image, No Signal Image, RS-232C Sync, Local Network Sync, PIP, PBP (4), Screen Share, Video Tag (4), Play via URL, Screen Rotation, External Input Rotation, Gapless Playback, Tile Mode Setting (Max. 15 x 15), Setting Data Cloning, SNMP/ISM Method, Auto Set ID, Status Mailing, Control Manager, Crestron Connected ² , Smart Energy Saving, PM Mode, Wake on LAN, Network Ready, Beacon, HDMI-CEC ³ , SI Server Setting, webRTC, ProIdiom					
Environmental Conditions	Operation Temperature	32°F to 104°F / 0°C to 40°C	32°F to 104°F / 0°C to 40°C	32°F to 104°F / 0°C to 40°C	32°F to 104°F / 0°C to 40°C	
	Operation Humidity	10% to 80%	10% to 80%	10% to 80%	10% to 80%	
Power	Power Supply	100-240 Vac, 50/60 Hz	100-240 Vac, 50/60 Hz	100-240 Vac, 50/60 Hz	100-240 Vac, 50/60 Hz	
	Power Type	Built-In Power	Built-In Power	Built-In Power	Built-In Power	
	Power Consumption	Typ. / Max.	130 W (TBD) / 184 W (TBD)	103 W / 154 W	83 W (TBD) / 134 W (TBD)	65 W / 124 W (TBD)
		BTU (British Thermal Unit)	444 BTU/Hr (Typ.), 699 BTU/Hr (Max.)	351 BTU/Hr (Typ.), 525 BTU/Hr (Max.)	283 BTU/Hr (Typ.), 457 BTU/Hr (Max.)	222 BTU/Hr (Typ.), 423 BTU/Hr (Max.)
		Smart Energy Saving (70%)	91 W	72 W	58 W	46 W
		DPM	0.5 W	0.5 W	0.5 W	0.5 W
Power off	0.5 W	0.5 W	0.5 W	0.5 W		
Sound	Built-in Speakers	Yes (10W X 2)	Yes (10W X 2)	Yes (10W X 2)	Yes (10W X 2)	
Certification	Safety	CB / NRTL	CB / NRTL	CB / NRTL	CB / NRTL	
	EMC	FCC Class "B" / CE / KC	FCC Class "B" / CE / KC	FCC Class "B" / CE / KC	FCC Class "B" / CE / KC	
	ERP / Energy Star	Yes / Yes	Yes / Yes	Yes / Yes	Yes / Yes	
	ePEAT (US Only)	Yes (Carbon "Reducing CO ₂ ")	Yes (Carbon "Reducing CO ₂ ")	Yes (Carbon "Reducing CO ₂ ")	Yes (Carbon "Reducing CO ₂ ")	
Software Compatibility	SuperSign CMS, SuperSign Control+, SuperSign WB, SuperSign Cloud, Mobile CMS, LG ConnectedCare ⁴					
Language	English, French, German, Spanish, Italian, Korean, Chinese (Simplified), Chinese (Original), Portugues (Brazil), Swedish, Finnish, Norwegian, Danish, Russian, Japanese, Portugues (Europe), Dutch, Czech, Greek, Türkçe, Arabic, Polski					
Warranty & Other	Basic	Remote Controller, Power Cord, QSG, Regulation Book, Phone to RS232C Gender, Cable Holder (For Power Cord), IR/Light Sensor Receiver (EU/EK Only), Magnetic Sheet (2, EU/EK Only)				
	Optional	Slim Wall Mount (WB21LMA/B), Normal Wall Mount (OLW4B0A/B), IR/Light Sensor Receiver (ACC-L)				
	Tilt (Face up/Face down)	Yes (Max. 15° Degree, 40°C Temperature)	Yes (Max. 15° Degree, 40°C Temperature)	Yes (Max. 15° Degree, 40°C Temperature)	Yes (Max. 15° Degree, 40°C Temperature)	
	IP Rating	IP5X	IP5X	IP5X	IP5X	
	Conformal Coating (Power Board)	Yes (Partial Space Coating)	Yes (Partial Space Coating)	Yes (Partial Space Coating)	Yes (Partial Space Coating)	
	Warranty	3 year limited	3 year limited	3 year limited	3 year limited	

- 1) The luminosity ratio of Full Black / Full White color on video input condition.
- 2) Network based control.
- 3) Compatibility may differ by equipment.
- 4) The availability can differ by region.

