

PERFORMANCE

Processor

MediaTek Dimensity 6400 (8C, 2x A76 @2.5 GHz + 6x A55@2.0 GHz)

Graphics

Integrated Arm Mali-G57 MC2 GPU

Chipset

MediaTek SoC Platform

Memory

8GB Soldered LPDDR4x

Storage

128GB UFS 2.2

Card Reader

microSD Card Slot

Max Storage Support

- 128GB UFS 2.2 on systemboard
- microSD card, supports up to 2TB (exFAT)

Speakers

4 speakers, optimized with Dolby Atmos®

Microphone

Dual Microphone

Camera

Front 8.0MP / Rear 13.0MP

VoiceCall

No

Vibration Motor

No support

Sensors

- Accelerometer sensor
- Ambient light sensor (ALS)
- Hall sensor

Battery

10200mAh (Typical)

Power Adapter

None

DESIGN

Display^[1]

12.1" 2.5K (2560x1600) IPS 600nits (typical) / 800nits (HBM), 96% DCI-P3, 90Hz, Touch

Touchscreen

10-point Multi-touch

Screen-to-Body Ratio

87.5%

Pen

Pen Bundled

Keyboard

None

Dimensions (WxDxH)^{[2][3]}

278.8 x 181.05 x 6.29 mm (10.98 x 7.13 x 0.25 inches)

Weight^[4]

Around 530 g (1.17 lbs)

Case Color

Luna Grey

Case Material

Metal

SOFTWARE

Operating System^[5]

Android™ 15 or Later

CONNECTIVITY

WLAN + Bluetooth®

Wi-Fi® 5, 802.11ac 1x1 + BT5.2

WWAN

Non-WWAN

Location Services

GPS + GLONASS + Galileo

Standard Ports

- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging
- 1x Card slot
- 1x Pogo pin connector (3-point)

SECURITY & PRIVACY

Fingerprint Reader

None

SERVICE

Base Warranty^[6]

1-year, Mail-in

ACCESSORIES

Bundled Accessories

Lenovo® Tab Pen + Folio Case

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 9.0 (only available for TB361FU)
- ErP Lot 6/26
- RoHS compliant

Dust and Water Resistant

IP52

Other Certifications

- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

Product : TB361FU

TopSeller : No

Announce Date : 2025-06-26

EAN / UPC / JAN : 199271888568



Product image is a sample, it may not match the real color of this model

Note:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

[2] The system dimensions may vary depending on configurations.

[3] The height is 8.55 mm (0.34 inches) with the camera bump.

[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[5] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

[6] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the [web page](#).

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Tab Pen Plus

ZG38C05194

With 4,096 levels of pressure and tilt detection, sketch, draw or just take notes with the highest degree of precision, responsiveness and control yet with the new Lenovo Tab Pen Plus, featuring ultra-low-latency, hig...



Lenovo Multi-Device Wireless Keyboard

ZG38C05810

Upgrade your tablet experience with the Lenovo Multi-Device Wireless keyboard. Connect to up to 3 devices, and switch among them effortlessly. Whether you are using Android, Windows or iOS, you are just one tab away f...

Please click [here](#) to view the full list of accessories.

Lenovo

PSREF
Product Specifications
Reference