

PERFORMANCE

Processor

Intel® Core™ Ultra 5 226V, 8C (4P + 4LPE) / 8T, Max Turbo up to 4.5GHz, 8MB

AI PC Category^[1]

Copilot+ PC

NPU

Integrated Intel® AI Boost, up to 40 TOPS

Graphics

Integrated Intel® Arc™ Graphics 130V

Chipset

Intel® SoC Platform

Memory

16GB Soldered LPDDR5x-8533, MoP Memory

Memory Slots

Lunar Lake: memory soldered to systemboard, no slots, dual-channel

Max Memory

Lunar Lake: 16GB soldered memory, not upgradable

Storage

512GB SSD M.2 2242 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Slot

Models with V series processor: one M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support^[2]

Lunar Lake: one drive, up to 1TB M.2 2280 SSD

Card Reader

No card reader

Audio Chip

High Definition (HD) Audio, Senary SN6147 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®, audio by HARMAN

Microphone

2x, Array

Camera

FHD 1080p + IR Hybrid with Privacy Shutter

Battery

48Wh

Power Adapter

65W USB-C® (2-pin)

DESIGN

Display^[3]

14" WUXGA (1920x1200) IPS 300nits Anti-glare, 45% NTSC, 60Hz

Screen-to-Body Ratio

90%

Pen

Pen Not Supported

Keyboard

Backlit, English

Dimensions (WxDxH)^[4]

313 x 220.3 x 10.1/15.25 (front/rear), 19.7 (maximum) mm; 12.32 x 8.67 x 0.40/0.60 (front/rear), 0.78 (maximum) inches

Weight^[5]

Starting at 1.32 kg (2.91 lbs)

Case Color

Black

Case Material

Aluminium (Top), Aluminium (Bottom)

SOFTWARE

Operating System

Windows® 11 Pro, English (US) / English (UK)

CONNECTIVITY

WLAN + Bluetooth^[6]

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN

Non-WWAN

Ethernet

100/1000M (RJ-45)

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.1 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)

Optional Ports (configured)

1x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.1 and DisplayPort™ 2.1

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® E14 Gen 7 \(Intel®\)](#)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0 Enabled

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Other Security

- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)
- ThinkShield

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

1-year, Courier or Carry-in

CERTIFICATIONS

Green Certifications^[7]

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

TopSeller	: Yes	Announce Date	: 2025-08-21
EAN / UPC / JAN	: 199271867211	End of Support	: 2032-02-22



Product image is a sample, it may not match the real color of this model

Note:

[1] Copilot+ PCs have at least 16GB RAM, 256GB storage, and.....

· Lenovo reserves the right to change specifications without notice.
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please access the [web page](#).

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Universal USB-C Dock

40AY0090US

THE SMARTER WAY TO WORK Introducing the ThinkPad Universal USB-C Dock. This advanced, universally compatible one-cable docking solution lets you work smarter, not harder. It comes with a vast array of ports, next-gen ...

Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Courier/Carry-in (5WS1L39180)
BETTER	3Y Premier Support Upgrade from 1Y Courier/Carry-in (5WS0T36151)
GOOD	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A23681)

Please click [here](#) to view the full list of accessories.



PSREF
Product Specifications
Reference