HP OmniDesk Slim Desktop S03-0039 PC (BB4S0AA)



Overview

The slim, reliable desktop PC for home productivity

HP OmniDesk Slim Desktop helps easily manage daily tasks, from organizing family photos to streaming shows and managing budgets. This slim and reliable desktop PC features the latest Intel® Processors[1], ample memory for fast data transfers, the latest easy-access ports and fast, reliable Wi-Fi technology[3].

Effortless tech for at-home productivity

Enjoy effortless at-home productivity with the Intel® Processor[1], fast data transfers and easy access ports.

Seamless connectivity for multi-device homes

Connect easily with the latest ports and enjoy reliable Wi-Fi 6[3] technology for seamless online experiences.

Slim build, more space

With its slim design, the HP OmniDesk Slim Desktop blends into any interior while freeing up space.

Reliable performance, responsible design

The HP OmniDesk Slim Desktop PC is designed using recycled metals and post-consumer recycled plastic[4].

Features

Windows 11

Get a fresh perspective

From a rejuvenated Start menu, to new ways to connect to your favorite people, news, games, and content—Windows 11 is the place to think, express, and create in a natural way.[5]

Intel® Core™ i3,5,7

The performance you need to connect and learn. Intel® Core™ performance and graphics help you navigate and collaborate confidently. Enjoy an immersive experience with Intel® Core™ high-quality processors.[6]

EPEAT® Gold with Climate+

With EPEAT® Gold with Climate+, you're choosing a movement towards responsibility and climate action.[7]

ENERGY STAR® certified

Save energy and money with ENERGY STAR®, certified by the EPA so you will use less energy and save money where it counts most.[8]

Design contains recycled metals and post-consumer recycled plastics

Built for a better tomorrow. Designed using recycled metals and post-consumer recycled plastics to reduce environmental impact and promote super energy efficiency.[9]

Effortlessly connected

Enjoy faster speeds, improved performance and greater capacity with Wi-Fi 6 and Bluetooth® 5.4 wireless card.[10]

---

[1] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[3] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 (802.11ax) is backwards compatible with prior 802.11 specs. The specifications for Wi-Fi 6 are draft and are not final. If the final specifications differ from the draft specifications, it may affect the ability of the notebook to communicate with other Wi-Fi 6 devices. Only available in countries where 802.11ax is supported. Wi-Fi 6 (802.11ax) is not supported in Ukraine, Russia, and Indonesia where Wi-Fi settings will be optimized to local regulatory requirements (802.11ac).

[4] Percentage of ocean-bound plastic contained in each component varies by product. Ocean Bound plastic is expressed as a percentage of the total weight plastic. Ocean Bound plastic is based on the definition set by the UL2809 standard. Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT standard for computers, IEEE 1680.1-2018 standard.

[5] Not all features are available in all editions or versions of Windows. Systems may require upgraded and/or separately purchased hardware, drivers, software or BIOS update to take full advantage of Windows functionality. Windows is automatically updated and enabled. High speed internet and Microsoft account required. ISP fees may apply and additional requirements may apply over time for updates. See http://www.windows.com.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel’s numbering is not a measurement of higher performance.

[7] EPEAT® Gold with Climate+ registered where applicable. EPEAT registration varies by country. See www.epeat.net for registration status by country.

[8] ENERGY STAR and the ENERGY STAR logo are registered trademarks of the U.S. Environmental Protection Agency.

[9] Laptops manufactured with recycled ocean-bound plastic material in product speaker enclosures, recycled aluminum material in product cover and post-consumer recycled plastic in keycaps. Percentage of material contained in each component varies by product.

[10] Wireless access point and internet service required and sold separately. Availability of public wireless access points limited. Wi-Fi 6 is backwards compatible with prior 802.11 specs. Wi-Fi 6 is designed to support gigabit data rate when transferring files between two devices connected to the same router. Requires a wireless router, sold separately, that supports 80MHz and higher channels. Wi-Fi 6 (802.11ax) is not supported in Belarus where Wi-Fi settings will be optimized to local regulatory requirements (802.11ac). Bluetooth® 5.4 operation requires Microsoft OS/Chrome OS support. Until Microsoft OS/Chrome OS support is available, Bluetooth® 5.4 will function as Bluetooth® 5.3 or lower. Bluetooth® is a trademark owned by its proprietor and used by HP Inc. under license.

Specifications

Form Factor	Customized
Operating System Software	Windows 11 Home
Product Color Description (fixed)	Meteor silver, jack black chassis
Processor Family	Intel® Core™ i3 14th generation processor
Processor Name	Intel® Core™ i3-14100 (up to 4.7 GHz with Intel® Turbo Boost Technology, 12 MB L3 cache, 4 cores, 8 threads)[6,7]
Chipset	Intel® H770
Standard Memory Description 01	8 GB DDR5-4800 MT/s (1 x 8 GB)
Memory Slots	2 DIMM
Hard Drive Description (01)	512 GB PCIe® Gen4 NVMe™ M.2 SSD
Product Design	Paint coat
Graphics Card Segment 01	Integrated
GScardseg 01 Available Card 01	Intel® UHD Graphics
Product Dimensions (metric)	30.35 x 10 x 30.80 cm
Product Dimensions (imperial)	11.94 x 3.94 x 12.13 in
Weight (metric)	3.8 kg
Weight (imperial)	8.38 lb
Keyboard	HP 510SP Black Wireless Keyboard and Mouse Combo
Video Connectors	1 HDMI 1.4b; 1 DisplayPort™ 1.4a
External I/O Ports	1 USB Type-C® 10Gbps signaling rate; 3 USB Type-A 5Gbps signaling rate; 1 headphone/microphone combo
Expansion Slots	2 M.2 (1 for SSD, 1 for WLAN)
External I/O Ports 02	4 USB 2.0 Type-A; 1 RJ-45; 1 line out
Package Dimensions (metric)	49.9 x 20 x 39.8 cm
Package Weight (metric)	6.2 kg
Network Interface	Integrated 10/100/1000 GbE LAN
Wireless Technologies	Realtek Wi-Fi 6 (2x2) and Bluetooth® 5.4 wireless card
Power Supply Type	180 W AC power adapter
Energy Star Certified	ENERGY STAR® certified
Sustainable Impact Specifications	At least 20% recycled metal; At least 60% post-consumer recycled plastic
Security Management	Kensington Security lock slot; Padlock
Software Included	McAfee Online Protection 30-day trial
Software - Productivity & Finance	1 month trial for new Microsoft 365 customers[24]
Cloud Service	100 GB Dropbox storage for 3 months[1]

UPC Number	198990840376

Additional specifications

Bluetooth Version	Bluetooth® 5.4
Color	Meteor silver
Ecolabels	EPEAT® Gold with Climate+
Ethernet (RJ-45)	1
HDMI out – version	1.4b
HDMI –out	1
Headphone/microphone combo	1
I/O Port Location 01	Front
I/O Port Location 02	Rear
Keyboard Connectivity	Wireless
Memory Layout (Slots & Size)	1 x 8 GB
Memory Module Type	UDIMM
Memory Size	8
Memory Size UOM	GB
Memory Slots Number	1
Memory Speed	4800
Memory Speed UOM	MT/s
Memory Storage Simplified	8 GB memory;512 GB SSD storage
Memory Type	DDR5
Package Dimensions (imperial)	19.65 x 7.87 x 15.67 in
Package Weight (imperial)	13.67 lb
Processor Brand	Intel®
Processor Cache Installed	12 MB L3
Processor Core	4
Processor Family (Short)	Core™ i3
Processor Frequency Technology	Intel® Turbo Boost Technology
Processor Generation	14th Generation
Processor Maximum Frequency	4.7
Processor Maximum Frequency UOM	GHz
Processor Model	14100
Processor Socket	LGA1700
Processor Threads	8
Product Brand Name	HP

Product Long Name Specifications	HP OmniDesk Slim Desktop S03-0039 PC, Windows 11 Home, Intel® Core™ i3, 8GB RAM, 512GB SSD, Meteor silver
Product Long Name Specifications V2	Windows 11 Home, Intel® Core™ i3, 8GB RAM, 512GB SSD, Meteor silver
Product Short Name Specifications	HP OmniDesk Slim Desktop S03-0039 PC, Intel® Core™ i3, 8GB RAM, 512GB SSD
Storage Capacity 01	512
Storage Capacity UOM 01	GB
Storage Form Factor 01	M.2
Storage Interface 01	PCIe® Gen 4
Storage Interface Protocol 01	NVMe™
Storage Type 01	SSD
Storage type (filter)	SSD
UNSPSC Code	43211507
USB Type-A	7
USB Type-C	1
Wireless Antenna	2x2
Wireless Standard	Wi-Fi 6
Wireless Supplier	Realtek

---

[1] 100 GB of free Dropbox storage for 3 months from date of registration. For complete details and terms of use, including cancellation policies, visit the Dropbox website at https://www.dropbox.com/help/space/hp-promotion. Internet service required and not included.

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See http://www.intel.com/technology/turboboost/ for more information.

[24] Must activate within 180 days of Windows activation.

Monitors

Business Monitors

★ : Recommended

E-Series

HP E22 G5 FHD Monitor	6N4E8AA	
HP E22 G5 FHD Monitor	6N4E8AS	
HP E22 G5 FHD Monitor	6N4E8E9	
HP E24 G5 FHD Monitor	6N6E9AA	
HP E24i G4 WUXGA Monitor	9VJ40AA	
HP E24m G4 FHD USB-C Conferencing Monitor	40Z32AA	
HP E24mv G4 FHD Conferencing Monitor	169L0AA	
HP E24mv G4 FHD Conferencing Monitor	169L0AS	
HP E24mv G4 FHD Conferencing Monitor	169L0E9	
HP E24t G5 FHD Touch Monitor	6N6E6AA	
HP E24t G5 FHD Touch Monitor	6N6E6AS	
HP E24t G5 FHD Touch Monitor	6N6E6E9	
HP E24u G5 FHD USB-C Monitor	6N4D0AA	
HP E27 G5 FHD Monitor	6N4E2AA	
HP E27 G5 FHD Monitor	6N4E2AL	
HP E27 G5 FHD Monitor	6N4E2AS	obsolete
HP E27 G5 FHD Monitor	6N4E2E9	obsolete
HP E27 G5 FHD PVC Free Monitor	6N4E2A5	obsolete
HP E27k G5 4K USB-C Monitor	6N4C4AA	
HP E27k G5 4K USB-C Monitor	6N4C4AS	
HP E27k G5 4K USB-C Monitor	6N4C4E9	
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AA	
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29AS	
HP E27m G4 QHD USB-C Conferencing Monitor	40Z29E9	
HP E27u G5 QHD USB-C Monitor	6N4D3AA	
HP E32k G5 4K USB-C Monitor	6N4D6AA	
HP E32k G5 4K USB-C Monitor	6N4D6AS	
HP E32k G5 4K USB-C Monitor	6N4D6E9	
HP E32k G5 4K USB-C PVC Free Monitor	6N4D6A5	
HP E45c G5 DQHD Curved Monitor	6N4C1AA	

HP E45c G5 DQHD Curved Monitor	6N4C1AS	
HP E45c G5 DQHD Curved Monitor	6N4C1E9	

Business LCD Monitors

HP P204v 19.5-inch Monitor	5RD66A7	
HP P204v 19.5-inch Monitor	5RD66AA	

P-Series

HP P22a G5 FHD Monitor - P22a	8D5J1AA	obsolete
HP P22b G5 FHD Monitor - P22b	8D5K4AA	obsolete
HP P22h G5 FHD Monitor	64W30AA	
HP P24a G5 FHD Monitor - P24a	8D5J5AA	obsolete
HP P24a G5 FHD Monitor - P24a	8D5J5L9	obsolete
HP P24h G5 FHD Monitor	64W34AA	
HP P27 G5 FHD Monitor	64X69AA	
HP P27h G5 FHD Monitor	64W41AA	
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56A7	
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56AA	
HP P34hc G4 WQHD USB-C Curved Monitor	21Y56AS	

Series 3 Pro

HP Series 3 Pro 21.45 inch FHD Monitor - 322pv	9U5A2A6	
HP Series 3 Pro 21.45 inch FHD Monitor - 322pv	9U5A2AA	
HP Series 3 Pro 21.45 inch FHD Monitor - 322pv	9U5A2AS	
HP Series 3 Pro 21.5 inch FHD Monitor - 322pf	9U5B0AF	
HP Series 3 Pro 21.5 inch FHD Monitor - 322pf	9U5B0AS	
HP Series 3 Pro 21.5 inch FHD Monitor - 322pf	9U5B0UT	
HP Series 3 Pro 23.8 inch FHD Monitor - 324pf	9U5J5AF	
HP Series 3 Pro 23.8 inch FHD Monitor - 324pf	9U5J5AS	
HP Series 3 Pro 23.8 inch FHD Monitor - 324pf	9U5J5UT	
HP Series 3 Pro 23.8 inch FHD Monitor - 324pv	9U5C1A6	
HP Series 3 Pro 23.8 inch FHD Monitor - 324pv	9U5C1AA	
HP Series 3 Pro 23.8 inch FHD Monitor - 324pv	9U5C1AS	

Series 5 Pro

HP Series 5 Pro 23.8 inch FHD Monitor - 524pf	9D9L6AL	

HP Series 5 Pro 23.8 inch FHD Monitor - 524pf	9D9L6UT
HP Series 5 Pro 23.8 inch FHD Monitor - 524pf PVC Free	9D9L6A5
HP Series 5 Pro 23.8 inch FHD No Stand Monitor - 524pf	9D9L6A9
HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu	9D9V7AA
HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu	9D9V7AS
HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu	9D9V7E9
HP Series 5 Pro 23.8 inch FHD USB-C Monitor - 524pu PVC Free	9D9V7A5
HP Series 5 Pro 24 inch WUXGA Monitor - 524pn	9D9A7AA
HP Series 5 Pro 24 inch WUXGA Monitor - 524pn PVC Free	9D9A7A5
HP Series 5 Pro 27 inch QHD Monitor - 527pq	9D9S0UT
HP Series 5 Pro 27 inch QHD Monitor - 527pq PVC Free	9D9S0A5
HP Series 5 Pro 27 inch QHD No Stand Monitor - 527pq	9D9S0A9
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5AA
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5AS
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu	9E0G5E9
HP Series 5 Pro 27 inch QHD USB-C Monitor - 527pu PVC Free	9E0G5A5

Series 7 Pro

HP Series 7 Pro 23.8 inch FHD Monitor - 724pf	8X530AA
HP Series 7 Pro 23.8 inch FHD Monitor - 724pf	8X530E9
HP Series 7 Pro 23.8 inch FHD Monitor - 724pf PVC Free	8X530A5
HP Series 7 Pro 24 inch WUXGA Monitor - 724pn	8X534AA
HP Series 7 Pro 24 inch WUXGA Monitor - 724pn	8X534E9
HP Series 7 Pro 24 inch WUXGA Monitor - 724pn PVC Free	8X534A5
HP Series 7 Pro 24 inch WUXGA USB-C Monitor - 724pu	8Y2F7AA
HP Series 7 Pro 24 inch WUXGA USB-C Monitor - 724pu	8Y2F7E9
HP Series 7 Pro 24 inch WUXGA USB-C Monitor - 724pu PVC Free	8Y2F7A5
HP Series 7 Pro 27 inch 4K Conferencing Monitor - 727pm	8K135AA
HP Series 7 Pro 27 inch 4K Conferencing Monitor - 727pm	8K135E9
HP Series 7 Pro 27 inch 4K Conferencing Monitor - 727pm PVC Free	8K135A5
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk	8J9G2AA
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk	8J9G2E9
HP Series 7 Pro 27 inch 4K Thunderbolt 4 Monitor - 727pk PVC Free	8J9G2A5
HP Series 7 Pro 27 inch QHD Monitor - 727pq	8J4D8E9
HP Series 7 Pro 27 inch QHD Monitor - 727pq	8J4D8UT
HP Series 7 Pro 27 inch QHD Monitor - 727pq PVC Free	8J4D8A5

HP Series 7 Pro 27 inch QHD Thunderbolt 4 Monitor - 727pu	8J9E6E9
HP Series 7 Pro 27 inch QHD Thunderbolt 4 Monitor - 727pu	8J9E6UT
HP Series 7 Pro 27 inch QHD Thunderbolt 4 Monitor - 727pu PVC Free	8J9E6A5
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9AA
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk	8Y2K9E9
HP Series 7 Pro 31.5 inch 4K Thunderbolt 4 Monitor - 732pk PVC Free	8Y2K9A5
HP Series 7 Pro 34 inch WQHD Conferencing Monitor - 734pm	8K157E9
HP Series 7 Pro 34 inch WQHD Conferencing Monitor - 734pm	8K157UT
HP Series 7 Pro 34 inch WQHD Conferencing Monitor - 734pm PVC Free	8K157A5
HP Series 7 Pro 37.5 inch WQHD+ Thunderbolt 4 Monitor - 738pu	8K167AA
HP Series 7 Pro 37.5 inch WQHD+ Thunderbolt 4 Monitor - 738pu	8K167E9
HP Series 7 Pro 37.5 inch WQHD+ Thunderbolt 4 Monitor - 738pu PVC Free	8K167A5
HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor - 740pm PVC Free	8Y2R2A5
HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor-740pm	8Y2R2AA
HP Series 7 Pro 39.7 inch 5K2K Conferencing Monitor-740pm	8Y2R2E9

HP Home Monitors

Series 3

HP Series 3 27 inch FHD Monitor - 327se	B7HS7AA

Series 5

HP Series 5 31.5 inch FHD Monitor - 532sf	94F51A6

OMEN by HP Displays

OMEN Transcend 31.5 inch UHD 240Hz OLED Gaming Monitor - OMEN Transcend 32	9R181AA
OMEN by HP 23.8 inch FHD 165Hz Gaming Monitor - OMEN 24	780F0A6
OMEN by HP 31.5 inch QHD 165Hz Curved Gaming Monitor - OMEN 32c	780K7A6

HyperX Gaming Peripherals

HyperX Microphones

★ : Recommended

HyperX USB/XLR Microphones

HyperX FlipCast - USB/XLR Dynamic Microphone (Black)	B2CM1AA

Hybrid Work Solutions

Audio

★ : Recommended

Wired Headset

Poly Blackwire 3220 Stereo USB-C Headset +USB-C/A Adapter	93S87AA
Poly Blackwire 3220 USB-C Headset USB-C/A Adapter	B7SL7AA
Poly Blackwire 5220 Headset +3.5mm Plug USB-C/A Adapter	B7SL8AA
Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter	93S88AA

Speakerphones

Poly Sync 10 Speakerphone +USB-A to C Cable	B7SM0AA
Poly Sync 10 Speakerphone +USB-A to USB-C Cable	7S4M6AA

Wireless Headset

Poly Voyager 4310-M Headset UC	B7SL4AA
Poly Voyager 4310-M UC Headset +USB-C Cable +BT700 dongle	7Y210AA
Poly Voyager 4320-M Headset +USB-C Cable +BT700 dongle	7Y211AA
Poly Voyager 4320-M Headset UC	B7SL5AA
Poly Voyager Focus 2 USB-C-C Headset USB-C/A Adapter Charging Stand Customer Special 1	A58JDAA
Poly Voyager Focus 2 USB-C-C Headset USB-C/A Adapter Customer Special 1	A58JCAA
Poly Voyager Focus 2-M USB-C-C Headset USB-C/A Adapter Charging Stand	A4HT2AA
Poly Voyager Focus 2-M USB-C-C Headset USB-C/A Adapter Charging Stand Customer Special 1	A4HT5AA
Poly Voyager Focus 2-M USB-C-C Headset USB-C/A Adapter Customer Special 1	A4HT0AA
Poly Voyager Legend 30 Headset	AV4P5AA
Poly Voyager Legend 30 Headset Customer Special 1	AV4P6AA
Poly Voyager Legend 50 Headset	AV4P1AA
Poly Voyager Legend 50 Headset Customer Special 1	AV4N9AA
Poly Voyager Legend 50-M Headset UC	AV4P2AA
Poly Voyager Legend 50-M Headset UC Customer Special 1	AV4P0AA
Poly Voyager Surround 80 UC Microsoft Teams Certified USB-C Black Headset +USB-C/A Adapter	9D452AA
Poly Voyager Surround 80 UC Microsoft Teams Certified USB-C Headset +USB-C/A Adapter	8H2G3AA

Disclaimer — Copyright

Intel, Core, Optane, Celeron, Pentium, Iris, XMM, and Thunderbolt are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. AMD, Ryzen, Athlon, and Radeon are trademarks of Advanced Micro Devices, Inc. Qualcomm and Snapdragon are trademarks or registered trademarks of Qualcomm Technologies, Inc. and/or its subsidiaries. Bluetooth is a trademark owned by its proprietor and used by HP Inc. under license. NVIDIA and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. McAfee and McAfee LiveSafe are trademarks or registered trademarks of McAfee LLC in the United States and other countries. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. All other trademarks are the property of their respective owners.

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 28, 2026 6:30 AM UTC+0000