

**PERFORMANCE****Display Size**

27"

**View Area**

597.7x335.7 mm

**Panel**

In-Plane Switching

**Backlight**

WLED

**Aspect Ratio**

16:9

**Resolution**

2560x1440

**Pixel Pitch**

0.0777x0.2331 mm

**Dot / Pixel Per Inch**

109 dpi

**View Angle (H / V)**

178° / 178°

**Response Time**

4ms GtG (Extreme mode) / 6ms GtG (Typical mode)

**Color Support**

16.7 Million

**Refresh Rate**

48Hz - 120Hz

**Brightness**350 cd/m<sup>2</sup>**Contrast Ratio**

1500:1

**Color Gamut**

99% sRGB, 99%BT.709

**Screen Surface Treatment**

Anti-glare

**Curvature**

None

**Camera**

Integrated webcam (5MP, IR+RGB)

**Microphone**

Integrated Microphone

**Speakers**

5Wx2

**Power Consumption (Typical / Maximum)**

23.4W / 173W

**Power Adapter**

Integrated

**DESIGN****Stand**

Tilt, Swivel, Pivot, Height Adjust Stand

**Case Color**

Eclipse Black

**Side Bezel Width**

2 mm

**Mounting**

Supports VESA mount 100 x 100 mm

**ThinkCentre M Series Support**

Tiny Support

**Dimensions (WxDxH)<sup>[1]</sup>**

• Highest Position | 613.6 x 200 x 584.2 mm (24.16 x 7.87 x 23.00 inches)

• Lowest Position | 613.6 x 200.0 x 429.2 mm (24.16 x 7.87 x 16.90 inches)

• Head Only | 613.6 x 50.0 x 404.8 mm (24.16 x 1.97 x 15.94 inches)

**Packaging Dimensions (WxDxH)**

782.0 x 132.0 x 480.0 mm (30.79 x 5.20 x 18.90 inches)

**Weight<sup>[2]</sup>**

• Monitor With Stand | 7.2 kg (15.9 lbs)

• Monitor Head Only | 5.0 kg (11.0 lbs)

**Packaging Weight**

10.5 kg (23.1 lbs)

**CONNECTIVITY****USB Port**

1x USB-C® (USB 5Gbps, PD 3.0 100W, USB upstream), 3x USB-A (USB 5Gbps, 1x BC 1.2, USB downstream), 1x USB-C (USB 5Gbps, 15W PD, USB downstream)

**Video Connector**

1x HDMI® 2.1 TMDS, 1x DP 1.4 (HBR2), 1x DP 1.4 Out, 1x USB-C® (DP 1.4 Alt Mode HBR2)

**Network Connectivity**

1x RJ45, Ethernet (10M/100M/1000M)

**SERVICE****Base Warranty**

3-year

**CERTIFICATIONS****Environmental Certification**

ENERGY Star Certified, TCO 10, TCO Edge 2.1, EPEAT™ Gold, EU Energy Efficiency Level (Level-F), Volatile Organic Compound Certification, RoHS

**Ergonomic Certification**

Eyesafe® Display 2.0, TÜV Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort (5 Stars)

**Sync Technology**

None

**Special Features**

- AI Feature (Smart Face Framing, Multi-person Detection, Smart Volume Control)
- Conference Indicator
- LADM (Lenovo® Accessories and Display Manager) Lenovo Accessories and Display Manager supports Windows® 10 & 11, Mac OS (functions vary across systems). Lenovo Accessories and Display Manager is formerly Lenovo Display Control Center.
- LDFM (Lenovo® Display Fleet Manager)
- Mirrored Power Button
- Natural Low Blue Light
- Smart Power
- Smart Sensor (Auto Ambient Brightness Sensor, Human Detection Sensor)
- Windows® Hello

**SOFTWARE****Operating System**

Support Windows® 10, Windows 11

**ACCESSORIES****In the Box**

- Monitor with stand
- 1x DP 1.4 cable (1.8m)
- 1x USB-C® to USB-C Gen 1 cable (1.8m)
- 1x Power cable (1.8m)
- Quick setup guide

**MODEL****Region** : APS**EAN / UPC / JAN**: 0198157434493 / 198157434493 / None**Announce Date** : 2025-08-19

Note:

- [1] The system dimensions may vary depending on configurations.
- [2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
- Please refer to the official [Lenovo store website](#) or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

**Base Warranty** - Included with the systems you purchase, default 1- or 3-year coverage window.

**Warranty Extensions & Upgrades** - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories

 UAE (United Arab Emirates)



Humanscale Dual Monitor Arm White  
4ZE1U10767



ThinkVision MS30 Monitor Soundbar  
4XD1J05151



ThinkVision MC60 Monitor Webcam  
4XC1J05150

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference