

NEWLAND 3-STAGE QUICK ASSEMBLY HEIGHT ADJUSTABLE TABLES

Newland™ 3-stage quick assembly height adjustable tables are an effective option for workplace wellness programs. They encourage users to move freely and ergonomically between sitting and standing throughout the day, increasing productivity and promoting healthy work habits without work interruption. Height adjustable tables can be used stand-alone or in conjunction with freestanding desking products.



quick assembly instructions

Leg columns, support beam and motors are all preassembled. Unfold leg columns. Attach feet and worksurface support to base. Fasten assembly to top. Plug in connections and start to use.



features + benefits

- quick assembly base design allows user to be operational in 15 minutes or less
- 3-stage base with height range of 22.6" to 48.2"H including 1" thick top
- each leg column is powered by its own motor, kept synchronized by the control box
- telescopic support beam accommodates top widths from 46" to 76" wide x 23" to 29" deep
- return kits can be added to create L-shaped configurations
- easy to use up/down controller with digital read-out and four memory programmable positions
- 265 lbs. lift capacity for rectangular tables
330 lbs. for L-shaped tables
- anti-collision sensor
- travel speed 1.2" per second
- 10 standard laminate finish options
- 1" thick thermally fused laminate tops with 2mm matching edgeband
- Black, Designer White or Tungsten finish base
- standby power consumption 0.1W, active power consumption 220W
- meet ANSI/BIFMA X5.5
- ETL/CETL and GREENGUARD certified

model # width depth

rectangular tables	NL48243QHT	46"	23"
	NL60243QHT	58"	23"
	NL72243QHT	70"	23"
	NL60303QHT	58"	29"
	NL72303QHT	70"	29"
return kits	NL36243QHR	35"	23"
	NL42243QHR	41"	23"



website



NEWLAND 3-STAGE QUICK ASSEMBLY HEIGHT ADJUSTABLE TABLES

surface

high performance thermally fused laminate tops, 1" thick with matching 2mm edgebanding

telescopic frame accommodates 46" to 76" widths in 1mm increments

steel tube

3.3" x 2.1"

height range

22.6" to 48.2"
with 1" top

travel speed
1.2"/second

return

add-on return kits
to create L-shaped
configurations

controller

easy to use digital
read-out with four
memory positions

motors

3-stage,
dual motors

foot

low profile, flat foot
design, no cross bar


anti-collision sensor




ACJ Absolute Acajou



ASN Asian Night




DES Dark Espresso



DWT Designer White



NBL Noce Biondo



NGL Noce Grigio



NEL Noce Leggero



NML Noce Medio



WHC White Chocolate



WCR Winter Cherry

