Product datasheet

Specifications



APC Easy UPS On-Line, 10kVA/10kW, Rackmount 2U, 230V, 1x Hard wire 3-wire(1P+N+E) outlet, Intelligent Slot, Extended runtime, No battery, W/O rail kit

SRVPM10KRIL

Overview

Lead time	Usually in Stock

Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	10000 W
Rated power in VA	10000 VA
Output connector type	Hard wire 3-wire (1P + N + E) 1
Number of rack unit	2U
Provided equipment	1 USB cable 1 RS-232 configuration cable 1 rack mounting brackets 1 battery cable user manual

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	8.65 cm
Width	43.8 cm
Depth	61.5 cm
Net weight	16 kg
Mounting location	Front

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting preference	Lower
Mounting mode	Rack-mounted with kit
USB compatible	Yes
Mounting position	Horizontal

Input

Input voltage limits	110...300 V half load 176...300 V full load
Number of input connectors	1 hard wire 3-wire (1P + N + E)
Network frequency	40...70 Hz auto sensing

Output

Maximum configurable power in VA	10000 VA
Maximum configurable power in W	10000 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	94 % (full load)
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

Conformance

Product certifications	CE EAC
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	0…40 °C
Relative humidity	0…95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-15…60 °C
Storage Relative Humidity	0…95 % Non-condensing
Storage altitude	0…15000 m
Acoustic level	58 dBA
IP degree of protection	IP20

Batteries & Runtime

Battery type	External battery system
Battery voltage	240 V
Number of battery filled slots	0
Number of battery free slots	0

Battery charger power	1170 W rated

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slots	1

Surge Protection and Filtering

Surge energy rate	600 J

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 cm
Package 1 Width	76 cm
Package 1 Length	60 cm
Package 1 Weight	20 kg

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace

Recommended replacement(s)