

**PERFORMANCE****Processor**

Intel® Core Ultra 7 265H, 16C (6P + 8E + 2LPE) / 16T, Max Turbo up to 5.3GHz, 24MB

**AI PC Category**

AI PC

**NPU**

Integrated Intel® AI Boost, up to 13 TOPS

**Graphics**

NVIDIA® GeForce RTX™ 5070 8GB GDDR7 Laptop GPU

**Chipset**

Intel® SoC Platform

**Memory**

32GB LPCAMM2 LPDDR5x-7467

**Memory Slots**

One LPCAMM2 connector, dual-channel

**Max Memory**

Up to 64GB (1x 64GB LPCAMM2), upgradable

**Storage**

1TB SSD M.2 2280 PCIe® 5.0x4 Performance NVMe® Opal 2.0

**Storage Slot**

Two M.2 2280 PCIe® 4.0 x4 slots

**Max Storage Support<sup>[1]</sup>**

Up to two M.2 2280 Gen 5 Performance SSD; up to 8TB, 4TB each

**RAID Preset**

None

**Card Reader**

SD Express 7.0 Card Reader

**Audio Chip**

SoundWire®, Cirrus Logic® CS42L43 codec

**Speakers**

Stereo speakers, 2W x2, Dolby Atmos®

**Microphone**

2x, Array

**Camera**

5.0MP + IR with Privacy Shutter and Computer Vision Human Presence Detection on ISP

**Battery**

90Wh

**Power Adapter**

140W USB-C® GaN (3-pin)

**DESIGN****Display**

16" WQUXGA (3840x2400) IPS 800nits Anti-glare, 100% DCI-P3, 60Hz, DisplayHDR™ 400, Dolby Vision®, Eyesafe®, TÜV Low Blue Light

**Touchscreen**

None

**Screen-to-Body Ratio**

91.7% (IPS models)

**Color Calibration**

X-Rite® Factory Color Calibration

**Pen**

Pen Not Supported

**Keyboard**

Backlit, Canadian French

**Dimensions (WxDxH)<sup>[2]</sup>**

354.3 × 241.0 × 9.9 / 15.8 (front / rear), 20.6 (maximum) mm 13.95 x 9.49 x 0.39 / 0.62 (front / rear), 0.81 (maximum) inches

**Weight<sup>[3]</sup>**

Starting at 1.84 kg / 4.06 lbs

**Case Color**

Black

**Case Material**

Aluminium (Top), Aluminium (Bottom)

**SOFTWARE****Operating System**

Windows® 11 Pro, French / Canadian French / English

**Bundled Software**

Intel® Connectivity Performance Suite

**CONNECTIVITY****WLAN + Bluetooth**

Intel® Wi-Fi® 7 BE201, 802.11be 2x2 + BT5.4, vPro®

**WWAN**

Non-WWAN

**SIM Card**

None

**Ethernet**

No Onboard Ethernet

**NFC**

None

**Standard Ports**

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2), Always On
- 2x Thunderbolt™ 5, with USB PD 3.1 and DisplayPort™ 2.1, 140W input / 15W output
- 1x Thunderbolt™ 4, with DisplayPort™ 2.1 and USB PD 3.1, 140W input / 15W output
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x SD Express 7.0 card reader

**Docking**

Various docking solutions supported via Thunderbolt™ or USB-C®. For more compatible docking solutions, please visit [Docking for ThinkPad T1g Gen 8](#)

**SECURITY & PRIVACY****Security Chip**

Discrete TPM 2.0 Enabled

**Physical Locks**

Kensington® Nano Security Slot, 2.5 x 6 mm

**Fingerprint Reader**

Touch Style, Match-on-Chip, Integrated in Power Button

**Other Security**

- Bottom cover tamper detection
- Camera privacy shutter
- Computer Vision-based User Presence Sensing on Image Signal Processor (ISP)
- IR camera for Windows® Hello (facial recognition)

**MANAGEABILITY****System Management**

Intel® vPro® Enterprise

**SERVICE****Base Warranty**

1-year, Courier or Carry-in

**Included Upgrade**

1Y Premier Support Upgrade from 1Y Courier/Carry-in

**ACCESSORIES****CERTIFICATIONS****Green Certifications**

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered
- RoHS compliant
- TCO Certified, generation 10

**Mil-Spec Test**

MIL-STD-810H military test passed

**Other Certifications**

- Eyesafe® Certified 2.0
- Intel® Evo™ Platform
- TÜV Rheinland® Low Blue Light

**MODEL**

TopSeller : Yes EAN / UPC / JAN: 199272428008

Announce Date: 2025-09-05 End of Support : 2032-04-25

• Lenovo reserves the right to change specifications without notice. To see more note information, please access the [web page](#).

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams) 4XD1S19778



Lenovo Self-Charging Bluetooth Keyboard-French Canadian 058 4Y41R69498



Lenovo Essential FHD Webcam Gen2 4XC1S15018

Please click [here](#) to view the full list of accessories.

**Lenovo**

**PSREF**  
Product Specifications  
Reference