Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Power Cord, C19 to L6-20P, 3.7m



AP9871

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Product or Component Type	Power cord	
Input Connection Type	NEMA L6-20P	
Number of rack unit	0U	
Cable length	12 ft (3.7 m)	
Number of cables	1	

Physical

Color	Black	
Height	2.52 in (6.4 cm)	
Width	4.02 in (10.2 cm)	
Depth	11.50 in (29.2 cm)	
Net Weight	2.2 lb(US) (1 kg)	
Mounting Location	Front	
Mounting preference	No preference	
Mounting Mode	Not rack-mountable	

Input

Input Frequency	50/60 Hz
Permissible voltage	200240 V
Max line current	16 A
Input current limits	16 A

Output

Max current draw	16 A	
Number of power socket outlets	1 IEC 60320 C19	
Protection Type	Without circuit breaker	

Conformance

Product Certifications	CSA	
	UL Listed	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

Ambient air temperature for operation	32113 °F (045 °C)	
Relative Humidity	095 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.000000000 m)	

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS	
Discount Schedule	APC1	
GTIN	731304111030	
Returnability	No	
Country of origin	US	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	4.02 in (10.2 cm)	
Package 1 Width	12.01 in (30.5 cm)	
Package 1 Length	4.02 in (10.2 cm)	
Package 1 Weight	2.4 lb(US) (1.1 kg)	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes