Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rack PDU, Basic, Zero U, 20A, 120V, (14)5-15

AP9551

Usually in Stock

Toolless Mounting Kit User Manual

Overview

Lead time

Main	
Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	12 ft (3.7 m)
Number of cables	1
Provided Equipment	Rack Mounting brackets

Complementary

Input Voltage	100 V 120 V	
Height	24.02 in (61 cm)	
Width	1.65 in (4.2 cm)	
Output Voltage	120 V	
Depth	1.73 in (4.4 cm)	
Net Weight	4.9 lb(US) (2.2 kg)	
Mounting Location	Side	
Mounting preference	No preference	
Input Plug Type	NEMA L5-20P	
Mounting Mode	Rack-mounted	
Rack units	OU	
Mounting position	Vertical	
Line Rated Current	16 A	
Permissible voltage	90132 V	
Max line current	20 A	
Input current limits	20 A	
Load Capacity	1920 VA	
Input Frequency	50/60 Hz	
Outlet type and quantity	14 NEMA 5-15R	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cUL Listed CSA	
	UL Listed	
Ambient air temperature for operation	32113 °F (045 °C)	
Relative Humidity	095 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.000000000 m)	

Ordering and shipping details

GTIN 731304021247	
-------------------	--

Packing Units

•		
Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	25.51 in (64.8 cm)	
Package 1 Width	5.98 in (15.2 cm)	
Package 1 Length	7.01 in (17.8 cm)	
Package 1 Weight	6.44 lb(US) (2.92 kg)	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	56
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
[™] Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes