
Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications





AP9560

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Color	Black	
Product or Component Type	PDU	
PDU Type	Basic	
Cord length	12 ft (3.7 m)	
Number of cables	1	
Provided Equipment	User Manual Rack Mounting brackets	

Complementary

Input Voltage	100 V 120 V	
Height	1.73 in (4.4 cm)	
Width	17.60 in (44.7 cm)	
Output Voltage	120 V	
Depth	2.24 in (5.7 cm)	
Net Weight	5.5 lb(US) (2.5 kg)	
Mounting Location	Front Rear	
Mounting preference	No preference	
Input Plug Type	NEMA L5-30P	
Mounting Mode	Rack-mounted	
Rack units	1U	
Mounting position	Horizontal	
Line Rated Current	24 A	
Permissible voltage	90132 V	
Max line current	24 A	
Input current limits	30 A	
Load Capacity	2880 VA	
Input Frequency	50/60 Hz	
Outlet type and quantity	10 NEMA 5-20R	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Product Certifications	cUL Listed UL Listed
Standards	UL 60950
Ambient air temperature for operation	5113 °F (-1545 °C)
Relative Humidity	095 %
Operating altitude	010000 ft
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)
Storage Relative Humidity	095 %
Storage altitude	050000 ft (0.000000000015240.0000000000 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS	
Discount Schedule	APC1	
GTIN	731304192930	
Returnability	No	
Country of origin	IN	

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	5.98 in (15.2 cm)	
Package 1 Width	6.97 in (17.7 cm)	
Package 1 Length	19.13 in (48.6 cm)	
Package 1 Weight	8.02 lb(US) (3.64 kg)	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	64
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
[™] Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Halogen content performance	Product contains halogen above thresholds
Take-back	Yes