

APC Step-Down Transformer RM 2U 208V IN 120V OUT; w/5-20 Receptacles

AP9626

Overview

Presentation	The Step-Down Transformer converts high voltage (208 or 200 VAC) output into low voltage (120 or 100 VAC) output for powering low voltage AC equipment.
Lead time	Usually in Stock

Main

····	
Main Input Voltage	208 V
Product or Component Type	Accessory
Main Output Voltage	120 V
Input Connection Type	NEMA L6-30P
Number of rack unit	2U
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Physical

Color	Black	
Height	3.50 in (8.9 cm)	
Width	17.52 in (44.5 cm)	
Depth	24.02 in (61 cm)	
Net Weight	95.20 lb(US) (43.18 kg)	
Mounting Location	Front	
Mounting preference	No preference	
Mounting Mode	Rack-mounted	

Input

Permissible voltage	208 V
Max line current	24 A
Input current limits	30 A
Load Capacity	5000 VA

Output

Max current draw	24 A
Number of power socket outlets	12

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Efficiency	90 %
Number of power socket outlets	12 NEMA 5-20R

Conformance

Product Certifications	CSA
Standards	OSHPD UL 1778

Environmental

Ambient air temperature for operation	32104 °F (040 °C)	
Relative Humidity	095 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	5113 °F (-1545 °C)	
Storage Relative Humidity	095 %	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	

Ordering and shipping details

GTIN 731304249139

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	37.52 in (95.3 cm)
Package 1 Length	24.49 in (62.2 cm)
Package 1 Weight	110.2 lb(US) (50 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	4550
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances		
EU RoHS Directive	Compliant with Exemptions	
REACh Regulation	REACh Declaration	
[⋄] Energy efficiency		
Optimized Energy Efficiency	Energy efficient product	

Use Again

○ Repack and remanufacture		
Circularity Profile	End of Life Information	
Halogen content performance	Product contains halogen above thresholds	
Take-back	Yes	