

Product data sheet

Specifications



APC Smart-UPS RT 192V RM Battery Pack

SURT192RMXLBP3U

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	208 V
Product or Component Type	External battery pack
Main Output Voltage	208 V
Number of rack unit	3U
Number of cables	1.0
Battery Type	Lead-Acid battery
Provided Equipment	Installation guide Rack Mounting brackets User Manual
Range of Product	Smart-UPS Battery Systems

Batteries & Runtime

Battery blocks per string	16
Battery Slots Empty	0
Included Battery Modules	4
Device mounting	Stand alone battery stack
Battery Voltage	192V
Additional information	Replace all batteries in operation together (UPS internal and external batteries) all-at-once
RBC Quantity	2
Replacement battery	APCRBC140

Physical

Color	Black
Height	5.1 in (130 mm)
Width	17.008 in (432 mm)
Depth	26.0 in (660 mm)
Net Weight	200.42 lb(US) (90.91 kg)
Mounting Mode	Rack-mounted
USB compatible	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Battery Capacity	18 Ah
------------------	-------

Conformance

Standards	OSHDP
-----------	-------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
Storage Relative Humidity	0...95 % non-condensing

Ordering and shipping details

GTIN	731304259336
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	16.3 in (41.3 cm)
Package 1 Width	39.4 in (100 cm)
Package 1 Length	23.6 in (60 cm)
Package weight(Lbs)	223.46 lb(US) (101.36 kg)

Contractual warranty

Warranty (in months)	24
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	464 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	375 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	25 kg CO2 eq.
Carbon footprint of the installation phase [A5]	29 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	35 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	A64c500c-f72a-458b-8faa-8175a94429fe
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.