

# Product data sheet

Specifications



## APC NetShelter Basic Rack PDU, Zero U, 11 kW, 230V, 36 C13 and 6 C19 outlet

AP7557NA

### Overview

|           |                  |
|-----------|------------------|
| Lead time | Usually in Stock |
|-----------|------------------|

### Main

|                           |                                                                                      |
|---------------------------|--------------------------------------------------------------------------------------|
| Color                     | Black                                                                                |
| Product or Component Type | PDU                                                                                  |
| PDU Type                  | Basic                                                                                |
| Cord length               | 3.0 ft (0.9 m)                                                                       |
| Provided Equipment        | Installation guide<br>Rack Mounting brackets<br>Toolless Mounting Kit<br>User Manual |

### Complementary

|                          |                                     |
|--------------------------|-------------------------------------|
| Input Voltage            | 400 V 3 phase                       |
| Height                   | 70 in (1778 mm)                     |
| Width                    | 2.2 in (56 mm)                      |
| Output Voltage           | 230 V                               |
| Depth                    | 1.7 in (44 mm)                      |
| Net Weight               | 12.39 lb(US) (5.62 kg)              |
| Mounting Location        | Side                                |
| Mounting preference      | No preference                       |
| Input Plug Type          | IEC 60309 20 A 3P+N+E               |
| Mounting Mode            | Rack-mounted                        |
| Rack units               | 0U                                  |
| Mounting position        | Vertical                            |
| Line Rated Current       | 16 A                                |
| Input current limits     | 20 A                                |
| Load Capacity            | 11500 VA                            |
| Input Frequency          | 50/60 Hz                            |
| Outlet type and quantity | 36 IEC 60320 C13<br>6 IEC 60320 C19 |

### Environment

|                        |           |
|------------------------|-----------|
| Product Certifications | UL Listed |
|------------------------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |                            |
|---------------------------------------|----------------------------|
| Standards                             | UL 60950-1                 |
| Ambient Air Temperature for Operation | 23...113 °F (-5...45 °C)   |
| Relative Humidity                     | 5...95 %                   |
| Operating altitude                    | 0...10000 ft               |
| Ambient Air Temperature for Storage   | -13...149 °F (-25...65 °C) |
| Storage Relative Humidity             | 5...95 %                   |
| Storage altitude                      | 0...50000 ft (0...15240 m) |

## Ordering and shipping details

|      |              |
|------|--------------|
| GTIN | 731304263784 |
|------|--------------|

## Packing Units

|                        |                      |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE                  |
| Nbr. of units in pkg.  | 1                    |
| Package 1 Height       | 84.02 in (213.4 cm)  |
| Package 1 Width        | 5.0 in (12.7 cm)     |
| Package 1 Length       | 6.0 in (15.2 cm)     |
| Package weight(Lbs)    | 20.7 lb(US) (9.4 kg) |

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 24 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



### Environmental footprint

|                                                        |                                               |
|--------------------------------------------------------|-----------------------------------------------|
| Total lifecycle Carbon footprint                       | 137 kg CO2 eq.                                |
| Carbon footprint of the manufacturing phase [A1 to A3] | 24 kg CO2 eq.                                 |
| Carbon footprint of the distribution phase [A4]        | 0.4 kg CO2 eq.                                |
| Carbon footprint of the installation phase [A5]        | 0 kg CO2 eq.                                  |
| Carbon footprint of the use phase [B2, B3, B4, B6]     | 9 540 kg CO2 eq.                              |
| Carbon footprint of the end-of-life phase [C1 to C4]   | 0.8 kg CO2 eq.                                |
| Environmental Disclosure                               | <a href="#">Product Environmental Profile</a> |

## Use Better



### Materials and Substances

|                                        |                                                                             |
|----------------------------------------|-----------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                         |
| Packaging without single use plastic   | No                                                                          |
| SCIP Number                            | 1cdb2fed-a06f-4574-913d-8df8e70936b2                                        |
| EU RoHS Directive                      | <a href="#">Compliant</a>                                                   |
| REACH Regulation                       | <a href="#">Free of Substances of Very High Concern above the threshold</a> |
| Halogen content performance            | Product contains halogen above thresholds                                   |

## Use Longer



### Lifetime extension

|        |    |
|--------|----|
| Repair | No |
|--------|----|

## Use Again



### Repack and remanufacture

|                               |                                                                                                                                                                                                                  |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Recyclability potential, in % | 45                                                                                                                                                                                                               |
| Circularity Profile           | <a href="#">End of Life Information</a>                                                                                                                                                                          |
| Take-back                     | Nej                                                                                                                                                                                                              |
| WEEE Label                    |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |