Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



APC Universal Transfer Switch 6-circuit 120V, L5-30

UTS6H

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Product or Component Type	Transfer switch
Main Output Voltage	120 V
Other Output Voltage	240 V
Input Connection Type	IEC 60320 C14 NEMA 5-15P NEMA L5-30P
Number of cables	1
Provided Equipment	Hardwire panel User Manual Installation guide

Physical

Color	Black	
Height	19.61 in (49.8 cm)	
Width	15.51 in (39.4 cm)	
Depth	3.31 in (8.4 cm)	
Net Weight	21.54 lb(US) (9.77 kg)	
Mounting Location	Front Side Top	
Mounting preference	No preference	
Mounting Mode	Not rack-mountable	
USB compatible	No	

Input

Input Frequency	4763 Hz
Max line current	20 A

Conformance

Product Certifications cTUVus

Environmental

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient air temperature for operation	-13104 °F (-2540 °C)	
Relative Humidity	595 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)	
Storage altitude	010000 ft (0.00000000003048.0000000000 m)	

Ordering and shipping details

GTIN 731304264514

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.98 in (53.3 cm)
Package 1 Width	5.98 in (15.2 cm)
Package 1 Length	17.52 in (44.5 cm)
Package 1 Weight	24.05 lb(US) (10.91 kg)
SCC14	10731304264511

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	0faaa581-e733-4efc-987a-3938986edbd8
REACh Regulation	REACh Declaration
China RoHS Regulation	China RoHS declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No